

AUTOMOTIVE GRADE WIDE TERMINAL CHIP RESISTOR

TYPE 3430 SERIES

INTRODUCTION

TE Connectivity (TE) is pleased to introduce this latest automotive grade high power wide terminal chip resistor. The ruthenium based thick film element, along with the wide terminals helps to allow a greater power capability than previously possible with traditional methods. Highly reliable multilayer electrode construction and 100% CCD inspection improve long term stability and reliability.

•

FEATURES

- AEC-Q200 compliance
- Highly reliable multilayer electrode construction
- Compatible with all soldering processes
- 100% CCD inspection
- Moisture sensitivity level MSL1

APPLICATIONS

- Automotive industry
- Telecommunication equipment
- Radio and tape recorders, TV
 tuners
- Digital cameras, watches, pocket calculators
- Computers, instruments
 - Medical equipment

ELECTRICAL CHARACTERISTICS

| Item | Size | Power rating @70°C (W) | | Max | Resistance | Resistance | TCR | | |
|------|------|------------------------|----------------------|---------------------|---------------------|------------|----------|----|------|
| Size | code | Jumper Rated Current | Operating Voltage | Overload Voltage | range (m Ω) | Tolerance | (ppm/°C) | | |
| | | 1 W | | | 1R ~ 9R76 | 1% | ±150 | | |
| 0508 | A2 | | 200 V | 400 V | 10R ~ 1M | 170 | ±100 | | |
| | | Jumper 5 A | | | 0R <10 mΩ | - | - | | |
| 0612 | D2 | DЭ | B2 | B2 1.5 W 200 V | | 400 V | 1R ~ 1M | 1% | ±100 |
| 0012 | DZ | Jumper 6 A | 200 V | 400 V | 0R <10 mΩ | - | - | | |
| | | 2 W | | 400 V | 1R ~ 9R76 | 10/ | ±150 | | |
| 1020 | H2 | | 200 V | | 10R ~ 1M | 1% | ±100 | | |
| | | Jumper 10 A | | | 0R <10 mΩ | - | - | | |
| | | 3 W | | | 1R ~ 29R4 | 1% | ±200 | | |
| 1225 | A3 | luman an 10 A | 200 V | 400 V | 30R ~ 1M | 1% | ±100 | | |
| | | Jumper 12 A | | | 0R <10 mΩ | - | - | | |

Operating temperature range: -55 ~ 155 °C

Operating voltage= $\sqrt{(P^*R)}$ or Max. operating voltage listed above, whichever is lower.

Overload voltage= $2.5*\sqrt{(P*R)}$ or Max. overload voltage listed above, whichever is lower.

Tighter tolerances may be available on application





Type 3430 Series

DERATING CURVE



ENVIRONMENTAL CHARACTERISTICS

| Item | Requirement | Test Method | | | |
|--|---------------------------|--|--|--|--|
| Temperature coefficient of resistance (T.C.R.) | As spec | JIS-C-5201-1 4.8 IEC-60115-1 4.8 At 25 °C/-55 °C and 25 °C/+125 °C, 25 °C is the reference temperature | | | |
| Short time overload | ±(1.0%+0.05 Ω) | JIS-C-5201-1 4.13 IEC-60115-1 4.13 RCWV*2.5 or maximum overload voltage whichever is lower for 5 seconds | | | |
| Insulation resistance | ≥10G | JIS-C-5201-1 4.13 IEC-60115-1 4.13 RCWV*2.5 or maximum overload voltage whichever is lower for 5 seconds | | | |
| Operational life | ±(1.0%+0.10 Ω) | MIL-STD-202 method 108 Condition D steady state TA=125 °C at derated power. Measurement at 24±4 hours after test conclusion. | | | |
| Biased humidity | ±(1.0%+0.10 Ω) | MIL-STD-202 method 103 1000 hrs 85 °C/85%RH 10% of operating power. (≤100 V) | | | |
| High temperature exposure | ±(1.0%+0.05 Ω) | MIL-STD-202 method 108 at +155 °C for 1000 hrs | | | |
| Board flex | ±(1.0%+0.05 Ω) | AEC-Q200-005 Bending once for 60 seconds 3mm | | | |
| Solderability | 95% min. coverage | JIS-C-5201-1 4.17 IEC-60115-1 4.17 J-STD-002 245±5 °C for 3 seconds | | | |
| Resistance to soldering heat | ±(0.5%+0.05 Ω) | MIL-STD-202 method 210 260±5 °C for 10 seconds | | | |
| Voltage proof | No breakdown or flashover | JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times maximum overload voltage for 1 minute | | | |

Automotive Grade Wide Terminal Chip Resistor

Type 3430 Series

| Item | Requirement | Test Method |
|------------------------|--|---|
| Leaching | Individual leaching area ≤5% Total leaching area ≤10% | JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260 ±5 °C for 30 seconds |
| Temperature cycling | ±(0.5% +0.05 Ω) | JESD22 method JA-104 -55 °C to +125 °C, 1000 cycles |
| Mechanical shock | ±(0.25% +0.05 Ω) | MIL-STD-202 method 213 Wave Form: Tolerance for half sine shock pulse. Peak value is 100g's. Normal duration (D) is 6. |
| Vibration | ±(0.5% +0.05 Ω) | MIL-STD-202 method 204 5 g's for 20 min., 12 cycles each of 3 orientations, 10-2000 Hz |
| ESD | ±(3% +0.05 Ω) | AEC-Q200-002 Human body model: 2 KV |
| Resistance to solvents | No visible damage on appearance and marking. | MIL-STD-202 method 215 Add aqueous wash chemical - OKEM clean or equivalent. Do not use banned solvents. |
| Terminal strength | Not broken | AEC-Q200-006 Force of 1.8 kg for 60 seconds. |
| Flammability | No ignition of the tissue paper or scorching or the pinewood board | UL-94 V-0 or V-1 are acceptable. Electrical test not required. |
| Sulfur Test | ∆R ±1% | EIA-977 (Condition A) 60 ±2 °C, no power rating for 500 hrs. |

RCWV(Rated Continuous Working Voltage)= $\sqrt{(P^*R)}$ or Max. Operating Voltage whichever is lower. * not include Jumper(0Ω)

Storage Temperature: 15 °C ~28 °C; Humidity < 80%RH

Shelf Life: 2 years from production date.

CONSTRUCTION AND DIMENSIONS (Unit: mm)



| $(\widehat{1})$ Alumina Substrate | (4)Edge Electrode | (7) Resistor Layer |
|-----------------------------------|------------------------|--------------------|
| Bottom Electrode | 5 Barrier Layer | Primary Overcoat |
| 3 Top Electrode | 6 External Electrode | Secondary Overcoat |

| Туре | Size | L (mm) | W (mm) | T (mm) | D1 (mm) | D2 (mm) | Weight (g) 1000 pcs | |
|--------|-------|------------|------------|------------|-------------|-----------|---------------------|--|
| 3430A2 | 0500 | 105 101 | 200.101 | | 0.30 ±0.15 | 0.70+0.15 | F | |
| Jumper | 0508 | 1.25 ±0.1 | 2.00 ±0.1 | 0.55 ±0.1 | 0.20 ±0.15 | 0.30±0.15 | 5 | |
| 3430B2 | 0.010 | 155 101 | 7 00 1015 | 0.55.101 | 0.05 + 0.15 | 0.401015 | 8 | |
| Jumper | 0612 | 1.55 ±0.1 | 3.00 ±0.15 | 0.55 ±0.1 | 0.25 ±0.15 | 0.40±0.15 | ŏ | |
| 3430H2 | 1020 | 2.45 +0.15 | E 00 ±01 | 0.60 +0.15 | 0.35 ±0.20 | 0.70+0.20 | 26 | |
| Jumper | 1020 | 2.45 ±0.15 | 5.00 ±0.1 | 0.60 ±0.15 | 0.45 ±0.20 | 0.70±0.20 | 26 | |
| 3430A3 | 1225 | 7 20 ±0 20 | 6 40 ±0 15 | 0.65 ±0.15 | 0.40 ±0.20 | 1.10±0.20 | 41 | |
| Jumper | 1225 | 3.20 ±0.20 | 6.40 ±0.15 | 0.65 ±0.15 | 0.50 ±0.20 | 0.70±0.20 | 41 | |

Type 3430 Series

RECOMMENDED LAND PATTERN



| Size | A (mm) | B (mm) | C (mm) |
|------|--------|--------|--------|
| 0508 | 0.55 | 0.90 | 2.00 |
| 0612 | 0.70 | 0.80 | 3.20 |
| 1020 | 1.00 | 1.20 | 5.00 |
| 1225 | 1.00 | 2.00 | 7.00 |

SOLDERING CONDITION (REF. IPC/JEDEC J-STD-020 & J-STD-002)



| Reflow Profiles | |
|--|------------------|
| Profile Feature | Pb free assembly |
| Preheat | |
| Min. Temperature (Tsmin) | 150 °C |
| Max Temperature (Tsmax) | 200 °C |
| Preheating time (ts) from (Tsmin to Tsmax) | 60 - 120 seconds |
| Ramp-up rate (TL to TP) | 3 °C/second max. |
| Liquidous temperature (TL) Time (tL) maintained above TL | 217 °C |
| | 60 - 150 seconds |
| Min. Peak temperature (TP min) | 235°C |
| Max. Peak temperature (TP max) | 260°C |
| Time (tp) within 5 °C of the specified classification temperature (Tc) | 30 seconds max. |
| Ramp-down rate (TP to TL) | 6 °C/second max. |
| Time 25 °C to peak temperature | 8 minutes max. |

Type 3430 Series





PACKAGING

Reel dimensions and quantity



| Size | Qty | Tape Width | Reel Diameter | ΦA (mm) | ΦB (mm) | ΦC (mm) | W (mm) | T (mm) | |
|------|-----|------------|---------------|------------|---------------------|------------|------------|------------|--|
| 0508 | 5K | 0 | 7 la ch | 170 5 11 5 | 60 ^{+1/-0} | 17.0+0.2 | 00105 | 12 5 1 0 5 | |
| 0612 | 1K | 8mm | 7 Inch | 178.5±1.5 | 60 | 13.0±0.2 | 9.0±0.5 | 12.5±0.5 | |
| 1020 | 4K | 10 | 71 | 170 5 11 5 | 60 ^{+1/-0} | 17.0.1.0.5 | 17.0.1.0.5 | | |
| 1225 | 1K | 12mm | 7 Inch | 178.5±1.5 | 60 * | 13.0±0.5 | 13.0±0.5 | 15.5±0.5 | |

PAPER TAPE SPECIFICATION



| Size | A ±0.10 (mm) | B ±0,20 (mm) | W ±0.20 (mm) | E ±0.10 (mm) | F ±0.05 (mm) | P₀ ±0.10 (mm) | P ₁ ±0.05 (mm) | P₂ ±0.05 (mm) | ØD₀ +0.1 -0 (mm) | T ±0.10 (mm) |
|------|-----------------|-----------------|-----------------|-----------------|-----------------|------------------|------------------------------|------------------|---------------------|-----------------|
| 0508 | 1.60 | 2.40 | 8.0 | 1.75 | 3.5 | 4.0 | 4.0 | 2.0 | 1.5 | 0.85 |
| 0612 | 1.90 | 3.50 | 8.0 | 1.75 | 3.5 | 4.0 | 4.0 | 2.0 | 1.5 | 0.85 |

EMBOSSED PLASTIC TAPE SPECIFICATION



| Size | A (mm) | B (mm) | W ±0.10 (mm) | E ±0.10 (mm) | F ±0.05 (mm) | P₀ ±0.05 (mm) | P ₁ ±0.10 (mm) | P₂ ±0.05 (mm) | ØD₀ +0.10 (mm) | T ±0.20 (mm) |
|------|------------|------------|-----------------|-----------------|-----------------|------------------|------------------------------|------------------|-------------------|-----------------|
| 1020 | 2.80 ±0.15 | 5.40 ±0.20 | 12.00 | 1.75 | 5.50 | 4.00 | 4.00 | 2.00 | 1.55 | 1.00 |
| 1225 | 3.50 ±0.10 | 6.70 ±0.10 | 12.00 | 1.75 | 5.50 | 4.00 | 4.00 | 2.00 | 1.55 | 1.00 |

MARKING

All models 4 digit marking

| Resistance | 22.6Ω | 487Ω | 499ΚΩ |
|------------|-------|------|-------|
| Marking | 22R6 | 4870 | 4993 |

ORDERING INFORMATION

| | | | | Part | Num | her | | | |
|----------|------------------------|---|------|------|-----|-----|----|----------|-----------------------|
| | | | 3430 | H2 | F | 3K3 | TE | | |
| | | | | 1 | 1 | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| Common P | art | | | | | | | Packagii | ng |
| 3430 | Automotive Grade Wide |] | | | | | | TDF | 1K Reel |
| 3430 | Terminal Chip Resistor | | | | | | | TD | 5K Reel (0508 & 0612) |
| ize Code | | | | | | | | TE | 4K Reel (1020 & 1225) |
| A2 | 0508 | 1 | | | | | | | |
| B2 | | - | | | | | | Resistan | ce Value |
| | 0612 | - | | | | | | 1R0 | 1Ω |
| H2 | 1020 | - | | | | | | 100R | 100Ω |
| A3 | 1225 | | | | | | | 1КО | 1ΚΩ |
| | T . 1 | | | | | | | 100К | 100ΚΩ |
| | Tolerance | 1 | | | | | | 1MO | 1ΜΩ |
| F | 1% | | | | | | | | |

te.com

©2024 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

1773204-9 Rev. C 08/24 ED

