

CMH035N06A

60V, 3mΩ typ., 200A N-Channel MOSFET

General Description

The CMH035N06A uses advanced SGT technology to provide excellent RDS(ON). This device is ideal for high-frequency switching and synchronous rectification.

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant


Product Summary

BVDSS	R _{DS(on)} max.	ID
60V	3.4mΩ	200A

Applications

- High Frequency Switching and Synchronous Rectification
- BLDC

TO-247 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	60	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current	200	A
I _D @T _C =100°C	Continuous Drain Current	140	A
I _{DM}	Pulsed Drain Current ¹	800	A
EAS	Single Pulse Avalanche Energy ²	1512	mJ
P _D @T _C =25°C	Total Power Dissipation	300	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	47	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	0.42	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	60	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=20A$	---	3	3.4	mΩ
		$V_{GS}=4.5V$, $I_D=20A$	---	4	4.8	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1	---	3	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=60V$, $V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	±100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	42	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1.8	---	Ω
Q_g	Total Gate Charge	$I_D=20A$	---	54.2	---	nC
Q_{gs}	Gate-Source Charge	$V_{DD}=30V$	---	10.2	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	7.8	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=30V$ $V_{GS}=10V$ $R_G=2.7\Omega$	---	11.6	---	ns
T_r	Rise Time		---	46.5	---	
$T_{d(off)}$	Turn-Off Delay Time		---	47	---	
T_f	Fall Time		---	58	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	3700	---	pF
C_{oss}	Output Capacitance		---	1080	---	
C_{rss}	Reverse Transfer Capacitance		---	25	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	200	A
I_{SM}	Pulsed Source Current		---	---	800	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=30A$, $T_J=25^{\circ}\text{C}$	---	0.84	1.5	V

Note :

1.Repetitive rating; pulse width limited by maximum junction temperature.







2.The EAS data shows Max. rating . The test condition is $V_{DD}=30V$, $V_{GS}=10V$, $L=1\text{mH}$, $I_{AS}=55A$.


This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.

Typical Characteristics



Package Dimension
TO-247
Unit :mm


符号	机械尺寸/mm			符号	机械尺寸/mm		
	最小值	典型值	最大值		最小值	典型值	最大值
A	4.80	5.00	5.20	E2		5.00	
A1	2.21	2.41	2.61	E3		2.50	
A2	1.90	2.00	2.10	e		5.44	
b	1.10	1.20	1.35	L	19.42	19.92	20.42
b1		2.00		L1		4.13	
b2		3.00		P	3.50	3.60	3.70
c	0.55	0.60	0.75	P1		7.19	
D	20.80	21.00	21.20	P2		2.50	
D1		16.55		Q		5.80	
D2		1.20		S	6.05	6.15	6.25
E	15.60	15.80	16.0	T		10.00	
E1		13.30		U		6.20	