

# Multilayer Ceramic Chip Capacitor


**Part Number:** 2211Y5000394KXT

**Description:** 2211 500Vdc 390nF  $\pm 10\%$  X7R (2R1)

A range of X7R MLC capacitors to suit a variety of applications. In a wide selection of chip sizes, rated voltages and terminations, including FlexiCap™, the world's first commercially available flexible termination.

WS2 and WS3 parts use StackiCap™ patented construction technology.

Suffix code PXX or PX mandates the use of precious metal electrode (PME) materials. This may incur additional costs.



## Mechanical Specification

|                                            |                                                                                  |
|--------------------------------------------|----------------------------------------------------------------------------------|
| Size Code                                  | 2211                                                                             |
| Length (L1) in mm (")                      | 5.7 +0.50/-0.40 (0.225 +0.02/-0.016)                                             |
| Width (W) in mm (")                        | 2.79 $\pm$ 0.30 (0.11 $\pm$ 0.012)                                               |
| Thickness (T) in mm (")                    | 2.8 Max (0.11 Max)                                                               |
| Minimum Termination Band (L2,L3) in mm (") | 0.25 (0.010)                                                                     |
| Maximum Termination Band (L2,L3) in mm (") | 0.80 (0.030)                                                                     |
| Termination Material                       | FlexiCap™ Polymer termination, Nickel barrier, Sn Plated Solder (RoHS compliant) |
| Solderability                              | IEC-60068-2-58                                                                   |
| Packaging                                  | 7" Reel Horizontal Orientation, 500 per reel                                     |
| Conformal Coating                          | Not normally required                                                            |

## General Electrical Specification

|                                                              |                                                         |
|--------------------------------------------------------------|---------------------------------------------------------|
| Rated Voltage                                                | 500Vdc                                                  |
| Nominal Capacitance Value                                    | 390nF                                                   |
| Capacitance Tolerance                                        | $\pm 10\%$                                              |
| Tangent of Loss Angle (Tan $\delta$ )                        | $\leq 0.025$                                            |
| Capacitance and Tan $\delta$ Test Conditions                 | 1.0Vrms @ 1kHz                                          |
| Voltage Proof                                                | 750Vdc                                                  |
| (Voltage applied for 5 secs max. @ 50mA max. charge current) |                                                         |
| Min Insulation Resistance (IR)                               | 2.56GOhm @ 100Vdc                                       |
| Dielectric Classification                                    | X7R (2R1)                                               |
| Rated Temperature Range                                      | -55°C / +125°C                                          |
| Maximum Capacitance Change over Temperature Range            | No DC Voltage $\pm 15\%$<br>Rated DC Voltage -          |
| Climatic Category (IEC)                                      | 55/125/56                                               |
| Ageing Characteristic                                        | <2% per decade (nominal capacitance is 1000 hour value) |

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Tuesday, April 25, 2023

20230425 085300242UTC

# Multilayer Ceramic Chip Capacitor

**Part Number:** 2211Y5000394KXT

**Description:** 2211 500Vdc 390nF  $\pm 10\%$  X7R (2R1)

## Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

233 compliant

California Proposition 65

No exposure risk

## Board Layout

Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

### IPC-7351 pad design

|   | 2211   |        |
|---|--------|--------|
| C | 5.40mm | 0.213" |
| Y | 1.35mm | 0.053" |
| X | 3.10mm | 0.122" |



## Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.



## Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness  $> 1.0\text{mm}$ . Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

PdAg terminations are primarily intended for conductive epoxy attachment - they may be suitable for soldering but trials are recommended.

Application notes with mounting and handling guidance are available on request.



Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Tuesday, April 25, 2023

20230425 085300242UTC