

CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LSA-PLUS plug (COMTRAB CT 10) with coarse/fine surge protection, for 10 floating signal circuits. Nominal voltage: 24 V DC. Version: 10 double wires.

Your advantages

- Space-saving due to compact design
- Flexible fields of application with modular protective plug
- Can be used in LSA-PLUS disconnect and control strips or CT-TERMIBLOCK via adapted connection technology

Commercial data

Item number	2807955
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL03
Product key	CL3212
Catalog page	Page 106 (C-6-2013)
GTIN	4017918104740
Weight per piece (including packing)	125.3 g
Weight per piece (excluding packing)	125.15 g
Customs tariff number	85363010
Country of origin	DE

CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Technical data

Product properties

Product type	Surge protection for MCR technology
Product family	COMTRAB
IEC test classification	C1
	C2
	C3
	D1
Type	LSA-PLUS module
Surge protection fault message	none
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00
Wire pairs per module	10

Insulation characteristics

Overvoltage category	II
----------------------	----


Electrical properties

Nominal voltage U_N	24 V DC
-----------------------	---------

Connection data

Connection method	can be plugged into COMTRAB-TERMIBLOCK and LSA-PLUS disconnect and switching strips
-------------------	---

Dimensions

Dimensional drawing	
Width	111 mm
Height	22 mm
Depth	68.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Housing material	PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Maximum continuous voltage U_C	40 V DC
	28 V AC
Operating effective current I_C at U_C	$\leq 5 \mu A$ (a-b)
Residual current I_{PE}	$\leq 1 \mu A$ (per path)
Nominal discharge current I_n (8/20) μs (line-line)	119 A (25 °C)
Nominal discharge current I_n (8/20) μs (line-ground)	5 kA
Total surge current (8/20) μs	10 kA
Max. discharge current I_{max} (8/20) μs maximum (line-line)	119 A (25 °C)
Max. discharge current I_{max} (8/20) μs maximum (line-earth)	5 kA
Nominal pulse current I_{an} (10/1000) μs (line-line)	23 A (25 °C)
Output voltage limitation at 1 kV/ μs (line-line) spike	$\leq 70 V$
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 650 V$
Output voltage limitation at 1 kV/ μs (line-line) static	$\leq 60 V$
Output voltage limitation at 1 kV/ μs (line-earth) static	$\leq 650 V$
Residual voltage at I_n (conductor-conductor)	$\leq 85 V$
Residual voltage with I_{an} (10/1000) μs (line-line)	$\leq 65 V$
Response time t_A (line-line)	$\leq 1 ns$
Response time t_A (line-earth)	$\leq 100 ns$
Input attenuation aE, sym.	0.1 dB (typ. up to 2 MHz / 50 Ω)
	0.1 dB (typ. up to 1 MHz / 150 Ω)
	0.1 dB (typ. up to 400 kHz / 600 Ω)
Cut-off frequency f_g (3 dB), sym. in 50 Ω system	10 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 150 Ω system	4 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 600 Ω system	1 MHz (typ.)
Capacity (Core-Core)	1.1 nF ($f=1 MHz / V_R=0 V$)
Capacity (Core-Earth)	1 pF
Surge protection fault message	none
Impulse durability (line-earth)	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 100 A
	D1 - 2.5 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 75 °C

Standards and regulations

Air clearances and creepage distances

Standards/regulations	VDE 0110-1 / IEC 60664-1
-----------------------	--------------------------

CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Standards Information technology specification

Standards/regulations	IEC 61643-21
	IEC 61643-21
Standards/specifications	IEC 61643-21
Note	2000

Mounting

Mounting type	On CT-TERMIBLOCK and LSA-PLUS disconnect strip
---------------	--

CT 10-2PE/FS-24 - Surge protection plug


2807955

<https://www.phoenixcontact.com/us/products/2807955>




Drawings

Circuit diagram



Dimensional drawing



CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2807955>



EAC

Approval ID: EAC-Zulassung



EAC

Approval ID: RU C-DE.*09.B.00169

CT 10-2PE/FS-24 - Surge protection plug



2807955

<https://www.phoenixcontact.com/us/products/2807955>

Classifications

ECLASS

ECLASS-11.0	27130807
ECLASS-13.0	27171501

ETIM

ETIM 9.0	EC000943
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

CT 10-2PE/FS-24 - Surge protection plug



2807955
<https://www.phoenixcontact.com/us/products/2807955>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1dcf6c6b-0140-494c-ad67-1fddd62fb80b

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com