


UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



N disconnect terminal block, Assembly instructions:

For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips., nom. voltage: 400 V, nominal current: 76 A, Special and hybrid connection, 1st level connection right, Rated cross section: 16 mm², cross section: 2.5 mm² - 25 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: blue

Your advantages

- With screw disconnect slide

Commercial data

Item number	3006166
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1252
Catalog page	Page 509 (C-1-2017)
GTIN	4017918091385
Weight per piece (including packing)	23.185 g
Weight per piece (excluding packing)	23.185 g
Customs tariff number	85369010
Country of origin	TR

UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

Technical data

Notes

General	Assembly instructions: For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
---------	---

Product properties

Product type	Installation terminal block
Number of connections	2
Number of rows	1
Potentials	1

Data management status

Article revision	03
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	2.43 W
Current carrying capacity of the neutral busbar	140 A

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²

1st level connection right

Screw thread	M4
Tightening torque	1.5 ... 1.8 Nm
Stripping length	11 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross section rigid	2.5 mm ² ... 25 mm ²
Cross section AWG	12 ... 4 (converted acc. to IEC)
Conductor cross section flexible	4 mm ² ... 16 mm ²
Conductor cross section, flexible [AWG]	10 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm ² ... 16 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	1.5 mm ² ... 16 mm ²
2 conductors with same cross section, solid	1.5 mm ² ... 6 mm ²
2 conductors with same cross section, flexible	1.5 mm ² ... 4 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with TWIN	0.75 mm ² ... 10 mm ²

UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

ferrule with plastic sleeve	
Nominal current	76 A
Maximum load current	90 A (with 25 mm ² conductor cross section)
Nominal voltage	400 V
Nominal cross section	16 mm ²

Dimensions

Width	12 mm
End cover width	1.8 mm
Height	43.5 mm
Depth on NS 32	52 mm
Depth on NS 35/7,5	47 mm
Depth on NS 35/15	54.5 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-40 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Electrical tests

Surge voltage test

Test voltage setpoint	7.3 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 16 mm ²	1.92 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mechanical tests

UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 32/NS 35
Test force setpoint	10 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross section/weight	2.5 mm ² / 0.7 kg
	16 mm ² / 2.9 kg
	25 mm ² / 4.5 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32
Screw thread	M3

UIKN 16 BU - N disconnect terminal block

3006166

<https://www.phoenixcontact.com/us/products/3006166>



Drawings

Circuit diagram



UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3006166>



EAC

Approval ID: RU C-DE.BL08.B.00534

UIKN 16 BU - N disconnect terminal block



3006166

<https://www.phoenixcontact.com/us/products/3006166>

Classifications

ECLASS

ECLASS-11.0	27141138
ECLASS-12.0	27141138
ECLASS-13.0	27250111

ETIM

ETIM 9.0	EC001257
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UIKN 16 BU - N disconnect terminal block



3006166
<https://www.phoenixcontact.com/us/products/3006166>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com