








REVISIONS					
P.	LYR	DESCRIPTION	DATE	OWN	APVD
	A	RELEASE PER ECN-22-172004	29AUG2022	WZ	DZ



600	20	200	W/O CAP	15u" GOLD	1.20MM	1.20MM	4-2381578-9
			W/CAP	30u" GOLD	1.20MM	1.20MM	3-2381578-9
				15u" GOLD	1.20MM	1.20MM	2-2381578-9
			W/PICK AND PLACE TAPE	30u" GOLD	1.20MM	1.20MM	1-2381578-9
				15u" GOLD	1.20MM	1.20MM	2381578-9
			W/CAP	30u" GOLD	2.00MM	4.20MM	1-2381578-8
					2.00MM	3.00MM	1-2381578-7
					2.00MM	2.20MM	1-2381578-6
					2.00MM	1.50MM	1-2381578-5
				15u" GOLD	2.00MM	4.20MM	1-2381578-4
					2.00MM	3.00MM	1-2381578-3
					2.00MM	2.20MM	1-2381578-2
					2.00MM	1.50MM	1-2381578-1
			W/PICK AND PLACE TAPE	30u" GOLD	2.00MM	4.20MM	2381578-8
					2.00MM	3.00MM	2381578-7
					2.00MM	2.20MM	2381578-6
2.00MM	1.50MM	2381578-5					
15u" GOLD	2.00MM	4.20MM		2381578-4			
	2.00MM	3.00MM		2381578-3			
	2.00MM	2.20MM		2381578-2			
	2.00MM	1.50MM		2381578-1			
Q'TY/CARTON	POCKET TAPE PITCH	Q'TY/REEL	CAP OPTION	2 CONTACT FINISH	DIM B	DIM A	PART NUMBER

NOTES

1. MATERIALS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS STEEL
CONTACT: COPPER ALLOY.
PICK AND PLACE TAPE: POLYIMIDE FILM.

2 FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100u" MIN.
UNDER PLATING: NICKEL PLATING 50u" min OVER ALL
SHELL: UNDER PLATING: NICKEL PLATING 50u" min OVERALL.


3. HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-72

4 TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.

5 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 21-0CT-2020 CHK DAVID ZHANG 21-0CT-2020 APP'D DAVID ZHANG 21-0CT-2020	 TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.30 1 PLC ±.20 3 PLC ±.10 4 PLC ±.10 ANGLES ±.2°	NAME MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	SIZE A 00779 C-2381578	
MATERIAL - - -	FINISH - - -	APPLICATION SPEC 108-60133 114-60030	CAGE CODE -	DRAWING NO -
		WEIGHT -	RESTRICTED TO -	SHEET 1 OF 5
		CUSTOMER DRAWING -	SCALE 5:1	REV A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




RECOMMENDED PCB LAYOUT
(GENERAL TOLERANCES: ±0.05)


SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020	 TE Connectivity	
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS:		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	
mm		PRODUCT SPEC: 108-60133		
		APPLICATION SPEC: 114-60030	SIZE: A CAGE CODE: 00779 DRAWING NO: 2381578	
MATERIAL: -		WEIGHT: -	RESTRICTED TO: -	
		CUSTOMER DRAWING	SCALE: 5:1 SHEET: 2 OF 5 REV: A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-






COMPONENTS KEEP OUT AREA
LIMITATION HEIGHT: 0mm
SCALE 6:1




COMPONENTS KEEP OUT AREA
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020		
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS:		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD. 124P, SMT TYPE, 85ohm	
mm		PRODUCT SPEC: 108-60133		
		APPLICATION SPEC: 114-60030	SIZE: A CAGE CODE: 00779 DRAWING NO: 2381578	
MATERIAL: -		WEIGHT: -	RESTRICTED TO: -	
		CUSTOMER DRAWING	SCALE: 5:1 SHEET: 3 OF 5 REV: A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020	 TE Connectivity	
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS:		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	
mm		PRODUCT SPEC		
		108-60133	SIZE: A 00779 C=2381578	
		APPLICATION SPEC		
MATERIAL		114-60030	RESTRICTED TO	
		WEIGHT		
		CUSTOMER DRAWING	SCALE 5:1 SHEET 5 OF 5 REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2381578-5](#) [1-2381578-7](#) [1-2381578-6](#) [1-2381578-8](#) [1-2381578-9](#) [3-2381578-9](#) [2381578-5](#) [2381578-7](#)