





D

C

B

A



1. CODING IS AS FOLLOWS.SEE TABLE 1.

2.APPLIED RECEPTACLE CONTACT P/N:

DESCRIPTION	SINGLE-WIRE SEAL(5mm HOLE)	
PART NO.	828904	828905
INSULATION DIA.(Ø)	1.2~2.1mm	2.2~3.0mm

3.APPLIED WIRE SEAL P/N:

DESCRIPTION	2.8mm SENSOR-FLAT RECEPTACLE OR EQUIVALENT	
PART NO.	967542 OR EQU	967543 OR EQU
WIRE SIZE	0.5~1.0	>1.0~2.5

4. LASERPRINT MARK THE PRODUCT PART NUMBER. CHARACTER SIZE APPROX 1.2MM RAISE.CHARACTER LOCATION AND ORIENTATION AS SHOWN

5. LASERPRINT MARK DATE CODE:
IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(17=2017)
MONTH: THIRD DIGIT , EXCLUDING 1 , A=JAN, B=FEB, C=MARCH...(K=OCTOBER)
DAY: FOURTH AND FIFTH DIGITS(14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(11=11AM)

6. SUPPLY CONDITION: HINGE IN PRELOCKED POSITION

7. SUPPLY CONDITION: CPA IN PRELOCKED POSITION

TABLE 1

CODE 1:2345394-1	CODE 11:2345394-2
12.0	8.0

1	1	PC	RED	PA46-GF15	CPA	4
1	1	PC	GREEN	SILICON	INNER SEAL	3
1		PC	YELLOW	PA6-GF25	CODE 11	2
	1	PC	BLUE	PA6-GF25	CODE 1	2
1	1	PC	BLACK	PA6-GF25	HOUSING	1
-2	-1	U/M	COLOR	MATERIAL	DESCRIPTION	ITEM
D	D	REVISION OF EACH ASSY NO.				
7.6	7.6	WEIGHT OF EACH ASSY NO. [g]				
QTY PER ASSY		PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.ZHAO	26APR2019	TE Connectivity		
DIMENSIONS: mm		CHK E.JIANG	26APR2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±5 FINISH N/A		APVD I.YIN	26APR2019	NAME SEALED-4P-PLUG-CPA-ASSEMBLY (FLAT SENSOR CONNECTOR)		
MATERIAL SEE TABLE		PRODUCT SPEC 108-32584				
		APPLICATION SPEC 114-160078		SIZE A2	CAGE CODE C-2345394	DRAWING NO RESTRICTED TO -
		WEIGHT -		SCALE 1:1	SHEET 1 OF 1	REV D1
		CUSTOMER DRAWING				

D

C

B

A