



Part Number : [334721886](#)
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, with Connector Position Assurance, Yellow
Series Number : 33472
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[334721886_sd.pdf](#)

Specifications
[AS-33472-100-CH-001.pdf](#)
[AS-33611-001-001.pdf](#)
[TS-33472-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, with Connector Position Assurance, Yellow
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	887191681849

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	16
Color - Resin	Yellow
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	18.550/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No

Temperature Range - Operating	-40° to +150°C
-------------------------------	----------------

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>
