

General Description

The CMSA130N10 uses advanced SGT technology to provide excellent RDS(ON). This is suitable device for High Frequency Switching and Synchronous Rectification applications.

Features

- Low On-Resistance
- 100% avalanche tested
- Simple Drive Requirements
- RoHS Compliant


Product Summary

BVDSS	R _{DS(on)} max.	ID
100V	13mΩ	58A

Applications

- Synchronous Rectifier
- Motor Drive

DFN-8 5x6 Pin Configuration



Type	Package	Marking
CMSA130N10	DFN-8 5x6	CMSA130N10

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	100	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current	58	A
I _D @T _C =100°C	Continuous Drain Current	36	A
I _{DM}	Pulsed Drain Current	232	A
EAS	Single Pulse Avalanche Energy ¹	42	mJ
P _D @T _C =25°C	Total Power Dissipation	75	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	47	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	1.67	°C/W

Electrical Characteristics($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=20A$	---	11.6	13	mΩ
		$V_{GS}=4.5V$, $I_D=20A$	---	15.4	18	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1.0	---	3.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=100V$, $V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	19	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2.4	---	Ω
Q_g	Total Gate Charge	$I_D=30A$	---	28.2	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=50V$	---	6.5	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	4.5	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DS}=50V$ $V_{GS}=10V$ $R_{G_{ext}}=2.7\Omega$	---	30	---	ns
T_r	Rise Time		---	81	---	
$T_{d(off)}$	Turn-Off Delay Time		---	24	---	
T_f	Fall Time		---	7	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1000	---	pF
C_{oss}	Output Capacitance		---	510	---	
C_{rss}	Reverse Transfer Capacitance		---	34	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	58	A
I_{SM}	Pulsed Source Current		---	---	232	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=20A$, $T_J=25^{\circ}\text{C}$	---	0.88	1.2	V

Note :







1. The EAS data shows Max. rating . The test condition is $V_{DD}=50V$, $V_{GS}=10V$, $L=0.5\text{mH}$, $I_{AS}=13A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice. Please refer to the latest version of specification.


Typical Characteristics



Package Dimension

DFN-8 5x6

Unit :mm



注:

1. 未注公差±0.05未标注圆角R max=0.25

Dimensions In Millimeters			
Symbol	Min.	Max.	Ave.
A	0.900	1.100	1.000
D	4.950	5.150	5.050
D1	3.850	4.250	4.050
E	5.750	5.950	5.850
E1	5.950	6.350	6.150
E2	3.300	3.700	3.500
E3	0.900	1.300	1.100
b	0.250	0.350	0.300
e	1.220	1.320	1.270
L	0.585	0.785	0.685
L1	0.525	0.725	0.625
Ø	1.000	1.400	1.200
L2	0~0.100		
L3	0~0.100		