

CUC-HDMI-J1ST-AH/HAF-SMD - HDMI PCB connectors



1332071  
<https://www.phoenixcontact.com/us/products/1332071>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HDMI PCB connectors, design: HDMI A, degree of protection: IP20, number of positions: 19, 14 Gbps, material: Plastic, connection method: Solder connection, cable outlet: straight

Your advantages

- Optimized for SMD reflow soldering processes
- Reliable transmission of 4K videos
- Can be processed automatically thanks to tape-on-reel packaging

Commercial data

Item number	1332071
Packing unit	300 pc
Minimum order quantity	300 pc
Sales key	AB14
Product key	ABNEAA
GTIN	4063151628857
Weight per piece (including packing)	3.38 g
Weight per piece (excluding packing)	3.38 g
Customs tariff number	85366930
Country of origin	CN

# CUC-HDMI-J1ST-AH/HAF-SMD - HDMI PCB connectors



1332071

<https://www.phoenixcontact.com/us/products/1332071>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	HDMI
Number of positions	19
Type of packaging	Tape and Reel
[W] tape width	32.00 mm
[A] coil diameter	330.00 mm
Number of slots	1
Type	Socket
Shielded	yes
Cable outlet	straight

### Data management status

Article revision	00
------------------	----

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/2)	40 V
Rated surge voltage (III/2)	1500 V
Rated current	0.5 A (Contacts)
Insulation resistance	100 MΩ
Test voltage	300 V AC
Contact resistance	20 mΩ
Transmission medium	Copper
Transmission speed	14,4 GBit/s

### Connection data

#### Connection technology

Connection method	Solder connection
-------------------	-------------------

### Dimensions

Width	15 mm
Height	6.18 mm
Length	12.16 mm

### Material specifications

Color of the housing part	black
Material	Selective gold plating
	Nickel coating 50 µ min

# CUC-HDMI-J1ST-AH/HAF-SMD - HDMI PCB connectors



1332071

<https://www.phoenixcontact.com/us/products/1332071>

	Tin coating 100 µ min
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy
Contact surface material	Gold over nickel

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	10000
Insertion force per signal contact	44.00 N
Extraction force per signal contact	< 10 N

## Environmental and real-life conditions

### Test specification

Specification	EIA 364-1000
Contact resistance $R_1$	30.00 mΩ

### Test specification

Specification	EIA 364-28
Frequency	10Hz - 200Hz
Sweep speed	1 octave/min
Amplitude	1.52 mm
Acceleration	15.00 m/s <sup>2</sup>
Test duration	12.00 min.

### Test specification

Specification	EIA 364-27
Acceleration	50.00 m/s <sup>2</sup>
Number of shocks per direction	18.00

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 85 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C

## Mounting

Mounting type	SMD soldering
---------------	---------------

### Processing notes

Process	THR/SMD
Moisture Sensitive Level	MSL 1
Classification temperature $T_c$	260 °C
Solder cycles in the reflow	3

# CUC-HDMI-J1ST-AH/HAF-SMD - HDMI PCB connectors




1332071

<https://www.phoenixcontact.com/us/products/1332071>

## Drawings

Diagram



Classification reflow soldering profile

# CUC-HDMI-J1ST-AH/HAF-SMD - HDMI PCB connectors



1332071  
<https://www.phoenixcontact.com/us/products/1332071>

## Classifications

### ECLASS

ECLASS-11.0	27440390
ECLASS-12.0	27440390
ECLASS-13.0	27460201

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1332071  
<https://www.phoenixcontact.com/us/products/1332071>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)