

SMT & THROUGH-HOLE BOARD STACKERS

(2.00 mm) .0787" PITCH • TW SERIES

CLT or MMS	SQT
8	4
G b p s	G b p s



TW

Board Mates:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS

Cable Mates:

TCSD

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

Current Rating:

TW-SM = 4.9 A per pin
(2 pins powered)
TW-TH = 5.2 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold



PROCESSING



Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*
*(.004" stencil solution
may be available; contact
ipg@samtec.com)

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	SM	OTHER OPTION																				
	02 thru 36	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail -T = Matte Tin	-S = Single Row -D = Double Row	- "XXX" = Stacker Height in inches (0.13 mm) .005" increments Example: -250 = (6.35 mm) .250"		- "XXX" = Polarized Position -A = Alignment Pin (Metal or plastic at Samtec discretion) (4.83 mm) .190" min. board space (-D only) -P = Pick & Place Pad (1.91 mm) .075" min. post height (04-36 only) - "X"R Specify "T" for Tape & Reel Specify "F" for Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-07 lead style N/A) (-06 lead style with -P option N/A as standard)																				
		<table><tr><th>LEAD STYLE</th><th>OAL</th></tr><tr><td>-02</td><td>(7.85) .309</td></tr><tr><td>-03</td><td>(11.86) .467</td></tr><tr><td>-04</td><td>(12.37) .487</td></tr><tr><td>-06</td><td>(15.37) .605</td></tr><tr><td>-07</td><td>(17.35) .683</td></tr><tr><td>-09</td><td>(9.86) .388</td></tr></table>		LEAD STYLE	OAL	-02	(7.85) .309	-03	(11.86) .467	-04	(12.37) .487	-06	(15.37) .605	-07	(17.35) .683	-09	(9.86) .388	<table><tr><th>ROW OPTION</th><th>A</th></tr><tr><td>-S</td><td>(5.08) .200</td></tr><tr><td>-D</td><td>(6.35) .250</td></tr></table>		ROW OPTION	A	-S	(5.08) .200	-D	(6.35) .250		
LEAD STYLE	OAL																										
-02	(7.85) .309																										
-03	(11.86) .467																										
-04	(12.37) .487																										
-06	(15.37) .605																										
-07	(17.35) .683																										
-09	(9.86) .388																										
ROW OPTION	A																										
-S	(5.08) .200																										
-D	(6.35) .250																										

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	TAIL SPEC																										
	02 thru 50	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail -T = Matte Tin	-S = Single Row -D = Double Row -T = Triple Row -Q = Four Row -5 = Five Row -6 = Six Row	- "XXX" = Stacker Height in inches (0.13 mm) .005" increments Example: -250 = (6.35 mm) .250"	- "XXX" = Tail Length in inches (0.13 mm) .005" increments Example: -150 = (3.81 mm) .150" - "XXX" = Polarized Position (Specify position to be removed)																										
		<table><tr><th>LEAD STYLE</th><th>OAL</th></tr><tr><td>-01</td><td>(8.20) .323</td></tr><tr><td>-02</td><td>(9.60) .377</td></tr><tr><td>-03</td><td>(13.60) .535</td></tr><tr><td>-04</td><td>(14.10) .555</td></tr><tr><td>-05</td><td>(15.10) .594</td></tr><tr><td>-06</td><td>(17.10) .673</td></tr><tr><td>-07</td><td>(19.10) .751</td></tr><tr><td>-08*</td><td>(21.10) .830</td></tr><tr><td>-09</td><td>(11.60) .456</td></tr><tr><td>-10</td><td>(15.60) .614</td></tr><tr><td>-11</td><td>(10.08) .397</td></tr><tr><td>-12*</td><td>(28.19) 1.110</td></tr></table>					LEAD STYLE	OAL	-01	(8.20) .323	-02	(9.60) .377	-03	(13.60) .535	-04	(14.10) .555	-05	(15.10) .594	-06	(17.10) .673	-07	(19.10) .751	-08*	(21.10) .830	-09	(11.60) .456	-10	(15.60) .614	-11	(10.08) .397	-12*	(28.19) 1.110
LEAD STYLE	OAL																															
-01	(8.20) .323																															
-02	(9.60) .377																															
-03	(13.60) .535																															
-04	(14.10) .555																															
-05	(15.10) .594																															
-06	(17.10) .673																															
-07	(19.10) .751																															
-08*	(21.10) .830																															
-09	(11.60) .456																															
-10	(15.60) .614																															
-11	(10.08) .397																															
-12*	(28.19) 1.110																															
		<table><tr><th>ROW OPTION</th><th>STACKER HEIGHT</th></tr><tr><td>-S, -D*, -Q</td><td>(3.05) .120 MIN</td></tr><tr><td>-T, -5, -6</td><td>(4.06) .160 MIN</td></tr></table>					ROW OPTION	STACKER HEIGHT	-S, -D*, -Q	(3.05) .120 MIN	-T, -5, -6	(4.06) .160 MIN																				
ROW OPTION	STACKER HEIGHT																															
-S, -D*, -Q	(3.05) .120 MIN																															
-T, -5, -6	(4.06) .160 MIN																															
* -D with stacker height greater than (4.06 mm) .160" will not have standoffs.																																
* Style -08 & -12 = S & D only																																

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TW-03-04-G-D-360-SM-LC](#) [TW-13-06-G-S-170-SM](#) [TW-30-07-G-D-563-SM-P](#) [TW-22-04-T-D-235-SM-A-P](#) [TW-07-07-F-D-300-SM-A](#) [TW-14-07-G-D-580-SM](#) [TW-07-03-L-D-340-SM](#) [TW-25-07-L-D-500-SM-A](#) [TW-12-07-G-D-420-SM-A](#) [TW-10-07-T-D-525-SM-A](#) [TW-02-02-T-D-200-SM](#) [TW-10-02-L-D-225-SM-A](#) [TW-04-02-T-D-170-SM](#) [TW-02-02-S-S-200-SM](#) [TW-02-07-S-D-500-SM](#) [TW-08-02-T-D-170-SM](#) [TW-03-02-L-D-170-SM](#) [TW-20-07-L-D-500-SM](#) [TW-20-09-G-D-258-SM-A](#) [TW-20-07-L-D-500-SM-A](#) [TW-20-03-L-D-320-SM-A](#) [TW-08-02-L-D-226-SM-A-M-TR](#) [TW-16-06-G-D-470-SM](#) [TW-10-09-T-D-250-SM-A-P](#) [TW-08-09-L-D-210-SM-P-TR](#) [TW-15-06-L-D-250-SM](#) [TW-08-03-TM-D-290-SM-000](#) [TW-10-06-L-D-410-SM](#) [TW-15-02-T-D-190-SM-A](#) [TW-10-04-L-D-320-SM-A](#) [TW-15-03-L-D-170-SM](#) [TW-07-03-G-D-200-SM-A](#) [TW-15-03-L-D-320-SM-A](#) [TW-08-02-LM-D-226-SM-A-M-TR](#) [TW-14-06-L-D-409-SM](#) [TW-10-02-T-D-170-SM](#) [TW-07-09-L-D-260-SM-P-TR](#) [TW-10-04-S-D-360-SM](#) [TW-06-06-G-D-450-SM](#) [TW-08-03-G-D-330-SM-A](#) [TW-08-02-T-D-190-SM-000](#) [TW-08-02-T-D-240-SM-000](#) [TW-06-09-L-D-216-SM](#) [TW-08-02-TM-D-190-SM-000](#) [TW-20-07-S-D-500-SM-A](#) [TW-20-02-L-D-190-SM-A-P](#) [TW-05-07-T-D-550-SM-A](#) [TW-05-03-T-D-200-SM](#) [TW-05-04-L-D-330-SM-A](#) [TW-24-07-L-D-290-SM-A-P](#) [TW-28-09-T-D-200-SM-A](#) [TW-20-06-G-D-438-SM-A](#) [TW-22-06-G-D-450-SM](#) [TW-30-02-G-D-190-SM-A](#) [TW-06-02-T-D-170-SM](#) [TW-22-09-G-D-190-SM-A](#) [TW-04-09-T-D-240-SM-P-TR](#) [TW-20-07-S-D-385-SM-A-P](#) [TW-18-07-L-D-268-SM-A](#) [TW-03-03-L-D-170-SM](#) [TW-20-06-L-D-475-SM-A](#) [TW-18-07-G-D-376-SM-A](#) [TW-15-07-L-D-400-SM-A](#) [TW-05-03-L-D-170-SM](#) [TW-12-09-T-D-195-SM-P](#) [TW-14-02-L-D-300-SM](#) [TW-15-03-L-D-273-SM-A](#) [TW-10-09-G-D-258-SM-A](#) [TW-03-03-F-D-170-SM](#) [TW-03-07-L-S-535-SM](#) [TW-03-09-G-S-195-SM](#) [TW-04-04-L-D-240-SM-A](#) [TW-04-03-G-D-250-SM](#) [TW-04-04-L-S-340-SM](#) [TW-04-02-F-D-170-SM](#) [TW-05-02-L-D-215-SM-A-P](#) [TW-14-02-L-D-170-SM-P-TR](#) [TW-04-09-T-D-210-SM](#) [TW-15-03-G-D-340-SM-A](#) [TW-17-03-L-D-280-SM-A](#) [TW-32-09-L-D-294-SM-P](#) [TW-13-02-T-D-170-SM](#) [TW-03-06-H-D-400-SM-A](#) [TW-10-09-T-D-195-SM-P](#) [TW-06-02-F-D-170-SM](#) [TW-02-09-L-S-220-SM](#) [TW-02-02-L-D-190-SM-A](#) [TW-03-06-L-D-480-SM](#) [TW-02-06-G-D-325-SM-A](#) [TW-05-04-L-D-320-SM-P-TR](#) [TW-10-02-F-D-170-SM](#) [TW-06-07-L-D-560-SM-A](#) [TW-12-06-L-D-475-SM](#) [TW-10-03-G-D-330-SM-A](#) [TW-06-07-F-D-250-SM-A](#) [TW-03-06-L-D-190-SM-A](#) [TW-04-02-T-S-170-SM](#) [TW-06-06-H-D-400-SM-A-P-TR](#) [TW-12-04-G-D-340-SM-A-P-TR](#) [TW-06-03-F-D-200-SM-P](#)