

# WRSP Series Weatherproof Single-pole Rocker Switches

**Approvals**

UL recognized. CSA and VDE approvals pending.  
Load rating: 20A 125/250 VAC. 3/4 HP, 125/250 VAC. 14A 14VDC. Contacts: fine silver for long life dependability.  
Dielectric strength: 1250 volts (live parts to ground).  
Life: 35,000 operations at maximum rating.  
Insulation resistance: 5 megohms.

**Water & Dust Resistance**

Designed to meet IP-64.

**High Inrush**

125 Amp inrush capability (AgNi contacts).

**Low Level Control**

For low level/dry circuit applications (<100 am) contact factory for part number.

**Terminals**

Style A - 1/4-inch quick-connect

**Mechanical Features**

100,000 mechanical operations



**Markings**

Letters, numbers and symbols can be applied to rocker actuator or to integral nylon bezel; see inside back cover for details.

**Mounting**

Snap-in type panel mounting for ease of installation without additional mounting hardware.

Circuit	Switching			
1	SPST Maintained			
2	SPDT Maintained			
3	SPDT Maintained Center Off			
4	SPST (Momentary) Normally Open			
5	SPDT (Momentary) Normally Closed			
6	SPDT (Momentary) Transfer			
7	SPDT Maintained Center Off (Momentary)			
8	SPDT (Momentary) Center Off (Momentary)			



**Ordering Information:**

**WRSP**



**Circuit**

- 1=SPST Maintained
- 2=SPDT Maintained
- 3=SPDT Maintained Center Off
- 4=SPST (Momentary) Normally Open
- 5=SPST (Momentary) Normally Closed
- 6=SPDT (Momentary) Transfer
- 7=SPDT Maintained Center Off (Momentary)
- 8=SPDT (Momentary) Center Off (Momentary)



**Terminal Option**

- A=Fine Silver (Normal Duty)
- G=Gold Plated Contacts
- H=High Inrush Contacts



**Actuator Color**

- 7=White
- 9=Black
- 11=Green (non-stock)
- 12=Red



**Housing Color**

- M9=Matte Black
- (For other colors contact factory)



**Accessories (Optional)**

- T=Boot
- E=Epoxy Seal
- G=Panel Gasket



Phone (203) 272-2794 • Fax (203) 272-3492 • <http://www.osloswitch.com>

MADE IN U.S.A.



Phone (203) 272-2794 • Fax (203) 272-3492 • <http://www.osloswitch.com>

MADE IN U.S.A.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## CW Industries:

[WRSP1A9M9](#) [WRSP3A9M9-G](#) [WRSP1A9M9-G](#) [WRSP1G9M9](#) [WRSP3A9M9-E](#) [WRSP6A9M9E](#) [WRSP3H9M9](#)  
[WRSP1A9M9-E](#) [WRSP1H9M9](#) [WRSP4A9M9](#) [WRSP1A9M9-WL](#) [WRSP2A9M9](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## CW Industries:

[WRSP1A9M9](#) [WRSP1A9M9-E](#) [WRSP1A9M9-G](#) [WRSP1G9M9](#) [WRSP1H9M9](#) [WRSP2A9M9](#) [WRSP3A9M9-E](#)  
[WRSP3A9M9-G](#) [WRSP3H9M9](#) [WRSP4A9M9](#) [WRSP1A9M9-WL](#) [WRSP6A9M9E](#)