

MS27470 Jam Nut Mount Hermetic Receptacle MIL-DTL-38999 Series I

How To Order: MS

Shell Style

MS27470 - Jam Nut Mount, Series I

Connector Material / Finish

D - Carbon Steel - Fused Tin Finish
E - Stainless Steel - Passivate Finish
N - Stainless Steel - Nickel Finish

Contact Termination

P - Pin, Solder Cup S - Socket, Solder Cup
X - Pin, Eyelet Z - Socket, Eyelet
C - Pin, PCB D - Socket, PCB
Flex Feedthrough Flex Feedthrough

Class
Y - Hermetic

MS27470

Y

11

N

35

P




A

Shell Size

9, 11, 13, 15, 17, 19, 21, 23, 25

Insert Arrangement
MIL-DTL-38999 Series I
Hermetic Inserts Per
MIL-STD-1560;
See Pages B-2 - B-4

Alternate Key
Position
A, B, C, D
(Omit for Normal)



MS27470

Jam Nut Mount Hermetic Receptacle

MIL-DTL-38999 Series I



D38999 QPL
Hermetics

How To Order: Commercial

Connector Series 231 - Series I Type	Shell Style H7 - Hermetic Jam Nut Mount	Shell Size 09, 11, 13, 15, 17, 19, 21, 23, 25	Contact Termination P - Pin, Solder Cup S - Socket, Solder Cup X - Pin, Eyelet Z - Socket, Eyelet C - Pin, PCB D - Socket, PCB	
231	- 100	- H7	Z1	11 - 35
Connector Type 100 - Hermetic Receptacle	Connector Material / Finish ZL - CRES, Nickel Z1 - CRES, Passivated FT - Carbon Steel, Fused Tin	Insert Arrangement Per MIL-STD-1560; See Pages B-2 - B-4	Alternate Key Position A, B, C, D, (N = Normal)	
			P	N

B

TABLE I: CONNECTOR DIMENSIONS

SHELL SIZE	A THREAD CLASS 2A	B DIA ±.016(0.4)	C ±.016(0.4)	D FLAT ±.005(0.1)	E DIA ±.011(0.3)	F DIA ±.005(0.1)
9/09	.6875-24 UNEF	1.188(30.2)	1.062(27.0)	.65(16.5)	.602(15.3)	.648(16.5)
11	.8125-20 UNEF	1.375(34.9)	1.25(31.8)	.75(19.1)	.726(18.4)	.772(19.6)
13	1.000-20 UNEF	1.5(38.1)	1.375(34.9)	.937(23.8)	.852(21.6)	.898(22.8)
15	1.125-18 UNEF	1.625(41.3)	1.5(38.1)	1.061(26.9)	.978(24.8)	1.024(26.0)
17	1.250-18 UNEF	1.75(44.5)	1.625(41.3)	1.186(30.1)	1.102(28.0)	1.148(29.2)
19	1.375-18 UNEF	1.938(49.2)	1.812(46.0)	1.311(33.3)	1.228(31.2)	1.274(32.4)
21	1.500-18 UNEF	2.062(52.4)	1.938(49.2)	1.436(36.5)	1.352(34.3)	1.398(35.5)
23	1.625-18 UNEF	2.188(55.6)	2.062(52.4)	1.561(39.6)	1.478(37.5)	1.524(38.7)
25	1.750-18 UNS	2.312(58.7)	2.188(55.6)	1.686(42.8)	1.602(40.7)	1.648(41.9)

TABLE I (CONTINUED): CONNECTOR DIMENSIONS


SHELL SIZE	G ±.016(0.4)	K DIA ±.005(0.1)	L MAX	M MAX	N ±.005(0.1)
9/09	.109(2.8)	.705(17.9)	1.200(30.5)	.280(7.1)	.665(16.9)
11	.109(2.8)	.827(21.0)	1.200(30.5)	.280(7.1)	.764(19.4)
13	.109(2.8)	1.012(25.7)	1.200(30.5)	.280(7.1)	.95(24.1)
15	.109(2.8)	1.139(28.9)	1.200(30.5)	.280(7.1)	1.079(27.4)
17	.109(2.8)	1.264(32.1)	1.200(30.5)	.280(7.1)	1.203(30.6)
19	.14(3.6)	1.389(35.3)	1.231(31.3)	.311(7.9)	1.328(33.7)
21	.14(3.6)	1.512(38.4)	1.231(31.3)	.311(7.9)	1.454(36.9)
23	.14(3.6)	1.639(41.6)	1.231(31.3)	.311(7.9)	1.579(40.1)
25	.14(3.6)	1.764(44.8)	1.231(31.3)	.311(7.9)	1.704(43.3)

TABLE II: CONTACT SIZE

PRINTED CIRCUIT TAIL CONFIGURATIONS
CONTACT STYLE C AND D



SIZE 12 AND SIZE 16



SIZE 22D AND SIZE 20

Contact Size	ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[MS27470Y11N35P](#) [MS27470Y13E35P](#) [MS27470Y15E97P](#) [MS27470Y11D98P](#) [231-100-H7FT09-35PN](#) [231-100-H7FT11-04PN](#) [231-100-H7FT11-05PN](#) [231-100-H7FT11-35PA](#) [231-100-H7FT11-35PN](#) [231-100-H7FT11-98PN](#) [231-100-H7FT13-35PN](#) [231-100-H7FT15-05PN](#) [231-100-H7FT15-18PN](#) [231-100-H7FT15-35PN](#) [231-100-H7FT15-97PN](#) [231-100-H7FT17-35PN](#) [231-100-H7FT17-99PN](#) [231-100-H7FT19-32PN](#) [231-100-H7FT19-35PA](#) [231-100-H7FT25-04PN](#) [231-100-H7FT25-35PB](#) [231-100-H7Z109-98PN](#) [231-100-H7Z111-05PN](#) [231-100-H7Z113-04PN](#) [231-100-H7Z113-08PN](#) [231-100-H7Z115-15PN](#) [231-100-H7Z115-18PN](#) [231-100-H7Z115-35PA](#) [231-100-H7Z115-35PC](#) [231-100-H7Z115-97PN](#) [231-100-H7Z117-06PN](#) [231-100-H7Z117-99PA](#) [231-100-H7Z117-99PN](#) [231-100-H7Z119-11PN](#) [231-100-H7Z119-35PA](#) [231-100-H7Z119-35PB](#) [231-100-H7Z119-35SB](#) [231-100-H7Z119-35SN](#) [231-100-H7Z121-11PN](#) [231-100-H7Z121-24PN](#) [231-100-H7Z121-35PA](#) [231-100-H7Z121-35PN](#) [231-100-H7Z123-21PA](#) [231-100-H7Z123-21PN](#) [231-100-H7Z123-35PA](#) [231-100-H7Z123-35PB](#) [231-100-H7Z123-35PC](#) [231-100-H7Z123-35PN](#) [231-100-H7Z123-55PN](#) [231-100-H7Z125-35PN](#) [231-100-H7ZL11-35PN](#) [231-100-H7ZL15-18PN](#) [231-100-H7ZL15-35CN](#) [231-100-H7ZL15-35PA](#) [231-100-H7ZL15-35PC](#) [231-100-H7ZL15-35PN](#) [231-100-H7ZL15-35SA](#) [231-100-H7ZL17-26CN](#) [231-100-H7ZL17-35CN](#) [231-100-H7ZL17-35PN](#) [231-100-H7ZL19-32SN](#) [231-100-H7ZL19-35PN](#) [231-100-H7ZL19-35SB](#) [231-100-H7ZL19-35SN](#) [231-100-H7ZL21-41PN](#) [231-100-H7ZL23-35PA](#) [231-100-H7ZL23-35PB](#) [231-100-H7ZL23-35PN](#) [231-100-H7ZL23-35SB](#) [231-100-H7ZL23-35SC](#) [231-100-H7ZL23-35SN](#) [231-100-H7ZL23-36PC](#) [MS27470Y17E35P](#) [MS27470Y15N35P](#) [MS27470Y15N35PC](#) [MS27470Y17N35P](#) [MS27470Y11E5P](#) [MS27470Y13D35P](#) [MS27470Y15D18P](#) [MS27470Y15E15P](#) [MS27470Y15E35PC](#) [MS27470Y15N18P](#) [MS27470Y15N35PA](#) [MS27470Y19D35PA](#) [MS27470Y19E35PA](#) [MS27470Y19E35PB](#) [MS27470Y19E35S](#) [MS27470Y19E35SB](#) [MS27470Y19N32S](#) [MS27470Y19N35S](#) [MS27470Y19N35SB](#) [MS27470Y21E35P](#) [MS27470Y23E21PA](#) [MS27470Y23E35PB](#) [MS27470Y23E35PC](#) [MS27470Y23E55P](#) [MS27470Y23N35P](#) [MS27470Y23N35PA](#) [MS27470Y23N35PB](#) [MS27470Y23N35S](#)