


THROUGH-HOLE MICRO HEADER

(1.27 mm) .050" PITCH • TMS/HTMS SERIES



TMS/HTMS

Mates:
SMS, SLM, RSM

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Current Rating (TMS/SMS):

5 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:

Yes

SERIES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION
--------	---	------------------	------------	----------------	------------	--------

TMS
= Standard

01 thru 50

Specify
**LEAD
STYLE**
from
chart

-L
= 10 μ"
(0.25 μm)
Gold on post,
Matte Tin
on tail

-S
= Single
Row

-RA
= Right-
angle





HTMS
= High Temp

-D
= Double
Row

-"XXX"
= Polarized
Position
(Specify position
of omitted pin)

-G
= 10 μ"
(0.25 μm)
Gold on post,
Gold flash
on tail

T/H LEAD STYLE	A	B	C
-01	(11.43) .450	(5.84) .230	(3.05) .120
-02	(8.13) .320	(2.54) .100	
-21	(12.83) .505	(5.84) .230	(4.45) .175
-51	(10.41) .410	(4.83) .190	
-52	(10.80) .425	(5.21) .205	
-53	(12.83) .505	(7.24) .285	
-54	(14.10) .555	(8.51) .335	
-55	(15.49) .610	(9.91) .390	(3.05) .120
-56	(15.88) .625	(10.29) .405	
-57	(16.51) .650	(10.92) .430	
-58	(17.91) .705	(12.32) .485	
-59	(19.18) .755	(13.59) .535	
-60	(20.96) .825	(15.37) .605	



**HTMS
-D
BODY
DESIGN**



ALSO AVAILABLE
MOQ Required

Other Plating

Important Note:

Style -02 does not mate
with SMS Series.

RA LEAD STYLE	D
-01	(5.84) .230
-02	(2.54) .100
-03	(3.18) .125



Note:

Some lengths, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HTMS-112-01-S-S](#) [HTMS-102-21-G-S](#) [HTMS-105-01-S-S](#) [HTMS-103-53-S-S](#) [HTMS-107-01-G-D-006](#) [HTMS-104-02-T-S](#) [HTMS-150-01-G-S](#) [HTMS-105-02-L-D](#) [HTMS-108-02-L-S](#) [HTMS-140-02-S-D](#) [HTMS-108-01-G-S](#) [HTMS-110-01-G-D](#) [HTMS-116-57-L-S](#) [HTMS-118-02-S-S-RA](#) [HTMS-103-03-G-S-RA](#) [HTMS-104-02-L-S](#) [HTMS-110-01-G-S](#) [HTMS-112-02-G-S](#) [HTMS-103-02-G-S](#) [HTMS-104-02-G-S-RA](#) [HTMS-105-02-G-S-RA](#) [HTMS-101-02-G-D](#) [HTMS-102-02-G-S](#) [HTMS-104-01-L-S](#) [HTMS-108-60-G-D](#) [HTMS-108-01-L-S](#) [HTMS-105-02-S-S](#) [HTMS-105-01-G-D-RA](#) [HTMS-104-02-G-S](#) [HTMS-106-52-G-S](#) [HTMS-111-02-G-S](#) [HTMS-106-03-T-S-RA](#) [HTMS-103-02-T-S](#) [HTMS-110-01-S-S](#) [HTMS-120-01-G-D](#) [HTMS-110-02-S-S](#) [HTMS-120-52-G-S](#) [HTMS-105-51-L-D](#) [HTMS-107-03-S-S-RA](#) [HTMS-110-03-G-S-RA](#) [HTMS-103-02-S-D](#) [HTMS-108-53-G-D](#) [HTMS-103-60-G-D](#) [HTMS-105-01-L-S](#) [HTMS-106-01-G-S](#) [HTMS-105-02-G-D-RA](#) [HTMS-150-01-S-S](#) [HTMS-101-02-G-D-RA](#) [HTMS-103-01-G-S](#) [HTMS-119-02-S-S](#) [HTMS-120-51-L-D](#) [HTMS-104-01-S-S-RA](#) [HTMS-117-51-T-D-SM-P](#) [HTMS-106-02-G-D-RA](#) [HTMS-120-02-G-S-RA](#) [HTMS-102-03-S-D-EM](#) [HTMS-105-01-G-S](#) [HTMS-110-02-L-D-RA](#) [HTMS-125-01-G-D](#) [HTMS-105-03-G-D-RA](#) [HTMS-110-02-G-S](#) [HTMS-108-01-S-S](#) [HTMS-111-02-G-S-RA](#) [HTMS-104-03-G-S-RA](#) [HTMS-150-03-S-D-RA](#) [HTMS-113-53-G-D](#) [HTMS-104-02-G-D-RA](#) [HTMS-102-02-G-D-RA](#) [HTMS-120-53-G-D](#) [HTMS-128-01-L-D-RA](#) [HTMS-113-02-G-D-EM](#) [HTMS-108-01-G-S-RA](#) [HTMS-105-01-G-S-RA](#) [HTMS-110-01-S-D-RA](#) [HTMS-104-01-G-S](#) [HTMS-104-01-S-D-006](#) [HTMS-118-01-L-S-RA](#) [HTMS-104-02-S-S](#) [HTMS-140-03-S-D-RA](#) [HTMS-106-01-G-S-RA](#) [HTMS-110-51-S-S](#) [HTMS-105-52-T-S](#) [HTMS-101-21-G-S](#) [HTMS-117-01-L-S](#) [HTMS-125-01-S-S](#) [HTMS-120-01-L-D-RA](#) [HTMS-101-01-G-S](#) [HTMS-150-02-S-D](#) [HTMS-106-02-L-S-RA](#) [HTMS-116-01-S-S](#) [HTMS-102-01-G-S-RA](#) [HTMS-106-02-G-S](#) [HTMS-108-57-G-S](#) [HTMS-102-01-G-S](#) [HTMS-107-51-G-S](#) [HTMS-105-02-G-S](#) [HTMS-150-01-S-S-RA](#) [HTMS-110-03-S-S-RA](#) [HTMS-125-02-S-D](#) [HTMS-103-02-S-S](#)