


1. SPECIFICATIONS:
WIRE: (2) #20 AWG RESISTOR
LEADS .031" Ø(0.812 mm)
2. POCKET RECOMMENDATION:
#1601424
- 3





 TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPECIFICATION 114-13166.
CONSULT TYCO ELECTRONICS ENGINEERING
FOR THE PROPER INSERTION DEPTH.
- 4

 TIP MAY BE RADIUSED WITHIN
DIMENSIONS SHOWN AND HAVE
CONVEX SIDES.
- 5

 PRELIMINARY - NOT FOR PRODUCTION



SECTION A-A
20 X SCALE



OBSELETE

-	-	-
-	-	-
PRE-TIN PLATE OVER NICKEL UNDERPLATE	-	5 1601144-4
SELECTIVE POST TIN PLATE OVER NICKEL UNDERPLATE	159-003-120	1601144-3
POST TIN-LEAD PLATE OVER NICKEL UNDERPLATE	159-003-118	1601144-2
UNPLATED	159-003-000	1601144-1
FINISH	REFERENCE PART NUMBER	TYCO PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002 PRODUCT SPEC APPLICATION SPEC 3	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.13] 3 PLC ± .005[.026] 4 PLC ± - ANGLES ± 2° FINISH SEE TABLE	NAME MULTIPLE WIRE I.D.C.TO OFFSET SQUARE PIN SIAMEZE TERMINAL
MATERIAL BRASS, 3/4 HARD	WEIGHT -	SIZE A2 CAGE CODE 00779 DRAWING NO C=1601144 RESTRICTED TO -
CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 1 REV B2