







RH WALL PLATE

Relative Humidity, Wall Plate

The ACI Relative Humidity Stainless Plate utilizes a thermoset polymer capacitive sensing element with a factory applied hygroscopic filter to deliver a proportional analog voltage output signal. The hygroscopic filter provides added resistance to moisture, dust, and other chemicals for greater long term reliability. The RH Stainless Plate transmitter features integral DIP switches for field selection of the proper output signal and supply voltage to meet your applications requirements. Each unit also contains 0%, 50%, and 100% test options to verify that the transmitter is both working and properly installed. Field calibration can be performed by using the increment and decrement calibration DIP switches without the need to replace the sensing element. These enhancements provide increased flexibility and outstanding long-term reliability. All RH Stainless Plate transmitters come standard

with an attractive brushed finish stainless steel, single gang wall mounting plate and are designed to mount over a single gang junction box in the wall. The PCBs are conformally coated for added protection from moisture and other contaminants. A temporary plastic sensor cover is included to provide protection for the RH sensor from chemicals used in wash down applications. Three point NIST Calibration Certificates are

Applications: Pharmaceutical, Hospitals, Operating Rooms, Vivariums, Clean Rooms, Process Control, Wash Down Environments & Stability Chambers


The ACI RH Wall Plate is covered by ACI's Five (5) Year Limited Warranty. The warranty can be found in the front of ACI's Sensors & Transmitters catalog, as well as on ACI's website, workaci.com.

PRODUCT SPECIFICATIONS		
RH Supply Voltage (Reverse Polarity Protected):	0-5 VDC: 12 - 40 VDC / 18 - 28 VAC 0-10 VDC: 18 - 40 VDC / 18 - 28 VAC	
RH Supply Current (VA):	8 mA maximum (0.32 VA)	
RH Output Load Resistance:	4K Ohms Minimum	
RH Output Signal:	3-wire: 0-5 or 0-10 VDC	
RH Accuracy @ 77°F (25°C):	+/- 2% or 3% from 10 to 95%	
RH Measurement Range:	0-100%	
Operating RH Range:	0 to 95% RH, non-condensing (Conformally Coated PCB's)	
Operating Temperature Range:	-40 to 140°F (-40 to 60°C)	
Storage Temperature Range:	-40 to 149°F (-40 to 65°C)	
RH Stability Repeatability Sensitivity:	Less than 2% drift / 5 years 0.5% RH 0.1% RH	
RH Response Time (T63):	20 Seconds Typical	
RH Sensor Type:	Capacitive with Hydrophobic Filter	
RH Transmitter Stabilization Time:	30 Minutes (Recommended time before doing accuracy verification)	
RH Connections Wire Size:	Screw Terminal Blocks (Polarity Sensitive) 16 (1.31 mm²) to 26 AWG (0.129 mm²)	
RH Terminal Block Torque Rating:	4.43 to 5.31 lb-in (0.5 to 0.6 Nm)	
RH NIST Test Points:	Default Test Points: 3 Points (20%, 50% & 80%)	
Wall Plate Material:	430 Stainless Steel (Brushed Stainless Steel Finish)	
Foam Material Foam Thickness:	Cross-linked LPDE (White) 0.25" (6.35 mm)	
Foam Flammability Rating:	FMVSS-302	
Sintered Filter Material:	304 Series Stainless Steel	
Product Dimensions (L x W x D):	4.51" (114.56 mm) x 2.76" (70.10 mm) x 1.25" (31.75 mm)	
Product Weight:	0.235 lbs. (0.107 kg)	
Agency Approvals:	CE, UKCA, RoHS, WEEE	









STANDARD ORDERING				
Model #	Item#	Description		
A/RH2-SP-05	138922	RH Stainless Plate, +/- 2%, 0-5 VDC Output (default), 0-10 VDC (selectable)		
A/RH2-SP-05-NIST	148201	RH Stainless Plate, +/- 2%, 0-5 VDC Output (default), 0-10 VDC (selectable), NIST Certificate		
A/RH2-SP-010	137895	RH Stainless Plate, +/- 2%, 0-10 VDC Output (default), 0-5 VDC (selectable)		
A/RH2-SP-010-NIST	148202	RH Stainless Plate, +/- 2%, 0-10 VDC Output (default), 0-5 VDC (selectable), NIST Certificate		
A/RH3-SP-05	132739	RH Stainless Plate, +/- 3%, 0-5 VDC Output (default), 0-10 VDC (selectable)		
A/RH3-SP-05-NIST	148203	RH Stainless Plate, +/- 3%, 0-5 VDC Output (default), 0-10 VDC (selectable), NIST Certificate		
A/RH3-SP-010	138166	RH Stainless Plate, +/- 3%, 0-10 VDC Output (default), 0-5 VDC (selectable)		
A/RH3-SP-010-NIST	148204	RH Stainless Plate, +/- 3%, 0-10 VDC Output (default), 0-5 VDC (selectable), NIST Certificate		

CUSTOM ORDERING	Model#Example: A/ RH2 SP 010 A. B. C. D.	MODEL #
A. Sensor Series No Selection Required	A/ —	A/
B. Accuracy Select One (1)	RH2 = +/-2% RH3 = +/-3%	
C. Configuration No Selection Required	SP = Stainless Plate	SP
D. Output Signal Select One (1)	010 = 0 to 10 VDC 05 = 0 to 5 VDC	

Note*: Outputs are field selectable between 0-5 VDC & 0-10 VDC

ACCESSORIES ORDERING		Model # Example: A/SINTERED FILTER -OR- 143433
Model #	Item #	Description
A/SINTERED FILTER	143433	3/8" Sintered Filter for RH Duct/Stainless Plate/Remote Probes
A/1"VINYL PULL CAP	143462	1" EZ Vinyl Filter Cover for RH Stainless Plates & Remote Probes





