

Part Number : 2025693002

Product Description : MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 28-26 AWG

Series Number : 202935

Status : Active

Product Category : Crimp Terminals

Engineering Number : 2029354000-FCT



---

## Documents & Resources

### Drawings

[2029354000\\_sd.pdf](#)

[2029350000-PK-000.pdf](#)

---

### Specifications

[2059250000-AS-000.pdf](#)

[2059250000-PS-000.pdf](#)

[2059250000-TS-000.pdf](#)

---

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

---

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### **Part Details**

#### **General**

Status	Active
Category	Crimp Terminals
Series	202935
Description	MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 28-26 AWG
Application	Power, Wire-to-Wire
Product Name	MultiCat
UPC	193264027019

#### **Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V AC/DC

#### **Physical**

Durability (mating cycles max)	500
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.200/g
Packaging Type	Bag
Plating min - Mating	1.300µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.10mm
Wire Size (AWG)	26, 28

Wire Size mm <sup>2</sup>	N/A
---------------------------	-----

---

### Use with Part(s)

Description	Part Number
MultiCat Mid-Power Plug Housings	<u>205925</u>

---

This document was generated on Oct 14, 2024