


	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																														
F											F																																																																																																																																																																																													
E											E																																																																																																																																																																																													
D											D																																																																																																																																																																																													
C											C																																																																																																																																																																																													
B											B																																																																																																																																																																																													
A											A																																																																																																																																																																																													
<table><tr><td rowspan="2">NO. OF CIRC. "XX"</td><td colspan="2">DIM. "A"</td><td colspan="2">DIM. "B"</td><td colspan="2">"C" $\begin{matrix} +.00 \\ -.25 \end{matrix} \left[\begin{matrix} +.000 \\ -.010 \end{matrix} \right]$</td><td rowspan="2">MATERIAL NO. (STANDARD)</td></tr><tr><td>MM</td><td>IN</td><td>MM</td><td>IN</td><td>MM</td><td>IN</td></tr><tr><td>03</td><td>20.3</td><td>[.80]</td><td>10.16</td><td>[.400]</td><td>15.2</td><td>[.60]</td><td>399400303</td></tr><tr><td>04</td><td>25.4</td><td>[1.00]</td><td>15.24</td><td>[.600]</td><td>20.3</td><td>[.80]</td><td>399400304</td></tr><tr><td>05</td><td>30.5</td><td>[1.20]</td><td>20.32</td><td>[.800]</td><td>25.4</td><td>[1.00]</td><td>399400305</td></tr><tr><td>06</td><td>35.6</td><td>[1.40]</td><td>25.40</td><td>[1.000]</td><td>30.5</td><td>[1.20]</td><td>399400306</td></tr><tr><td>07</td><td>40.6</td><td>[1.60]</td><td>30.48</td><td>[1.200]</td><td>35.6</td><td>[1.40]</td><td>399400307</td></tr><tr><td>08</td><td>45.7</td><td>[1.80]</td><td>35.56</td><td>[1.400]</td><td>40.6</td><td>[1.60]</td><td>399400308</td></tr><tr><td>09</td><td>50.8</td><td>[2.00]</td><td>40.64</td><td>[1.600]</td><td>45.7</td><td>[1.80]</td><td>399400309</td></tr><tr><td>10</td><td>55.9</td><td>[2.20]</td><td>45.72</td><td>[1.800]</td><td>50.8</td><td>[2.00]</td><td>399400310</td></tr><tr><td>11</td><td>61.0</td><td>[2.40]</td><td>50.80</td><td>[2.000]</td><td>55.9</td><td>[2.20]</td><td>399400311</td></tr><tr><td>12</td><td>66.0</td><td>[2.60]</td><td>55.88</td><td>[2.200]</td><td>61.0</td><td>[2.40]</td><td>399400312</td></tr><tr><td>13</td><td>71.1</td><td>[2.80]</td><td>60.96</td><td>[2.400]</td><td>66.0</td><td>[2.60]</td><td>399400313</td></tr><tr><td>14</td><td>76.2</td><td>[3.00]</td><td>66.04</td><td>[2.600]</td><td>71.1</td><td>[2.80]</td><td>399400314</td></tr><tr><td>15</td><td>81.3</td><td>[3.20]</td><td>71.12</td><td>[2.800]</td><td>76.2</td><td>[3.00]</td><td>399400315</td></tr><tr><td>16</td><td>86.4</td><td>[3.40]</td><td>76.20</td><td>[3.000]</td><td>81.3</td><td>[3.20]</td><td>399400316</td></tr><tr><td>17</td><td>91.4</td><td>[3.60]</td><td>81.28</td><td>[3.200]</td><td>86.4</td><td>[3.40]</td><td>399400317</td></tr><tr><td>18</td><td>96.5</td><td>[3.80]</td><td>86.36</td><td>[3.400]</td><td>91.4</td><td>[3.60]</td><td>399400318</td></tr><tr><td>19</td><td>101.6</td><td>[4.00]</td><td>91.44</td><td>[3.600]</td><td>96.5</td><td>[3.80]</td><td>399400319</td></tr><tr><td>20</td><td>106.7</td><td>[4.20]</td><td>96.52</td><td>[3.800]</td><td>101.6</td><td>[4.00]</td><td>399400320</td></tr><tr><td>21</td><td>111.8</td><td>[4.40]</td><td>101.60</td><td>[4.000]</td><td>106.7</td><td>[4.20]</td><td>399400321</td></tr><tr><td>22</td><td>116.8</td><td>[4.60]</td><td>106.68</td><td>[4.200]</td><td>111.8</td><td>[4.40]</td><td>399400322</td></tr><tr><td>23</td><td>121.9</td><td>[4.80]</td><td>111.76</td><td>[4.400]</td><td>116.8</td><td>[4.60]</td><td>399400323</td></tr><tr><td>24</td><td>127.0</td><td>[5.00]</td><td>116.84</td><td>[4.600]</td><td>121.9</td><td>[4.80]</td><td>399400324</td></tr></table>											NO. OF CIRC. "XX"	DIM. "A"		DIM. "B"		"C" $\begin{matrix} +.00 \\ -.25 \end{matrix} \left[\begin{matrix} +.000 \\ -.010 \end{matrix} \right]$		MATERIAL NO. (STANDARD)	MM	IN	MM	IN	MM	IN	03	20.3	[.80]	10.16	[.400]	15.2	[.60]	399400303	04	25.4	[1.00]	15.24	[.600]	20.3	[.80]	399400304	05	30.5	[1.20]	20.32	[.800]	25.4	[1.00]	399400305	06	35.6	[1.40]	25.40	[1.000]	30.5	[1.20]	399400306	07	40.6	[1.60]	30.48	[1.200]	35.6	[1.40]	399400307	08	45.7	[1.80]	35.56	[1.400]	40.6	[1.60]	399400308	09	50.8	[2.00]	40.64	[1.600]	45.7	[1.80]	399400309	10	55.9	[2.20]	45.72	[1.800]	50.8	[2.00]	399400310	11	61.0	[2.40]	50.80	[2.000]	55.9	[2.20]	399400311	12	66.0	[2.60]	55.88	[2.200]	61.0	[2.40]	399400312	13	71.1	[2.80]	60.96	[2.400]	66.0	[2.60]	399400313	14	76.2	[3.00]	66.04	[2.600]	71.1	[2.80]	399400314	15	81.3	[3.20]	71.12	[2.800]	76.2	[3.00]	399400315	16	86.4	[3.40]	76.20	[3.000]	81.3	[3.20]	399400316	17	91.4	[3.60]	81.28	[3.200]	86.4	[3.40]	399400317	18	96.5	[3.80]	86.36	[3.400]	91.4	[3.60]	399400318	19	101.6	[4.00]	91.44	[3.600]	96.5	[3.80]	399400319	20	106.7	[4.20]	96.52	[3.800]	101.6	[4.00]	399400320	21	111.8	[4.40]	101.60	[4.000]	106.7	[4.20]	399400321	22	116.8	[4.60]	106.68	[4.200]	111.8	[4.40]	399400322	23	121.9	[4.80]	111.76	[4.400]	116.8	[4.60]	399400323	24	127.0	[5.00]	116.84	[4.600]	121.9	[4.80]	399400324
NO. OF CIRC. "XX"	DIM. "A"		DIM. "B"		"C" $\begin{matrix} +.00 \\ -.25 \end{matrix} \left[\begin{matrix} +.000 \\ -.010 \end{matrix} \right]$		MATERIAL NO. (STANDARD)																																																																																																																																																																																																	
	MM	IN	MM	IN	MM	IN																																																																																																																																																																																																		
03	20.3	[.80]	10.16	[.400]	15.2	[.60]	399400303																																																																																																																																																																																																	
04	25.4	[1.00]	15.24	[.600]	20.3	[.80]	399400304																																																																																																																																																																																																	
05	30.5	[1.20]	20.32	[.800]	25.4	[1.00]	399400305																																																																																																																																																																																																	
06	35.6	[1.40]	25.40	[1.000]	30.5	[1.20]	399400306																																																																																																																																																																																																	
07	40.6	[1.60]	30.48	[1.200]	35.6	[1.40]	399400307																																																																																																																																																																																																	
08	45.7	[1.80]	35.56	[1.400]	40.6	[1.60]	399400308																																																																																																																																																																																																	
09	50.8	[2.00]	40.64	[1.600]	45.7	[1.80]	399400309																																																																																																																																																																																																	
10	55.9	[2.20]	45.72	[1.800]	50.8	[2.00]	399400310																																																																																																																																																																																																	
11	61.0	[2.40]	50.80	[2.000]	55.9	[2.20]	399400311																																																																																																																																																																																																	
12	66.0	[2.60]	55.88	[2.200]	61.0	[2.40]	399400312																																																																																																																																																																																																	
13	71.1	[2.80]	60.96	[2.400]	66.0	[2.60]	399400313																																																																																																																																																																																																	
14	76.2	[3.00]	66.04	[2.600]	71.1	[2.80]	399400314																																																																																																																																																																																																	
15	81.3	[3.20]	71.12	[2.800]	76.2	[3.00]	399400315																																																																																																																																																																																																	
16	86.4	[3.40]	76.20	[3.000]	81.3	[3.20]	399400316																																																																																																																																																																																																	
17	91.4	[3.60]	81.28	[3.200]	86.4	[3.40]	399400317																																																																																																																																																																																																	
18	96.5	[3.80]	86.36	[3.400]	91.4	[3.60]	399400318																																																																																																																																																																																																	
19	101.6	[4.00]	91.44	[3.600]	96.5	[3.80]	399400319																																																																																																																																																																																																	
20	106.7	[4.20]	96.52	[3.800]	101.6	[4.00]	399400320																																																																																																																																																																																																	
21	111.8	[4.40]	101.60	[4.000]	106.7	[4.20]	399400321																																																																																																																																																																																																	
22	116.8	[4.60]	106.68	[4.200]	111.8	[4.40]	399400322																																																																																																																																																																																																	
23	121.9	[4.80]	111.76	[4.400]	116.8	[4.60]	399400323																																																																																																																																																																																																	
24	127.0	[5.00]	116.84	[4.600]	121.9	[4.80]	399400324																																																																																																																																																																																																	
<table><tr><td rowspan="10">FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{D} = 0$ DIVISIONAL SYMBOLS</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="2">DIMENSION UNITS</td><td colspan="2">SCALE</td><td colspan="4" rowspan="3">CURRENT REV DESC: REMOVED "OPTIONAL 10A IMPRINTING" FROM SHEET-2</td><td colspan="4" rowspan="3"><div>moLEX</div><div>5.08/.200 PLUG ASSY, FWE WITH CLOSED ENDS (9409XX)</div></td></tr><tr><td colspan="2">MM/INCH</td><td colspan="2">2:1</td></tr><tr><td colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</td></tr><tr><td colspan="2">4 PLACES</td><td>±</td><td>---</td><td>±</td><td>---</td><td colspan="4" rowspan="5">EC NO: 790249 DRWN: ABENJAMINLW 2024/06/21 CHK'D: DACHAMMER 2024/06/24 APPR: JFMURPHY 2024/07/01 INITIAL REVISION: DRWN: JAFARMER 2024/07/28 APPR: grobertson 2024/12/08</td></tr><tr><td colspan="2">3 PLACES</td><td>±</td><td>---</td><td>±</td><td>.005</td></tr><tr><td colspan="2">2 PLACES</td><td>±</td><td>0.13</td><td>±</td><td>.01</td></tr><tr><td colspan="2">1 PLACE</td><td>±</td><td>0.3</td><td>±</td><td>---</td></tr><tr><td colspan="2">0 PLACES</td><td>±</td><td>---</td><td>±</td><td>---</td></tr><tr><td colspan="2">ANGULAR TOL</td><td>±</td><td>2°</td><td colspan="4" rowspan="2">THIRD ANGLE PROJECTION </td><td colspan="2">DRAWING B-SIZE</td><td colspan="2">SERIES 39940</td><td colspan="2">DOCUMENT NUMBER SD-39940-005</td><td colspan="2">DOC TYPE PSD</td><td colspan="2">DOC PART 001</td><td colspan="2">REVISION D1</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">MATERIAL NUMBER SEE CHART</td><td colspan="2">CUSTOMER GENERAL MARKET</td><td colspan="4">SHEET NUMBER 2 OF 2</td></tr></table>											FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{D} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED "OPTIONAL 10A IMPRINTING" FROM SHEET-2				<div>moLEX</div> <div>5.08/.200 PLUG ASSY, FWE WITH CLOSED ENDS (9409XX)</div>				MM/INCH		2:1		GENERAL TOLERANCES (UNLESS SPECIFIED)				4 PLACES		±	---	±	---	EC NO: 790249 DRWN: ABENJAMINLW 2024/06/21 CHK'D: DACHAMMER 2024/06/24 APPR: JFMURPHY 2024/07/01 INITIAL REVISION: DRWN: JAFARMER 2024/07/28 APPR: grobertson 2024/12/08				3 PLACES		±	---	±	.005	2 PLACES		±	0.13	±	.01	1 PLACE		±	0.3	±	---	0 PLACES		±	---	±	---	ANGULAR TOL		±	2°	THIRD ANGLE PROJECTION 				DRAWING B-SIZE		SERIES 39940		DOCUMENT NUMBER SD-39940-005		DOC TYPE PSD		DOC PART 001		REVISION D1		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NUMBER SEE CHART		CUSTOMER GENERAL MARKET		SHEET NUMBER 2 OF 2																																																																																																
FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{D} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																							
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED "OPTIONAL 10A IMPRINTING" FROM SHEET-2				<div>moLEX</div> <div>5.08/.200 PLUG ASSY, FWE WITH CLOSED ENDS (9409XX)</div>																																																																																																																																																																																															
	MM/INCH		2:1																																																																																																																																																																																																					
	GENERAL TOLERANCES (UNLESS SPECIFIED)																																																																																																																																																																																																							
	4 PLACES		±	---	±	---	EC NO: 790249 DRWN: ABENJAMINLW 2024/06/21 CHK'D: DACHAMMER 2024/06/24 APPR: JFMURPHY 2024/07/01 INITIAL REVISION: DRWN: JAFARMER 2024/07/28 APPR: grobertson 2024/12/08																																																																																																																																																																																																	
	3 PLACES		±	---	±	.005																																																																																																																																																																																																		
	2 PLACES		±	0.13	±	.01																																																																																																																																																																																																		
	1 PLACE		±	0.3	±	---																																																																																																																																																																																																		
	0 PLACES		±	---	±	---																																																																																																																																																																																																		
	ANGULAR TOL		±	2°	THIRD ANGLE PROJECTION 				DRAWING B-SIZE		SERIES 39940		DOCUMENT NUMBER SD-39940-005		DOC TYPE PSD		DOC PART 001		REVISION D1																																																																																																																																																																																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NUMBER SEE CHART					CUSTOMER GENERAL MARKET		SHEET NUMBER 2 OF 2																																																																																																																																																																																													
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2024/07/01</td><td>17:23:49</td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>											DOCUMENT STATUS	P1	RELEASE DATE	2024/07/01	17:23:49																																																																																																																																																																																									
DOCUMENT STATUS	P1	RELEASE DATE	2024/07/01	17:23:49																																																																																																																																																																																																				
	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																														

NO. OF CIRC. "XX"	"A" DIM.		"B" DIM.		"C" ⁺⁰⁰ _{-.25} [⁺⁰⁰⁰ _{-.010}]	MATERIAL NO. (STANDARD)
03	20.3	[.80]	10.16	[.400]	15.2 [.60]	399400303
04	25.4	[1.00]	15.24	[.600]	20.3 [.80]	399400304
05	30.5	[1.20]	20.32	[.800]	25.4 [1.00]	399400305
06	35.6	[1.40]	25.40	[1.000]	30.5 [1.20]	399400306
07	40.6	[1.60]	30.48	[1.200]	35.6 [1.40]	399400307
08	45.7	[1.80]	35.56	[1.400]	40.6 [1.60]	399400308
09	50.8	[2.00]	40.64	[1.600]	45.7 [1.80]	399400309
10	55.9	[2.20]	45.72	[1.800]	50.8 [2.00]	399400310
11	61.0	[2.40]	50.80	[2.000]	55.9 [2.20]	399400311
12	66.0	[2.60]	55.88	[2.200]	61.0 [2.40]	399400312
13	71.1	[2.80]	60.96	[2.400]	66.0 [2.60]	399400313
14	76.2	[3.00]	66.04	[2.600]	71.1 [2.80]	399400314
15	81.3	[3.20]	71.12	[2.800]	76.2 [3.00]	399400315
16	86.4	[3.40]	76.20	[3.000]	81.3 [3.20]	399400316
17	91.4	[3.60]	81.28	[3.200]	86.4 [3.40]	399400317
18	96.5	[3.80]	86.36	[3.400]	91.4 [3.60]	399400318
19	101.6	[4.00]	91.44	[3.600]	96.5 [3.80]	399400319
20	106.7	[4.20]	96.52	[3.800]	101.6 [4.00]	399400320
21	111.8	[4.40]	101.60	[4.000]	106.7 [4.20]	399400321
22	116.9	[4.60]	106.68	[4.200]	111.8 [4.40]	399400322
23	121.9	[4.80]	111.76	[4.400]	116.8 [4.60]	399400323
24	127.0	[5.00]	116.84	[4.600]	121.9 [4.80]	399400324



OPTIONAL
10A IMPRINTING
(ODD CIRCUIT CONFIGURATION SHOWN)

SEE SHEET ONE
EC NO: WNA2008-0391
DRAWN: JENC INAS 2008/07/01
CHKD: CYORK 2008/07/02
APPR: MACNE IL 2008/07/07

DESCRIPTION
REV

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .005
2 PLACES ± 0.13 ± .01
1 PLACE ± 0.3 ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY J. FARMER
DATE 2004/12/03
CHECKED BY R. KEMP
DATE 2004/12/03
APPROVED BY GHR
DATE 2004/12/03
MATERIAL NO. SEE CHART
SIZE B THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION STYLE
MM/IN
SCALE 2:1
DESIGN UNITS INCH
THIRD ANGLE PROJECTION
TITLE 5.08/.200 PLUG ASSY, FWE WITH CLOSED ENDS (9409XX)
MOLEX MOLEX INCORPORATED
DOCUMENT NO. SD-39940-005
SHEET NO. 2 OF 2