

Datasheet for part number CA3106E24-9P-B-A241

Our Catalog Part Number: CA3106E24-9P-B-A241
Our Global Manufacturing Part Number: 121575-4953
Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET

Product Datasheet	
Bayonet	Connector with bayonet coupling
Shell Style	Plug, straight
Endbell Style	Endbell with clamp and bushing
Gender	Pin
Shell Size	24
Contact Arrangement	24-9
Number of contacts	2 contacts size 4
Contact Type	Solder Cup
Contact Plating	Hard silver
Shielding	no
Contact Rating at +20 °C (68 °F) (Size 160/4)	135 A
Contact Resistance (Size 160/4)	0,5 mΩ
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Insulator Resistance	Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ
Test Voltage	2000 Vrms
Air and Creepage Paths (Min)	1,1 mm
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)
Safety Provisions	IP67 acc. to DIN 40 050 and IP68 (1 bar pressure for 16h)
Salt Spray Resistance	5 days cyclic / 500h static salt spray resistant
Mating Cycles	500 min
Sep. Force per Contact (Size 160/4)	4,0 N
Gauge	For infos on Gauge please see catalog VG95234, part 1
Coupling Torque	Closing: 14 Nm max / Opening: 0,8 Nm min
Contact Retention (Size 160/4)	90 N
Shell Material	Aluminium alloy
Shell Plating	Tin Zinc (SnZn), matt grey, highly conductive
Insulator and Grommet Material	CR-Elastomere
Contact Material	Copper alloy
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction
Wire Stripping (Size 160/4)	11,8 mm
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210</i>