






注記
NOTES



- 材質
ウエハー：耐熱性ナイロン UL94V-0
ピン：銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール：銅合金、ニッケル下地、錫メッキ
MATERIAL
WAFER: POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FINNTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色：ナチュラル、黒、赤、青
COLOR: NATURAL, BLACK, RED, BLUE
- 嵌合相手：
ハウジング:502351-**0*
錫メッキ端子:50212-8*00,50372-8*00,560085-0101
金メッキ端子:56161-8*81
MATES WITH
HOUSING:502351-**0*
SN PLATING TERMINAL: 50212-8*00,50372-8*00,560085-0101
AU PLATING TERMINAL: 56161-8*81

- エンボス梱包品の詳細はSD-560020-002参照
DETAILED TAPING PACKAGE, SEE SD-560020-002
- 半田付け面のコプラナリティ: 0.1mm MAX.
CO-PLANARITY OF SOLDER TAILS TO BE 0.1mm MAX.
- 一般公差
GENERAL TOLERANCES
10 UNDER: ± 0.2
10 OVER 30 UNDER: ± 0.25
30 OVER: ± 0.3
ANGULAR: $\pm 1^\circ$


INITIAL REVISION:		
DRWN	SHSHIBATA	2009/02/18
CHECK	HKOMATSU	2009/02/18
APPR	AKANESHIGE	2009/02/18




フィッティングネール
FITTING NAIL




FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex									
	mm	5:1															
	GENERAL TOLERANCES (UNLESS SPECIFIED)					2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT											
	MM	INCH															
DIVISIONAL SYMBOLS	4 PLACES	±	±	EC NO: 635305 DRWN: MUNEMOTO 2020/04/02 CHK'D: HIJIMA 2020/04/03 APPR: TOSADA 2020/04/06			PRODUCT CUSTOMER DRAWING										
	3 PLACES	±	±														
	2 PLACES	±	±														
	1 PLACE	±	±														
	0 PLACES	±	±														
	ANGULAR TOL		±				°										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER SD-560020-001		DOC TYPE PSD		DOC PART 001		REVISION K	
						A3-SIZE		560020		MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 4			





[illegible]



10	9	8	7	6	5	4	3	2	1										
F																			F
E																			E
D																			D
C																			C
B																			B
A																			A

Sn NATURAL	52.4	61.4	57.4	56	26.2	36.9	560020-1520	15	Au NATURAL	52.4	61.4	57.4	56	26.2	36.9	560020-1530	15					
						34.9	560020-1420	14							34.9	560020-1430	14					
						32.9	560020-1320	13							32.9	560020-1330	13					
	40.4	49.4	45.4	44	20.2	30.9	560020-1220	12		30.9	560020-1230	12										
						28.9	560020-1120	11		28.9	560020-1130	11										
						26.9	560020-1020	10		26.9	560020-1030	10										
						24.9	560020-0920	09		24.9	560020-0930	09										
						22.9	560020-0820	08		22.9	560020-0830	08										
						20.9	560020-0720	07		20.9	560020-0730	07										
						18.9	560020-0620	06		18.9	560020-0630	06										
	28.4	37.4	33.4	32	14.2	16.9	560020-0520	05		16.9	560020-0530	05										
						14.9	560020-0420	04		14.9	560020-0430	04										
						12.9	560020-0320	03		12.9	560020-0330	03										
		29.4	25.4	24	11.5	11.2	560020-0220	02		11.2	560020-0230	02										
						PLATING COLOR	F	E		D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSSED PACKAGE MATERIAL NO.	CIRCUITS	PLATING COLOR	F	E	D	C	(B)	(A)

Sn BLACK	52.4	61.4	57.4	56	26.2	36.9	560020-1521	15	Sn RED								15					
						34.9	560020-1421	14									14					
						32.9	560020-1321	13									13					
	40.4	49.4	45.4	44	20.2	30.9	560020-1221	12				12										
						28.9	560020-1121	11				11										
						26.9	560020-1021	10				10										
						24.9	560020-0921	09				09										
						22.9	560020-0821	08				08										
						20.9	560020-0721	07				07										
						18.9	560020-0621	06				06										
	28.4	37.4	33.4	32	14.2	16.9	560020-0521	05				05										
						14.9	560020-0421	04				04										
						12.9	560020-0321	03				03										
		29.4	25.4	24	11.5	11.2	560020-0221	02				02										
						PLATING COLOR	F	E		D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSSED PACKAGE MATERIAL NO.	CIRCUITS	PLATING COLOR	F	E	D	C	(B)	(A)

Sn BLUE								15	Sn BLUE								15					
								14									14					
								13									13					
	40.4	49.4	45.4	44	20.2	30.9		12		30.9		12										
						28.9		11		28.9		11										
						26.9		10		26.9		10										
						24.9		09		24.9		09										
						22.9		08		22.9	560020-0823	08										
						20.9		07				07										
						18.9		06		18.9	560020-0623	06										
	28.4	37.4	33.4	32	14.2	16.9		05		16.9		05										
						14.9		04		14.9	560020-0423	04										
						12.9		03		12.9	560020-0323	03										
		29.4	25.4	24	11.5	11.2		02		11.2	560020-0223	02										
						PLATING COLOR	F	E		D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSSED PACKAGE MATERIAL NO.	CIRCUITS	PLATING COLOR	F	E	D	C	(B)	(A)

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:								molex				
		mm		NTS														
		GENERAL TOLERANCES (UNLESS SPECIFIED)				PHASE: CO NO: DRWN: Hideo Yoneyama 2023-10-23 CHK'D: Hiromichi Komatsu 2023-10-23 APPR: Takashi Iida 2023-10-24												