


RUGGED RELIABLE MICRO SOCKETS

(1.00 mm) .0394" PITCH • CLM/MLE SERIES



CLM

Mates:

FTM, FTMH, MW

MLE

Mates:

FTM, FTMH, MW

SPECIFICATIONS

Insulator Material: Black LCP

Contact Material:

CLM: Phosphor Bronze

MLE: BeCu

Plating:

CLM: Au or Sn over

50 μ " (1.27 μ m) Ni

MLE: Au over 10 μ " (0.25 μ m) Ni

Current Rating (CLM/FTM):

3.1 A per pin

(2 pins powered)

Current Rating (MLE/FTM):

2.9 A per pin (2 pins powered)

Operating Temp Range:

-55 °C to +125 °C

Max Cycles:

CLM: 100 with 10 μ " (0.25 μ m) Au

Voltage Rating:

CLM: 270 VAC

MLE: 310 VAC

Insertion Depth:

CLM:

Top Entry = (1.40 mm) .055" min.,

Bottom Entry =

(2.41 mm) .095" min.

(Add board thickness for

correct post OAL)

MLE:

(1.63 mm) .064" to

(3.18 mm) .125" with

(0.38 mm) .015" wiper,

pass-through, or (2.44 mm) .096"

minimum for bottom entry

CLM	-	1	NO. PINS PER ROW	-	02	PLATING OPTION	-	D	OPTIONS
-----	---	---	------------------	---	----	----------------	---	---	---------

02 thru 50

-F

= Gold flash on contact,
Matte Tin on tail

-L

= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail

-BE

= Bottom Entry
(Required for bottom entry)

-K

= (3.50 mm) .138" DIA
Polyimide film
Pick & Place Pad
(7 positions minimum)

-P

= Pick & Place Pad
(7 positions minimum)

-PA

= Pick & Place Pad with
integral Alignment Pin


-TR

= Tape & Reel


-FR

= Full Reel Tape & Reel
(must order maximum
quantity per reel;
contact Samtec for
quantity breaks)


**TIGER
CLAW
CONTACT**



PIN/ROW	A
04-15	(3.56) .140
16-50	(7.11) .280



-PA



-P

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (02-25)

(0.15 mm) .006" max (26-50)*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

ALSO AVAILABLE

MOQ Required

Alignment pin

Other Gold plating options



Note:

Some lengths, styles and
options are non-standard,
non-returnable.

MLE	-	1	NO. PINS PER ROW	-	01	PLATING OPTION	-	DV	OPTIONS
-----	---	---	------------------	---	----	----------------	---	----	---------

02 thru 50

-G

= 10 μ "
(0.25 μ m)
Gold

-A

= Alignment Pin
(3 positions minimum)
Metal or plastic
at Samtec discretion

-K

= (4.00 mm) .1575" DIA
Polyimide film
Pick & Place Pad
(5 positions minimum)

-P

= Metal Pick & Place Pad
(5 positions minimum)



-TR

= Tape & Reel

-FR

= Full Reel Tape & Reel
(must order maximum
quantity per reel;
contact Samtec for
quantity breaks)

**TIGER
BEAM
CONTACT**



-P

-A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[CLM-135-02-F-D-P-TR](#) [CLM-150-02-L-D-A-TR](#) [CLM-103-02-L-D-BE-TR](#) [CLM-102-02-L-D-BE-TR](#) [CLM-128-02-L-D-BE-K-TR](#) [CLM-110-02-L-D-BE-P-TR](#) [CLM-114-02-F-D-A-K](#) [CLM-124-02-F-D-P-TR](#) [CLM-112-02-F-D-A-K-TR](#) [CLM-117-02-L-D-A-P-TR](#) [CLM-135-02-L-D-K](#) [CLM-140-02-H-D-P-TR](#) [CLM-116-02-H-D-TR](#) [CLM-133-02-F-D-K-TR](#) [CLM-105-02-F-D-K](#) [CLM-103-02-F-D-A-K](#) [CLM-103-02-L-D-K-TR](#) [CLM-106-02-H-D-A](#) [CLM-106-02-L-D-K-TR](#) [CLM-116-02-H-D-BE-K-TR](#) [CLM-128-02-L-D-A-K](#) [CLM-150-02-L-D-A-K-FR](#) [CLM-104-02-L-D-BE-K-TR](#) [CLM-105-02-F-D-K-FR](#) [CLM-105-02-L-D-A-FR](#) [CLM-107-02-G-D-K-FR](#) [CLM-107-02-L-D-P-FR](#) [CLM-110-02-L-D-P-FR](#) [CLM-110-02-LM-D-A-P-FR](#) [CLM-112-02-H-D-BE-A-P-TR](#) [CLM-114-02-FM-D-K-TR](#) [CLM-118-02-LM-D-A](#) [CLM-123-02-F-D-K-FR](#) [CLM-126-02-L-D-K-FR](#) [CLM-130-02-FM-D-A-P-FR](#) [CLM-130-02-L-D-A-P-FR](#) [CLM-132-02-H-D-BE-K-TR](#) [CLM-103-02-L-D-K-FR](#) [CLM-120-02-H-D-P-FR](#) [CLM-105-02-H-D-BE](#) [CLM-108-02-F-D-BE-PA-TR](#) [CLM-110-02-L-D-K-FR](#) [CLM-121-02-F-D-P-FR](#) [CLM-116-02-L-D-P-FR](#) [CLM-106-02-L-D-A-K](#) [CLM-118-02-L-D-BE-P-FR](#) [CLM-135-02-H-D-A-P-FR](#) [CLM-104-02-F-D-FR](#) [CLM-104-02-L-D-FR](#) [CLM-130-02-F-D-P-FR](#) [CLM-125-02-F-D-FR](#) [CLM-103-02-F-D-FR](#) [CLM-123-02-L-D-BE](#) [CLM-136-02-F-D-BE-P](#) [CLM-134-02-F-D-BE-P-FR](#) [CLM-103-02-F-D-K-FR](#) [CLM-112-02-H-D-A-P-FR](#) [CLM-112-02-G-D-FR](#) [CLM-103-02-L-D-FR](#) [CLM-114-02-F-D-A-P-FR](#) [CLM-112-02-L-D-K-FR](#) [CLM-111-02-F-D-BE-FR](#) [CLM-112-02-L-D-A-K-FR](#) [CLM-126-02-F-D-A-K-FR](#) [CLM-110-02-F-D-P-FR](#) [CLM-106-02-F-D-K-FR](#) [CLM-103-02-L-D-BE-K-TR](#) [CLM-111-02-F-D-BE-K-FR](#) [CLM-118-02-L-D-BE-K-FR](#) [CLM-112-02-L-D-BE-P-FR](#) [CLM-140-02-FM-D-K-FR](#) [CLM-110-02-G-D-BE-P-TR](#) [CLM-104-02-F-D-BE-K-FR](#) [CLM-104-02-L-D-K-FR](#) [CLM-110-02-L-D-A-P-FR](#) [CLM-108-02-L-D-BE-P-FR](#) [CLM-124-02-F-D-P-FR](#) [CLM-110-02-H-D-K-FR](#) [CLM-150-02-F-D-A-K-FR](#) [CLM-135-02-H-D-A-P-TR](#) [CLM-112-02-L-D-P-FR](#) [CLM-104-02-LM-D-A-K-TR](#) [CLM-112-02-F-D-P-FR](#) [CLM-112-02-F-D-BE-K-FR](#) [CLM-104-02-F-D-K-FR](#) [CLM-117-02-L-D-BE-A-P-TR](#) [CLM-116-02-H-D-BE-P](#) [CLM-128-02-L-D-K-FR](#) [CLM-108-02-LM-D-P-FR](#) [CLM-104-02-LM-D-A-K-FR](#) [CLM-102-02-L-D-FR](#) [CLM-118-02-L-D-A-P-FR](#) [CLM-108-02-L-D-P-FR](#) [CLM-105-02-F-D-BE-K](#) [CLM-108-02-G-D-BE-A](#) [CLM-111-02-F-D-BE-TR](#) [CLM-108-02-F-D-BE-K-FR](#) [CLM-110-02-F-D-K-FR](#) [CLM-112-02-H-D-BE-A](#) [CLM-104-02-F-D-BE-PA-FR](#)