


Actuator

704.114.0



<https://eao.com/p/704.114.0>

Your product:



704.114.0 Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 29 mm
Front bezel colour:	Nature

MOUNTING

Design:	raised
----------------	--------

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

MECHANICAL CHARACTERISTIC

Switching positions:	3 positions
Switching action:	Maintained - Rest (a) - Maintained
Weight:	0.07 kg
Mechanical lifetime:	≤50 000 cycles of operation
Switching angle:	42° left / 42° right

AMBIENT CONDITION

IP Protection:	IP65 front side
Storage temperature:	- 40 °C ... + 85 °C
Operating temperature:	- 40 °C ... + 55 °C

OTHER

Hints:

The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on


Short Description:

Actuator, Ø 29 mm, Nature, Aluminium, Maintained - Rest (a) - Maintained


max. number of switching elements:

3

Switching positions:




Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:



A = Screw terminal

Wiring diagrams:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[704.114.0](#)