


V23101D 102A201 Product Details



V23101D 102A201



Active

Communications / Signal PC Board Relays



[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- V23101 / W11 Relay Series
- DC Actuating System
- Input Voltage = 3 VDC
- Contact Arrangement = 1 Form C, SPDT, 1 C/O
- Contact Current Rating = 1 Amps.

[View all Features](#) | [Find Similar Products](#)



[Previous](#) 1 ... 6 7 **8** 9 10 ... 20 [Next](#)



Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [AXICOM Telecom, Signal and RF Relays](#) (PDF, English)
- [TELECOM AND SIGNAL RELAYS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = Through Hole
- Comment = Symmetrical terminal assignment, Standard 6-pin version

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 3
- Contact Current Rating (Amps.) = 1
- [Coil Resistance \(?\)](#) = 45
- Coil Power, Nominal (mW) = 200
- Dielectric Between Coil and Contacts (V rms) = 1000

Body Related Features:

- [Series](#) = V23101 / W11 Relay
- Polarized = No

Contact Related Features:

- Mounting Options = PC Board
- Enclosure = Immersion Cleanable
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver Palladium, Gold Overlay
- Approx. Dimensions (L x W x H) (mm [in]) = 15.60 x 10.60 x 11.50 [.614 x .417 x .453]
- Contact Type = Single
- Pin Configuration = DIP

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O
- [Coil Magnetic System](#) = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240C, Wave solder capable to 260C, Wave solder capable to 265C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Axicom

