


SMT MICRO TERMINAL STRIPS

(1.00 mm) .0394" PITCH • FTMH/FTM SERIES



FTMH

Mates:
CLM, MLE

FTM

Mates:
CLM, MLE

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal
Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

Current Rating (FTMH/CLM):

3.1 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +125 °C

Voltage Rating:

FTMH: 270 VAC

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

-DV: (0.10 mm) .004" max
-DH: (0.10 mm) .004" max (05-25)
(0.15 mm) .006" max (26-50)*

*(.004" stencil solution
may be available; contact
ipg@samtec.com)

ALSO AVAILABLE

MOQ Required

End shrouds with board locks

Molded end shrouds for
05 through 08 positions

Other platings



Note:
Some lengths, styles and
options are non-standard,
non-returnable.

FTMH	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	FLEX SHROUD OPTION	OTHER OPTION
------	---	---------------------	---------------	-------------------	---------------	-----------------------	-----------------

05
thru
50

-02
= (1.91 mm)
.075" Post
(Mates
with MLE)

-03
= (1.65 mm)
.065" Post
(Mates
with CLM)

-F
= Gold flash
on post,
Matte Tin
on tail

-L
= 10 μ "
(0.25 μ m)
Gold
on post,
Matte Tin
on tail

-DV
= Dual
Vertical

-DH
= Dual
Horizontal

(-DV only with
9 pins/row
minimum)

-ES
= End Shroud

-EC
= End Shroud
with Locking Clip
(Manual placement
required)

-EP
= End Shroud
with Guide Post
(Use only when
mating with CLM)




-A
= Alignment Pin
(3 positions min.)
Metal or plastic at
Samtec discretion
(-DV only)

-K
= (2.50 mm)
.098" DIA
Polyimide Film
Pick & Place Pad
(-DH only)


-P
= Plastic Pick
& Place Pad
(6 positions min.)
(-DV only)

-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)



-DV OPTION



-DH OPTION

OPTION	B
-ES	(1.57) .062
-EC	(4.06) .160
-EP	(5.49) .216

LEAD STYLE	A
-02	(1.91) .075
-03	(1.65) .065

FTM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	DV	FLEX SHROUD OPTION	OTHER OPTION
-----	---	---------------------	---------------	-------------------	----	-----------------------	-----------------

02 thru 50
= Unshrouded

05 thru 46
= Shrouded

-02
= (1.91 mm)
.075" Post
(Mates
with MLE)

-03
= (1.65 mm)
.065" Post
(Mates
with CLM)

-F
= Gold flash
on post,
Matte Tin
on tail

-L
= 10 μ "
(0.25 μ m)
Gold
on post,
Matte Tin
on tail




-S
= End Shroud
(05 positions
minimum).
Molded or
press-fit shroud
at Samtec's
discretion

-SA
= End Shroud with
Alignment Pins
(05 through 46
positions)

-P
= Plastic Pick
& Place Pad
(7 positions min.)

-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)



Shrouded options removed for clarity

OPTION	C
-S	(4.00) .157
-SA	(7.00) .276

LEAD STYLE	D
-02	(1.91) .075
-03	(1.65) .065

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FTMH-120-03-F-DV-ES](#) [FTMH-120-03-L-DV](#) [FTMH-120-03-F-DV-ES-P](#) [FTMH-120-02-L-DV](#) [FTMH-107-03-L-DV-ES](#)
[FTMH-107-03-L-DV](#) [FTMH-109-02-L-DH](#) [FTMH-120-03-F-DV-ES-A](#) [FTMH-113-03-L-DV](#) [FTMH-112-03-L-DV](#)
[FTMH-105-02-L-DH](#) [FTMH-105-02-L-DV](#) [FTMH-105-03-L-DV](#) [FTMH-150-02-F-DH](#) [FTMH-110-02-L-DV](#) [FTMH-132-](#)
[02-F-DH](#) [FTMH-110-03-L-DV](#) [FTMH-107-03-F-DV](#) [FTMH-108-02-F-DV-A-P-TR](#) [FTMH-109-02-L-DV-A](#) [FTMH-104-03-](#)
[L-DV](#) [FTMH-106-03-F-DH](#) [FTMH-106-03-L-DV](#) [FTMH-103-03-F-DV](#) [FTMH-107-02-F-DV-P-TR](#) [FTMH-107-03-L-DV-](#)
[ES-A](#) [FTMH-107-03-L-DV-A](#) [FTMH-105-03-F-DV](#) [FTMH-103-02-L-DV](#) [FTMH-107-03-F-DV-ES-P-TR](#) [FTMH-108-02-L-](#)
[DV-A](#) [FTMH-115-03-F-DV-A](#) [FTMH-135-02-LM-DV-EC-A](#) [FTMH-102-02-L-DV](#) [FTMH-108-03-L-DH](#) [FTMH-105-03-L-](#)
[DH-K-TR](#) [FTMH-105-03-L-DV-ES-A](#) [FTMH-107-03-F-DV-ES-A](#) [FTMH-107-03-H-DV-ES](#) [FTMH-111-03-L-DV](#) [FTMH-](#)
[107-02-L-DV-ES](#) [FTMH-110-03-L-DV-ES-P](#) [FTMH-130-02-L-DH](#) [FTMH-125-03-G-DV](#) [FTMH-106-02-L-DH](#) [FTMH-](#)
[111-02-L-DH](#) [FTMH-105-02-L-DV-ES](#) [FTMH-137-03-H-DV-EC-P](#) [FTMH-138-02-L-DV](#) [FTMH-140-03-F-DH](#) [FTMH-](#)
[110-03-F-DV-ES-A](#) [FTMH-135-02-L-DH-K](#) [FTMH-112-02-L-DH](#) [FTMH-111-03-L-DV-ES-P-TR](#) [FTMH-121-02-F-DV](#)
[FTMH-130-02-F-DV-A-P](#) [FTMH-117-02-L-DH](#) [FTMH-117-03-L-DV](#) [FTMH-135-02-L-DV-ES-A](#) [FTMH-121-02-F-DH](#)
[FTMH-115-03-L-DV-ES-P-TR](#) [FTMH-124-03-F-DV](#) [FTMH-120-03-F-DV](#) [FTMH-140-02-L-DV-ES-A](#) [FTMH-107-02-L-](#)
[DH](#) [FTMH-115-02-L-DV-ES](#) [FTMH-120-02-F-DV](#) [FTMH-120-03-L-DV-ES](#) [FTMH-140-02-L-DV-A](#) [FTMH-150-02-L-DV](#)
[FTMH-105-03-F-DH](#) [FTMH-130-02-L-DV](#) [FTMH-103-03-L-DV](#) [FTMH-108-02-L-DV](#) [FTMH-110-03-F-DV](#) [FTMH-120-](#)
[02-L-DV-ES-A](#) [FTMH-106-03-F-DV-A](#) [FTMH-106-02-L-DV](#) [FTMH-111-02-F-DV](#) [FTMH-115-03-L-DV](#) [FTMH-120-02-F-](#)
[DV-ES-A](#) [FTMH-125-03-F-DV](#) [FTMH-113-03-L-DV-A](#) [FTMH-116-02-L-DV-A](#) [FTMH-116-03-F-DV](#) [FTMH-112-03-F-DV](#)
[FTMH-116-02-F-DH](#) [FTMH-140-02-F-DH](#) [FTMH-150-02-F-DV-A](#) [FTMH-150-02-F-DV-ES-A](#) [FTMH-104-02-F-DV](#)
[FTMH-104-03-F-DV](#) [FTMH-106-02-F-DV](#) [FTMH-135-02-L-DV](#) [FTMH-175-03-L-DV](#) [FTMH-108-03-F-DV](#) [FTMH-108-](#)
[03-L-DV](#) [FTMH-110-02-L-DV-A](#) [FTMH-113-02-F-DH](#) [FTMH-109-03-L-DV](#)