





Einzelheit H (20:1)
Detail H (20:1)




Schnitt AA (20:1)
Section (20:1)



- 4) Plated-through hole ; incl. plating
suitable for compliant press-in zone
PCB-plating-through : 5...15 μm Sn or SnPb over min. 25 μm Cu
Drilled holes : $\phi 1.15 \pm 0.025$ and $\phi 3.15 \pm 0.025$
 - 3) torque retention ≥ 70 Ncm
 - 2) according to DIN 41611 p.5, DIN IEC 352-5; incl. plating
 - 1) according to DIN 41652 p.2 and p.4
-
- 4) Durchmetallisierte Löcher; incl. Oberflächenbehandlung
Geeignet für elastische Einpreßzonen
Metallierung des Loches: 5...15 μm Sn oder SnPb über min. 25 μm Cu
Bohrdurchmesser: $\phi 1.15 \pm 0.025$ und $\phi 3.15 \pm 0.025$
 - 3) Verdrehsticherheit ≥ 70 Nm
 - 2) Nach DIN 41611 T.5, DIN IEC 352-5; incl. Oberflächenbehandlung
 - 1) Nach DIN 41652 T.2 und T.4

Sachnr./Ordercode V23529-	Maß/Dimension Ø G
R1*02-C***	M3
R1*03-C***	4-40UNC

Anforderungsstufe 1)
performance level 1)




Dargestellt wird die 9-polige Ausführung V23529-R1202-C209
On the drawing : the 9 pole version V23529-R1202-C209


PROPRIETARY THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.						CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD		PAPER SIZE A2	
APPLICABLE SPEC. :						FINISH			
Tyco Electronics Corporation Oostkamp - Belgium						 DIMENSIONS IN MM		DIMENSIONS APPLY	
								PATING	
LOC GW						SCALE 2:1, 20:1, 1:1		WEIGHT	
						MATERIAL			
A3	SR10-0222-02	21.5.02	KV	DATE	7.2.96	NAME Sub-D 90° abgewinkelt Standard Einpreß Stiftleiste D-Sub 90° angled standard press fit Pin			
A2	SR10-0095-02	13.2.02	KV	NAME	Sterckx				
A1	SR10-0154-01	13.4.01	KV	APP.	EC CS CI				
A	WO 00/7008	16.6.00	VS						
O3	W000/2525	25.05.00	KV						
O2	W097/4510	14.8.97	RST						
O1		23.1.97	RST						
51		7.2.96	RST						
TOLERANCE UNLESS SPECIFIED OTHERWISE						NO.		SHT.	
						V23529-R****-C****-7427		1	
REV. CHANGE ORDER DATE APP.						CUSTOMER DRAWING No.: C 2-1393481-5 OF 3			

PROPRIETARY: THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.


Ausführung mit Gewindebolzen
Version with studbolt
V23529-R1*04/R1*05-C***




verdrehsicherheit: min. 60 Ncm
Torqueretention: min. 60 Ncm



Sachnr./Ordercode V23529-	Maß/Dimension Ø M
R1*04-C***	M3
R1*05-C***	4-40UNC



Leiterplattenbohrung (2:1)
PCB hole pattern (2:1)



Sachnr./Ordercode V23529-R1***-	Polzahl n Contacts n	Maß/Dimension		
		D	E	F
C*09	09	2.74	10.96	25.00
C*15	15	2.74	19.18	33.30
C*25	25	2.76	33.12	47.04
C*37	37	2.76	49.68	63.50

Anforderungsstufe 1)
performance level 1)

Verpreßhinweis
press-in information

Einpressen über Kunststoff mit:
- 2-Hub-Pressen 60kN : 1-1393491-3
- Einpreßmaschine 60/100 kN : 4-1393488-2
Zu verwendende Werkzeuge :
- Drückstück : 1393490-6
- Amboß : 3-1393489-5
Einstellhöhe : Abstand zwischen LP und
angedrücktem Stempel : 11.15 bis 11.3mm

pressing in via the plastic body :
- 2-stroke press 60kN : 1-1393491-3
- press-fit machine 60/100kN : 4-1393488-2
pressing-in tools :
-Compression tool : 1393490-6
-anvil : 3-1393489-5
set-up heights : distance between PCB and
compression tool : 11.15 to 11.3 mm

Erläuterungen siehe Seite 1
Remarks see page 1

APPLICABLE SPEC:				FINISH			
tyco Tyco Electronics Corporation Oostkamp - Belgium				DIMENSIONS APPLY		PLATING	
				SCALE	2:1	WEIGHT	
Electronics				MATERIAL			
				NAME: Sub-D 90° abgewinkelt Standard Einpreß Stiftleiste D-Sub 90° angled standard press fit Pin			
REV. A3 see page 1				NO. V23529-R***-C***-7427		SHT. 2	
DATE				DATE		DATE	
APP.				APP.		APP.	
CUSTOMER DRAWING No.: C 2-1393481-5				OF 3			

