



DEUTSCH MIL-DTL-38999 SERIES III CONNECTORS

RUGGED, HARSH ENVIRONMENT
SUBMINIATURE CONNECTORS

QUICK REFERENCE GUIDE

Wide Range

- Mil spec, commercial, and composite
- Full line of finishes, including black zinc nickel and PTFE nickel

High Performance

- Environmentally sealed

MIL-DTL-38999 Series III Connectors

Coupling Mechanism	Threaded, 360° turn
Shell Materials	Stainless steel Aluminum Composite
Features	Scoop proof Environmentally sealed Hermetic versions Filter versions Spring fingers for EMI control
Shell Platings	Olive drab cadmium Passivated Electroless nickel Electrodeposited nickel Nickel PTFE Black zinc-nickel
No. of Contact Sizes, Std.	23, 22, 20, 16, 12, 10, 8
Shell Sizes	9, 11, 13, 15, 17, 19, 21, 23, 25
No. of Signal Contacts, Max.	187
Contact Type	AS39029
Contact Styles	Crimp Solder cup or eyelet PCB tail
Operating Temperatures	-65°C to +200°C -65°C to +175°C -65°C to +150°C (Depends on shell finish)
Durability (Mating Cycles)	500 (Higher durability versions available)
Standard Configurations	
Plugs	Straight, with EMI spring fingers Lanyard release
Receptacles	Box mounting, both front and rear panel mounting Wall mounting, both front and rear panel mounting Jam nut, rear panel mounting Solder mount Weld mount Through-hole bulkhead

TE Components . . . TE Technology . . . TE Know-how . . .


AMP | Agastat | CII | Hartman | Kilovac | Microdot | Nanonics | Polamco | Raychem | Rochester | DEUTSCH
SEACON Phoenix | L.L. Rowe | Phoenix Optix | SEACON

Get your product to market faster with a smarter, better solution.

DEUTSCH 38999 Series III Connectors

Aluminum • Stainless Steel • Composite

				Commercial Composite	ACT	26	M	D	35	P	N
				Commercial Al/SS	DTS	26	F	15	35	P	N
				Military	D38999	/26	F	D	35	P	N
Commercial Composite	Commercial Alum./Stainless	Military	Description								
RANGE											
ACT	DTS	D38999									
STYLE											
20	20	/20	Square Flange Receptacle								
24	24	/24	Jam Nut Receptacle								
26	26	/26	Straight Plug								
—	20	/21	Hermetic Square Flange Receptacle								
—	24	/23	Hermetic Jam Nut Receptacle								
—	21	/25	Hermetic Solder Flange								
—	23	/27	Hermetic Weld Flange								
FINISH											
ALUMINUM SHELL											
—	F	F	Electroless Nickel Plated (48-hr. Salt Spray)								
—	G	G	Space-Grade Electroless Nickel (48-hr. Salt Spray)								
—	T	T	Nickel PTFE (500-hr. Salt Spray)								
—	W	W	Olive Drab Cadmium (500-hr. Salt Spray)								
—	Z	Z	Black Zinc Nickel (500-hr. Salt Spray)								
COMPOSITE SHELL											
M	—	M	Electroless Nickel Plated (2000-hr. Salt Spray)								
J	—	J	Olive Drab Cadmium (2000-hr. Salt Spray)								
STAINLESS STEEL SHELL											
—	K	K	Corrosion-Resistant S.S. - Firewall (500-hr. Salt Spray)								
—	S	S	Nickel Plated (500-hr. Salt Spray)								
—	L	L	Electrodeposited Nickel (48-hr. Salt Spray)								
HERMETIC											
—	Y	Y	Stainless Steel, Passivated								
—	N	N	Stainless Steel, Nickel Plated								
—	H	H	Space Grade								
SHELL SIZES											
9 (A), 11 (B), 13 (C), 15 (D), 17 (E), 19 (F), 21 (G), 23 (H), 25 (J)				Numbers = DTS Commercial; (Letters) = Military/ACT Commercial							
INSERT ARRANGEMENTS				See Insert Arrangements Table							
CONTACTS											
P, A, H, S, B, J				P = Pin, A = Less Pin, H = 1500-Cycle Pin, S = Socket, B = Less Socket, J = 1500-Cycle Socket							
CONTACTS FOR HERMETIC CONNECTORS											
C, D, X, Z				C = PC Tail Pin, D = PC Tail Socket X = Eyelet Pin, Z = Eyelet Socket							
KEYING											
N, A, B, C, D, E				N = Normal							



Jam Nut



Plug



MIL-SPEC



Square Flange
Receptacle



PCB Type



Lanyard

Insert Arrangements



Insert		Contact Size/Quantity											Includes K Class	Uses 38999/62-8* Boots	Inactive: Superseded by
DTS Commercial	Military and Commercial ACT	8 Twinax	8 Coax	8 Power	12 Twinax	12 Coax	10	12	16	20	22D	23			
09-07	A7 (A07)										7				
09-23	A23											9			
09-35	A35										6		✓		
09-98	A98									3			✓		
11-02	B2 (B02)								2						
11-04	B4 (B04)									4					
11-05	B5 (B05)									5					
11-23	B23											19			
11-35	B35										13		✓		
11-98	B98									6			✓		
11-99	B99									7			✓		
13-04	C4 (C04)								4						
13-08	C8 (C08)									8			✓		
13-23	C23											32			
13-35	C35										22		✓		
13-98	C98									10			✓		
15-05	D5 (D05)								5				✓		
15-15	D15								1	14					
15-18	D18									18			✓		
15-19	D19									19			✓		
15-23	D23											55			
15-26	D-26								2		24				
15-35	D35										37		✓		
15-97	D97								4	8			✓		
17-02	E2 (E02)	1									38				17-03
17-03	E3 (E03)	1									38			✓	
17-06	E6 (E06)							6					✓		
17-08	E8 (E08)								8				✓		
17-11	E11				2	1				8					
17-19	E19								4	11	4				
17-20	E20							4			16				
17-22	E22	2						2							
17-23	E23											73			
17-24	E24			2							22				
17-26	E26									26			✓		
17-35	E35										55		✓		
17-99	E99								2	21			✓		
19-11	F11								11				✓		
19-18	F18	4									14				19-19
19-19	F19	4									14			✓	
19-23	E23											88			
19-28	F28								2	26					



Insert		Contact Size/Quantity													Inactive: Superseded by
DTS Commercial	Military and Commercial ACT	8 Twlnax	8 Coax	8 Power	12 Twlnax	12 Coax	10	12	16	20	22D	23	Includes K Class	Uses 38999/62-8* Boots	
19-32	F32									32			✓		
19-35	F35										66		✓		
21-11	G11							11							
21-16	G16								16						
21-20	G20	2								18					
21-23	G23											121			
21-35	G35										79		✓		
21-39	G39								2	37			✓		
21-41	G41									41			✓		
21-48	G48			4											
21-75	G75	4													21-76
21-76	G76	4												✓	
23-06	H6 (H06)	6													
23-21	H21								21						
23-23	H23											151			
23-35	H35										100				
23-53	H53									53			✓		
23-54	H54							4	9		40				
23-55	H55									55					
23-63	H63							4	4		49				
25-04	J4 (J04)								8	48			✓		
25-07	J7 (J07)	2									97				25-09
25-08	J8 (J08)	8													25-10
25-09	J9 (J09)	2									97			✓	
25-10	J10	8												✓	
25-11	J11						9			2					
25-17	J17	6									36				
25-19	J19							19							
25-20	J20	3				4			13	10					25-21
25-21	J21	3				4			13	10				✓	
25-23	J23											187			
25-24	J24							12	12						
25-29	J29								29						
25-35	J35										128		✓		
25-37	J37								37						
25-43	J43								20	23					
25-46	J46		2						4	40					25-47
25-47	J47		2						4	40				✓	
25-61	J61									61			✓		
25-90	J90	2							4	40					25-91
25-91	J91	2							4	40				✓	

Blue shaded entries are not Mil Spec.
Green shading indicates high-density inserts.

For More Information

TE Technical Support Center

North America	+1 800 522 6752
Asia Pacific	+86 0 400 820 6015
Austria	+43 1 905 601 228
Baltic Regions	+46 8 5072 5000
Benelux	+31 73 6246 999
Czech Republic	+420 800 701 462
France	+33 1 34 20 86 86
Germany	+49 6251 133 1999
Hungary	+36 809 874 04
Italy	+39 011 401 2632
Nordic	+46 8 5072 5000
Poland	+48 800 702 309
Russia	+7495 790 790 2
Spain/Portugal	+34 93 2910366
Switzerland	+41 52 633 66 26
United Kingdom	+44 800 267 666

Follow us on Twitter for all the latest product news
@TEConnectivity, and on Facebook, TEConnectivity.

te.com/38999

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773860-8 ADM/RRD 1M 10/2015

DEUTSCH, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

YACT20MA35PNC00100	YACT20JA35SAC00100	YACT24MD97BA000000	YACT24ME26AC000000
YACT24MJ35JD-61490	YACT24MJ35BD000000	YACT24MH53PC000000	YACT20MD18BB000000
YACT20MA35HD-61490	YACT20MC35JN-61490	YACT20MA98AN000000	YACT24MB98BA000000
YACT24MH53SE-61490	YACT24MG41BN000000	YACT20MA35SA-61490	YACT20MA35AC000000
YACT24MB99BD000000	YACT20MG11AE000000	YACT24MC35AA000000	YACT24MJ35PD-61490
YACT24MH35AE000000	YACT20MJ24BN000000	YACT20MH53BB000000	YACT24MA98AE000000
YACT20MD05BA000000	YACT24MB99AB000000	YACT24MH55AN000000	YACT24MF35PC000000
YACT20MB35SBC00100	YACT24MG35SC-61490	YACT24MH53JE000000	YACT20MB35PN000000
YACT24MJ24AE000000	YACT24MJ35AB000000	YACT24MC08AC000000	YACT24ME99BN000000
YACT20MC35HD000000	YACT20MD15AE000000	YACT20MD35HC-61490	YACT24MB02AC000000
YACT20MA35SC000000	YACT24MH55BE000000	YACT20MD35JAC00100	YACT20MC35AN000000
YACT24MJ29AD000000	YACT20MB35HAC00100	YACT20MJ20BC000000	YACT20ME99BA000000
YACT20MD97BA000000	YACT20MF32BB000000	YACT24MJ04AA000000	YACT24MG35SA000000
YACT24MB98BE000000	YACT20MC35JD000000	YACT20MC04AE000000	YACT20MJ37AE000000
YACT20MD35HA000000	YACT20MG16BN000000	YACT24MJ35JN-61490	YACT20MC08BB000000
YACT24MG35BE000000	YACT20MJ61BC000000	YACT24MC08BA000000	YACT20MA35BA000000
YACT20MJ43BE000000	YACT24MG35HBC00100	YACT20ME26AB000000	YACT24MJ29BB000000
YACT24MJ04AE000000	YACT24MJ35BE000000	YACT24MB98AC000000	YACT20MD18AD000000
YACT20MA98AB000000	YACT24MG35HD-61490	YACT24MA98BC000000	YACT20ME26BA000000
YACT20MG11AA000000	YACT20ME35AE000000	YACT24MJ35JNC00100	YACT20MJ04BC000000
YACT24MH35HAC00100	YACT24MG35PC000000	YACT24MJ35JD000000	YACT20MD19AB000000
YACT24MH35BC000000	YACT20ME99BN000000	YACT24MF35AC000000	YACT24ME08BB000000
YACT20MF32AD000000	YACT24MD97BE000000	YACT24MD18BN000000	YACT20MC08AD000000
YACT20MJ19AB000000	YACT20MG35AN000000	YACT20MF32BC000000	YACT24MJ35HN000000
YACT24MH53HBC00100	YACT24MC04BB000000	YACT20MB35SB-61490	YACT20MB05BA000000