






EVEN CIRCUIT, RWE

ODD CIRCUIT, RWE

AUXILIARY VIEWS

SCALE 1:1



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: MOST 5.08 (.200) PIN HEADERS
6. "XX" REFERS TO THE QUANTITY OF CIRCUITS
7. ROHS COMPLIANT

8	2	2	SCREW, MOUNTING, M2.5 X .450	STEEL	ZINC CHROMATE
7	XX	XX	SCREW, M3.5 X .280	STEEL	ZINC CHROMATE
6	XX	XX	NUT, M3.5, HEX	STEEL	ZINC CHROMATE
5	XX/2	(XX-1)/2	REAR ROW TERMINAL (-G30 OPT.)	PHOS. BRONZE	SELECTIVE GOLD
4	XX/2	(XX+1)/2	FRONT ROW TERMINAL (-G30 OPT.)	PHOS. BRONZE	SELECTIVE GOLD
3	XX/2	(XX-1)/2	REAR ROW TERMINAL	PHOS. BRONZE	HOT TIN DIP
2	XX/2	(XX+1)/2	FRONT ROW TERMINAL	PHOS. BRONZE	HOT TIN DIP
1	1	1	BARRIER	THERMOPLASTIC	BLACK
ITEM	QTY. (EVEN NO. OF CIRCUITS)	QTY. (ODD NO. OF CIRCUITS)	DESCRIPTION	MATERIAL	FINISH

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED "OPTIONAL 10A IMPRINTING" FROM SHEET-2				molex						
	MM/INCH		2:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)								5.08/.200 PLUG ASSY, RWE WITH STD. MOUNTING ENDS (9468XX)						
		MM		INCH											
	4 PLACES		±	---	±	---	PRODUCT CUSTOMER DRAWING								
	3 PLACES		±	---	±	0.005									
	2 PLACES		±	0.13	±	0.01	DOCUMENT NUMBER SD-39940-002								
	1 PLACE		±	0.3	±	---					DOC TYPE PSD				
	0 PLACES		±	---	±	---	DOC PART 001								
ANGULAR TOL		± 2.0 °		REVISION F3											
DIVISIONAL SYMBOLS		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						THIRD ANGLE PROJECTION		DRAWING B-SIZE		SERIES 39940		MATERIAL NUMBER SEE TABLE	

10	9	8	7	6	5	4	3	2	1