









CONNECTOR DESIGNATORS

F-H

**SELF-LOCKING
ROTATABLE
COUPLING**



STYLE 1
** Length ± .060 (1.52)
Min. Order Length 1.5 inch
(See Note 4)

EMI/RFI Banding and Shrink Boot Adapter Self-Locking Rotatable Coupling - Standard Profile

TABLE III: ELBOW DIMENSIONS

Shell Size Conn. Desig.		F	G	H	J
A-F-L	H	Max	Max	Max	Max
08	09	.806 (20.5)	1.038 (26.4)	.906 (23.0)	1.146 (29.1)
10	11	.832 (21.1)	1.064 (27.0)	.966 (24.5)	1.210 (30.7)
12	13	.856 (21.7)	1.088 (27.6)	1.026 (26.1)	1.268 (32.2)
14	15	.882 (22.4)	1.114 (28.3)	1.076 (27.3)	1.330 (33.8)
16	17	.908 (23.1)	1.150 (29.2)	1.136 (28.9)	1.392 (35.4)
18	19	.927 (23.5)	1.190 (30.2)	1.176 (29.9)	1.438 (36.5)
20	21	.953 (24.2)	1.250 (31.8)	1.236 (31.4)	1.500 (38.1)
22	23	.979 (24.9)	1.320 (33.5)	1.296 (32.9)	1.562 (39.7)
24	25	1.004 (25.5)	1.380 (35.1)	1.356 (34.4)	1.625 (41.3)
28		1.197 (30.4)	1.500 (38.1)	1.422 (36.1)	1.654 (42.0)
32		1.280 (32.5)	1.620 (41.1)	1.545 (39.2)	1.777 (45.1)
36		1.294 (32.9)	1.750 (44.5)	1.652 (42.0)	1.844 (46.8)
40		1.320 (33.5)	1.870 (47.5)	1.960 (49.8)	2.070 (52.6)

1. When maximum cable entry is exceeded, Style 2 will be supplied. Dimensions F, G, H and J will not apply. Please consult factory.
2. Metric dimensions (mm) are indicated in parentheses.
3. Interface O-Ring not supplied with Connector Designator A.
4. Consult factory for shorter lengths on straight backshells.
5. See G-5 for Shrink Boot Reference Information.
6. Backshells supplied with 600-052-* band, see Glenair Series 600 Tool Catalog for installation.

TABLE IV: CABLE ENTRY

Dash No.	K	L	M	Shrink Boot *
01	.125 (3.2)	.250 (6.4)	.312 (7.9)	770-003S111
31	.188 (4.8)	.312 (7.9)	.374 (9.5)	770-003S111
02	.250 (6.4)	.375 (9.5)	.437 (11.1)	770-003S112
32	.312 (7.9)	.438 (11.1)	.500 (12.7)	770-003S112
03	.375 (9.5)	.500 (12.7)	.562 (14.3)	770-003S112
33	.438 (11.1)	.562 (14.3)	.624 (15.8)	770-001S104
04	.500 (12.7)	.625 (15.9)	.687 (17.4)	770-001S104
34	.562 (14.3)	.688 (17.5)	.750 (19.1)	770-001S104
05	.625 (15.9)	.750 (19.1)	.812 (20.6)	770-001S104
35	.688 (17.5)	.812 (20.6)	.874 (22.2)	770-001S105
06	.750 (19.1)	.875 (22.2)	.937 (23.8)	770-001S105
36	.812 (20.6)	.938 (23.8)	1.000 (25.4)	770-001S105
07	.875 (22.2)	1.000 (25.4)	1.062 (27.0)	770-001S105
37	.938 (23.8)	1.062 (27.0)	1.124 (28.5)	770-001S106
08	1.000 (25.4)	1.125 (28.6)	1.187 (30.1)	770-001S106
38	1.062 (27.0)	1.188 (30.2)	1.250 (31.8)	770-001S107
09	1.125 (28.6)	1.250 (31.8)	1.312 (33.3)	770-001S107
10	1.250 (31.8)	1.375 (34.9)	1.437 (36.5)	770-001S107
11	1.375 (34.9)	1.500 (38.1)	1.562 (39.7)	770-001S107
12	1.500 (38.1)	1.625 (41.3)	1.687 (42.8)	770-001S108
13	1.625 (41.3)	1.750 (44.5)	1.812 (46.0)	770-001S108
14	1.750 (44.5)	1.875 (47.6)	1.937 (49.2)	770-001S109
15	1.875 (47.6)	2.000 (50.8)	2.062 (52.4)	770-001S109
16	2.000 (50.8)	2.125 (54.0)	2.187 (55.5)	

* Glenair Shrink Boot Supplied with "T" Option
(see Part Number Development)

TABLE II: FINISHES

Symbol	Finish
B	Cadmium Plate, Olive Drab
C	Anodize, Black
GB	Black Anodize, Hard Coat
M	Electroless Nickel
N	Cad Plate, Olive Drab over Electroless Nickel
NF	Cadmium Plate, Olive Drab over Electroless Nickel
MT	Ni-PTFE 1000 Hour Grey™ Nickel Fluorocarbon Polymer
Z1	Stainless Steel Passivate
ZL	CRES, Electroless Nickel
ZN	Zinc-Nickel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[440HS069M2506-4](#) [440HN069NF1104](#) [440HJ069MT0902](#) [440HS069M1704-4](#) [440HS069NF1104-4](#)
[440HS069NF1303-3](#) [440HS069NF1707-5](#) [440HS069M1305-4](#) [440HS069M1906-4](#) [440HS069M1504-3](#)
[440HS069NF1534-4BT](#) [440HC069NF2104](#) [440HH069NF1302](#) [440HH069Z11706](#) [440HH069ZR0902](#)
[440HH069ZR1706](#) [440HN069M1103](#) [440HN069NF2510](#) [440HS069B2508-4B](#) [440HS069M1102-4B](#)
[440HS069MT1102-4P](#) [440HS069MT1104-4](#) [440HS069MT1131-4P](#) [440HS069N1733-4](#) [440HS069NF1104-5](#)
[440HS069NF2506-4](#) [440HS069NF2507-3P](#) [440HS069Z11535-3-63](#) [440HS069Z11906-4](#) [440HS069ZR1103-2](#)
[440HS069ZR1302-4](#) [440HD069NF1705](#) [440HH069ZR1103](#) [440HH069ZR1304](#) [440HS069B1708-4B](#)
[440HS069MT1302-4](#) [440HS069MT1303-4](#) [440HS069NF0903-5](#) [440HS069NF1102-3](#) [440HS069NF1102-4BT](#)
[440HS069NF1305-4](#) [440HS069NF2503-4](#) [440HS069Z11505-2](#) [440HS069ZR1503-4](#) [440HS069ZR1505-2](#)
[440HS069NF1933-4BT](#) [440HS069M2508-3-401F](#) [440HS069M1132-3-401F](#) [440HS069M1705-3-401F](#)
[440HS069M2136-3-401F](#) [440HS069M2337-3-401F](#) [440HN069NF1736](#) [440HS069M1905-4](#) [440HS069M2133-4](#)
[440HS069M2508-3-186AA](#) [440HS069M1534-4B](#) [440HS069M1907-3](#) [440HS069M2508-3](#) [440HS069M2537-4](#)
[440HS069MT1502-4](#) [440HS069MT1703-4](#) [440HS069NF2108-5](#) [440HS069Z11706-2](#) [440HS069ZR1503-3](#)
[440HS069ZR2510-2](#) [440HS069NF1535-4BT](#) [440HS069M2104-4](#) [440HS069M2305-4](#) [440HS069NF1704-4BT](#)
[440HS069M1333-3-186AA](#)