

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0879200830](#)
Status: **Active**
Overview: [C-Grid Connector Products](#)
Description: 2.54mm Pitch C-Grid Header, Surface Mount, Dual Row, Vertical, 8 Circuits, 2.50µm Tin (Sn) Plating, with Pick-and-Place Cap, without Peg, Tape on Reel Packaging, Lead-Free

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-87920-019-001 \(PDF\)](#)
[Packaging Specification PK-89990-479-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


UL E29179

General

Product Family PCB Headers
Series [87920](#)
Application Board-to-Board, Signal, Wire-to-Board
Overview [C-Grid Connector Products](#)
Product Name C-Grid
UPC 883906910730

Physical

Breakaway Yes
Circuits (Loaded) 8
Circuits (maximum) 8
Color - Resin Black
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Mated Height 8.13mm
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Nickel
Material - Resin High Temperature Thermoplastic
Net Weight 0.522/g
Number of Rows 2
Orientation Vertical
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 2.540µm
Plating min - Termination 1.270µm
Polarized to Mating Part No
Polarized to PCB No
Robotic Placement Pick and Place Cap
Shrouded No
Stackable No
Temperature Range - Operating -55° to +105°C
Termination Interface: Style Surface Mount



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87920 Series](#)

Mates With

[7859](#) Shunts, C-Grid Receptacles, SL
Crimp, FFC and IDT Housings

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-89990-479-001
Product Specification	PS-87920-019-001
Sales Drawing	SD-87920-050-001

This document was generated on 10/29/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION