



TML-125-02-G-D

TML-113-02-G-D-RA



TML-110-01-G-D

SHROUDED HEADER TML SERIES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?TML

Insulator Material:

Black Liquid
Crystal Polymer

Insulation Resistance:

5000 MΩ min

Terminal Material:

Phosphor Bronze

Plating:

Au over 50μ" (1,27μm) Ni

Current Rating:

1A

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Max Processing Temp:

230°C for 60 seconds, or

260°C for 20 seconds 3x

Lead-Free Solderable:

Yes




SMT Lead Coplanarity:

(0,15mm) .006" max



Mates with:
SMS, RSM

APPLICATIONS



Note: Other Gold plating options available. Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM