



推奨基板レイアウト
RECOMMENDED PCB LAYOUT




参考 : 基板厚 1.0mm
REFERENCE : PCB THICKNESS 1.0mm
メタルマスク厚 0.12mm
STENCIL THICKNESS 0.12mm
マスク開口率100%
APERTURE RATIO 100%.

半田エリア (パターンエリア)
SOLDER AREA (COPPER ZONE)

半田禁止エリア (パターン禁止エリア)
SOLDER KEEP OUT AREA (NO-COPPER ZONE)
半田上がりを防ぐため。
TO PREVENT SOLDER LIFTING.
レジストによって分離する場合は、パターン面よりも盛り上がらないこと。
IF APPLY RESIST IN THIS AREA, LEVEL AS PATTERN AREA FACE.


△5 嵌合図
MATED CONNECTORS




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex					
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 712179 DRWN: TENAGASE 2022/06/28 CHK'D: SAKIYAMA 2022/06/28 APPR: AIDA 2022/06/28				PICO-SPOX 1.5 W/B SINGLE ROW RIGHT ANGLE SMT PLUG ASSEMBLY GOLD PLATING					
ANGULAR TOL ± 3.0 °												
4 PLACES		± 0.2					INITIAL REVISION: DRWN: TODA 2016/08/08 APPR: TKANEKO 2017/03/23			PRODUCT CUSTOMER DRAWING		
3 PLACES		± 0.2										
2 PLACES		± 0.2										
1 PLACE		± 0.2	DOCUMENT NUMBER 2027060241				DOC TYPE	DOC PART	REVISION			
0 PLACES		± 0.2					PSD	000	E			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER		
					A3-SIZE	202706	SEE SHEET3		GENERAL	2 OF 3		

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/28	06:06:24
-----------------	----	--------------	------------	----------


エンボス梱包 詳細
EMBOSSED CARRIER TAPE PACKING DETAILS



注記
NOTE
7. リーダー部および末端部テープ長さ
LEADER AND TRAILER TAPE LENGTH





8. トップテープの剥離強度: IEC60286-3に準拠。
PEELING OFF FORCE OF THE TOP TAPE: DEFINED IEC60286-3.
(剥離方向は下図を参照)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)




9. EIA-481に準拠する。
PACKAGING STANDARD IS AS PER EIA-481.
10. 梱包数量=1000個/リール
TAPE & REEL QUANTITY=1000PCS/REEL
11. 本製品は乾燥剤入りハイバリア梱包での納品となる。
THIS PRODUCT IS DELIVERED IN A HIGH BARRIER PACKAGE WITH DESICCANT.
12. 梱包仕様書: 2027069200 PS 200
PACKING INFORMATION: 2027069200 PS 200

リール 詳細
REEL DETAILS



44.4	50.4	2±0.15	20.2±0.15	44	2027061541	2027061543	15
32.4	38.4	2±0.1	14.2±0.1	32	2027061441	2027061443	14
					2027061341	2027061343	13
					2027061241	2027061243	12
					2027061141	2027061143	11
24.4	30.4	2±0.1	11.5±0.1	24	2027061041	2027061043	10
					2027060941	2027060943	9
					2027060841	2027060843	8
					2027060741	2027060743	7
16.4	22.4	7.5±0.1	7.5±0.1	16	2027060641	2027060643	6
					2027060541	2027060543	5
					2027060441	2027060443	4
					2027060341	2027060343	3
					2027060241	2027060243	2
J	H MAX	G	F	E	ヘッダー番号 HEADER NO.	オーダー番号 ORDER NO.	極数 CIRCUIT SIZE

番号 NO.	部品 PART	材質 MATERIAL	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
			DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex					
			mm	NTS														
			GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 712179 DRWN: TENAGASE CHK'D: SAKIYAMA APPR: AIDA INITIAL REVISION: DRWN: TODA APPR: TKANEKO						PICO-SPOX 1.5 W/B SINGLE ROW RIGHT ANGLE SMT PLUG ASSEMBLY GOLD PLATING					
			ANGULAR TOL ± 3.0 °															
4 PLACES		± 0.2		2022/06/28														
3 PLACES		± 0.2		2022/06/28														
⑤	トップテープ TOP TAPE	ポリエチレン POLYETHYLENE (PE)	2 PLACES		± 0.2		2022/06/28		PRODUCT CUSTOMER DRAWING									
			1 PLACE		± 0.2		2016/08/08											
⑥	リール REEL	ポリスチレン POLYSTYRENE (PS)	0 PLACES		± 0.2		2017/03/23		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
							A3-SIZE		202706		SEE SHEET3		GENERAL				3 OF 3	