

S11MCC-P03MPH9-52C0  
ODU MEDI-SNAP®  
Straight plug



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S11MCC-P03MPH9-52C0 |
| Termination       | Solder              |
| Size              | 1                   |
| Locking principle | Push-Pull           |
| Coding            | C (60°)             |
| Cable Diameter    | 4 – 5.2 mm          |
| Cable outlet      | Back nut            |



The pin layout corresponds to the view on the termination area

Contact insert description

|                      |        |
|----------------------|--------|
| Number of contacts   | 3      |
| Contact type         | Pins   |
| Contact diameter     | 1.3 mm |
| Insulator material   | PEEK   |
| Wire cross section   | AWG 20 |
| Termination          | Solder |
| Termination diameter | 1.1 mm |

Reverse gender on request

Technical information

|                                          |                             |                                            |
|------------------------------------------|-----------------------------|--------------------------------------------|
| Max. creepage and air clearance distance | 1.2 mm (Contact to contact) |                                            |
| Nominal current single contact           | 12 A                        | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Nominal current insert                   | 12 A                        | VDE 0298-4:2003                            |
| Test voltage                             | 1.55 kV AC                  | EIA-364-20F:2019-02                        |

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

### Mechanical and environmental data

|                       |                 |
|-----------------------|-----------------|
| Degree of protection* | IP50            |
| Operating temperature | -50 °C – 120 °C |
| Mating cycles         | 2000            |

\*mated & unmated condition

### Material and surface treatments

|              |                                  |
|--------------|----------------------------------|
| Housing      | Cu-alloy with matt chrome finish |
| Color option | Chrome finish                    |
| Contact      | Cu-alloy with gold finish        |

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.