




CONTACT SIZE	SHELL SIZE	X	Y
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	16 THRU 40	.260 ^{+.052} _{-.041}	.102
12	16 THRU 40	.118 ^{+.039} _{-.056}	.102
0, 4, 8	16 THRU 40	.091±.039	.102

WIRE WELL DATA					
CONTACT SIZE	0	4	8	12	16
WELL DIA	.453±.005	.281 ^{+.005} _{-.004}	.179 ^{+.004} _{-.002}	.098 ^{+.004} _{-.001}	.063 ^{+.004} _{-.001}
WELL DEPTH ^{+.031} _{-.000}	.592	.500	.500	.250	.250

REVISIONS			
LTR	DESCRIPTION	DATE	APPVD
B	(CL11) SEE CHANGE NOTICE NUM:86973	9-17-99 PRESCOTT	<i>Prescott</i>



SEE NOTE 3

SEE SHEET 2.

NOTES:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORPORATION.

COMPANY ID: 9
INTERNAL: N
DATE CODE: N

COD/MS/CUST: N
LOT NO: N
SEE DRAW: N

N/A
N/A

STAMPING DATA

NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS	POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ±.0005 .XXX = ±.010 .XX = ±.03 .X = ±.1 ANGLES = ±2° OTHER STANDARDS PER 9-3800 AND DOD-D-1000 THIRD ANGLE PROJECTION	MATERIAL SPEC.	PARTS LIST				
	N/A	AMPHENOL CORPORATION BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y.				
	PROCESS SPEC.	CONNECTOR, ELECTRICAL RECEPTACLE, L TYPE GTC07R-(), OLIVE DRAB CADMIUM PLATED				
	SEE NOTE 4	SCALE: 2.0 REF: 88-581120/139 SHEET 1 OF 2				
APPROVALS		DATE	REV. B			
PREPARED		A. PRESCOTT	02-Apr-96			
CHECKED		A. PRESCOTT	4-10-96			
MATERIAL						
APPROVED						
APPROVED		R. BARNES	4-10-96			
PRO/ENG INFORMATION		GTC07R-24.ASSEM				
		71-581120-139				

FAMCODES DATA3: GTCBNS CICS: 1653

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC07R32-17S\(027\)\(RDS\)](#) [GTC07R32-5S\(023\)\(RDS\)](#) [GTC07R32-1S\(025\)\(RDS\)](#) [GTC07R20-19S\(RDS\)](#)
[GTC07R32-1S\(RDS\)](#) [GTC07R32-17S\(RDS\)](#) [GTC07R-20-29S](#) [GTC07R-14S-9S](#) [GTC07R24-10P](#) [GTC07R2018S](#)
[GTC07R24-10PW](#) [GTC07R36-5S-RDS](#) [GTC07R36-6SX-RDS-023](#) [GTC07R-32-15S](#) [GTC07R2024S](#) [GTC07R18-1P](#)
[GTC07R36-6S-RDS-023](#) [GTC07R32-1P](#) [GTC07R24-10S](#) [GTC07R36-6SY-RDS-023](#) [GTC07R249P](#) [GTC07R-36-5S](#)
[GTC07R-18-10P](#) [GTC07R2024P](#) [GTC07R20-29P](#) [GTC07R-32-5S](#) [GTC07R-36-10S](#) [GTC07R-32-17S](#) [GTC07R20-](#)
[23SY](#) [GTC07R22-10SX-A24](#) [GTC07R24-10SW](#) [GTC07R36-5SW](#) [GTC07R22-10S](#) [GTC07R36-22S](#) [GTC07R22-22S](#)
[GTC07R36-5SX-RDS](#) [GTC07R22-22S-RDS](#) [GTC07R32-5S-RDS](#) [GTC07R22-19P](#) [GTC07R22-22P](#) [GTC07R-36-5P](#)
[GTC07R18-1S](#) [GTC07R20-19P](#) [GTC07R14S-2S](#) [GTC07R18-7S](#) [GTC07R20-15S-A24](#) [GTC07R14S-7P](#)
[GTC07R18-11P](#) [GTC07R14S-7S](#) [GTC07R20-27S](#) [GTC07R20-23SX](#) [GTC07R20-30S](#) [GTC07R20-7S](#) [GTC07R20-](#)
[19S](#) [GTC07R20-23S](#) [GTC07R20-11S](#) [GTC07R18-3S](#) [GTC07R20-23SW](#) [GTC07R20-27SW](#) [GTC07R32-5P](#)
[GTC07R24-28S](#) [GTC07R20-25S](#) [GTC07R20-15S](#) [GTC07R18-7P](#) [GTC07R18-12P](#) [GTC07R20-24PW](#) [GTC07R24-](#)
[5S](#) [GTC07R20-29PW](#) [GTC07R24-12S-023](#) [GTC07R36-3P](#) [GTC07R20-33P](#) [GTC07R32-82P](#) [GTC07R32-25S](#)
[GTC07R22-9S](#) [GTC07R36-77S](#) [GTC07R22-23S](#) [GTC07R-32-17P](#) [GTC07R-20-22P](#) [GTC07R-36-6S](#) [GTC07R28-](#)
[AYS](#) [GTC07R1810S](#) [GTC07R2411S023](#) [GTC07R2023P](#) [GTC07R1812S](#) [GTC07R169S](#) [GTC07R2411P](#)
[GTC07R1611S](#) [GTC07R32-3P](#) [GTC07R32-1S](#) [GTC07R24-9S](#) [GTC07R24-12S](#) [GTC07R24-10S-C10](#) [GTC07R24-](#)
[12P-B30-014](#) [GTC07R24-12P-023](#) [GTC07R24-11P-023](#) [GTC07R32-3S](#) [GTC07R36-4S](#) [GTC07R36-4P](#) [GTC07R36-](#)
[14P-025](#) [GTC07R36-6SW-RDS-023](#)