

FIGURE 1




FIGURE 2




FIGURE 3




FIGURE 4





FIGURE 5



PANDUIT PART NUMBER	COPPER CABLE - AWG (METRIC)	NOMINAL GROUND ROD SIZE	DIMENSIONS - IN [mm]			PANDUIT DIE COLOR CODE & INDEX (QTY OF CRIMPS)	STD. PKG. QTY.
			FIGURE	WIRE PORT I.D.	ROD PORT I.D.		
FIG8-1/2-2/0	SOLID: N/A STRANDED: 2 AWG - 2/0 AWG (35-50 sq mm)	1/2" ROD (12.7mm)	FIGURE 1	0.46 [11.6]	0.53 [13.5]	BLACK P106 (1)	1
FIG8-5/8-2/0		5/8" ROD (15.9mm)	FIGURE 1		0.66 [16.7]		1
FIG8-3/4-2/0		3/4" ROD (19.1mm)	FIGURE 2		0.78 [19.8]		1
FIG8-1-2/0	1" ROD (25.4mm)	FIGURE 3	1.03 [26.2]	1			
FIG8-1/2-250	SOLID: N/A STRANDED: 3/0-250 kcmil (95-120 sq mm)	1/2" ROD (12.7mm)	FIGURE 1	0.61 [15.6]	0.53 [13.5]		1
FIG8-5/8-250		5/8" ROD (15.9mm)	FIGURE 1		0.66 [16.7]		1
FIG8-3/4-250		3/4" ROD (19.1mm)	FIGURE 2		0.78 [19.8]	1	
FIG8-1-250	1" ROD (25.4mm)	FIGURE 3	1.03 [26.2]	1			
FIG8-5/8-500	SOLID: N/A STRANDED: 300-500 kcmil (185-240 sq mm)	5/8" ROD (15.9mm)	FIGURE 2	0.85 [21.5]	0.66 [16.7]	1	
FIG8-3/4-500		3/4" ROD (19.1mm)	FIGURE 2		0.78 [19.8]	1	
FIG8-1-500		1" ROD (25.4mm)	FIGURE 4		1.03 [26.2]	1	
FIG8-5/8-32	SOLID: 2 AWG STRANDED: N/A QUANTITY 1, 2, OR 3 WIRES	5/8" ROD (15.9mm)	FIGURE 5	0.30 [7.5]	0.66 [16.7]	1	



DB RATED

NOTES:

- DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- ALL PARTS ARE cULus LISTED FOR UL 467 GROUNDING AND BONDING APPLICATIONS.
- ALL PARTS ARE SUITABLE FOR DIRECT BURIAL IN EARTH OR CONCRETE.
- PRE-APPLIED ANTIOXIDANT COMPOUND ENSURES A HIGH QUALITY MECHANICAL AND ELECTRICAL BOND, SPEEDING INSTALLATION.
- FOR TIN PLATED VERSION, ADD SUFFIX "TP" TO ANY PART NUMBER ABOVE. TIN PLATED CONNECTORS ARE FOR GALVANIZED GROUND ROD APPLICATIONS.
- ALL PARTS ARE SUITABLE FOR USE WITH COPPER CLAD, SOLID COPPER, AND STAINLESS STEEL GROUND RODS. TIN PLATED VERSIONS ARE ADDITIONALLY COMPATIBLE WITH GALVANIZED STEEL GROUND RODS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	DATE	CHK	SCALE	SHEET	
03	2/19	DAKOJHNU	RGB		REVISED METRIC WIRE RANGE		FIGURE 8 SERIES COPPER COMPRESSION GROUNDING TAP CONNECTORS CUSTOMER DRAWING ITEM REVISION NAME: 00195EBA/03 DATASET FILE NAME: 00195EBA-DC/03.SLDDRW UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ± THIRD ANGLE PROJECTION DRAWN BY: DAOS DATE: 8/27/18 CHK: JHNU SCALE: N/A	8/27/18	JHNU	N/A	1	
02	1/19	DAOSJHNU	RGB		REVISED METRIC WIRE RANGE			1				
01	12/18	DAOSJHNU	RGB		NOTE 6 ADDED			1				
00	8/18	DAOSJHNU	RGB		INITIAL RELEASE			1				
								PANDUIT HIGH CONDUCTIVITY COPPER DRAWING NUMBER: 00195EBA-DC				1
								SHEET 1 OF 1				1