

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 jack insert, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: IDC connection, connection cross section: AWG 26-22, cable outlet: straight, Keystone design for use with IP20 panel mounting frame or integrated directly into the housing panel, Ethernet

Product description

Keystone system

Your advantages

- Assembly without special tools
- Compact design
- Rugged design

Commercial data

Item number	1419021
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNACA
Catalog page	Page 374 (C-2-2019)
GTIN	4055626251448
Weight per piece (including packing)	20.13 g
Weight per piece (excluding packing)	20.13 g
Customs tariff number	85366990
Country of origin	PL

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Technical data

Product properties

Product type	Female insert
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Number of slots	1
Shielded	yes
Cable outlet	straight

Data management status

Article revision	03
------------------	----

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	0.8 kV
Frequency range	500 MHz
Insulation resistance	> 500 MΩ (100 V DC)
Nominal voltage U _N	72 V (DC)
Nominal current I _N	1.5 A
Transmission medium	Copper
Transmission characteristics (category)	CAT6 _A
Power transmission	PoE+

Connection data

Connection technology

Connection method	IDC connection
-------------------	----------------

Material specifications

Housing material	Metal
Housing surface material	metal-plated
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	PC
Material, protective cover	PC

Cable/line

External cable diameter	4.5 mm ... 9 mm
-------------------------	-----------------

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Wire diameter	0.4 mm ... 0.65 mm
Wire diameter including insulation	0.8 mm ... 1.6 mm

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 750

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Mounting

Mounting type	Snap in
---------------	---------

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419021>



cUL Recognized

Approval ID: FILE E 335024



UL Recognized

Approval ID: FILE E 335024

cULus Recognized

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Classifications

ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440223
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-K-J1ZNI-S/R4IDC8 - RJ45 jack insert

1419021

<https://www.phoenixcontact.com/us/products/1419021>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com