



SD05

Transient Voltage Suppression Diode

## Features


400Watts peak pulse power ( $t_p = 8/20\mu s$ )  
Unidirectional configurations  
Solid-state silicon-avalanche technology  
Low clamping voltage  
Low leakage current  
IEC 61000-4-2  $\pm 30kV$  contact  $\pm 30kV$  air  
IEC 61000-4-4 (EFT) 40A (5/50ns)  
IEC 61000-4-5 (Lightning) 27A (8/20 $\mu s$ )

## Mechanical Data


SOD323 package  
Molding compound flammability rating: UL 94V-0  
Packaging: Tape and Reel  
RoHS/WEEE Compliant

## Applications

USB Vbus,  
Power Line  
Power management



SOD323



UNIT	A	C	D	E	E <sub>1</sub>	b	L <sub>1</sub>	A <sub>1</sub>
mm	max	1.1	0.15	1.4	1.8	2.75	0.4	0.45
	min	0.8	0.08	1.2	1.4	2.55	0.25	0.2
mil	max	43	5.9	55	70	108	16	16
	min	32	3.1	47	63	100	9.8	7.9

## Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power ( $t_p = 8/20\mu s$ )	P <sub>PP</sub>	400	Watts
Peak Pulse Current ( $t_p = 8/20\mu s$ ) (note1)	I <sub>pp</sub>	27	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V <sub>ESD</sub>	30 30	kV
Lead Soldering Temperature	T <sub>L</sub>	260(10seconds)	°C
Junction Temperature	T <sub>J</sub>	-55 to + 150	°C
Storage Temperature	T <sub>stg</sub>	-55 to + 150	°C


# SD05

## Electrical Characteristics

Parameter	Symbol	Conditions	Min	Typical	Max	Units
Reverse Stand-Off Voltage	$V_{RWM}$				5.0	V
Reverse Breakdown Voltage	$V_{BR}$	$I_T=1\text{mA}$	6.0			V
Reverse Leakage Current	$I_R$	$V_{RWM}=5\text{V}, T=25^\circ\text{C}$			1	uA
Clamping Voltage	$V_C$	$I_{PP}=27\text{A}, t_p=8/20\mu\text{s}$		16	20	V
Junction Capacitance	$C_j$	$V_R = 0\text{V}, f = 1\text{MHz}$		165	200	pF

## Electrical Parameters (TA = 25°C unless otherwise noted)


Symbol	Parameter
$I_{PP}$	Maximum Reverse Peak Pulse Current
$V_C$	Clamping Voltage @ $I_{PP}$
$V_{RWM}$	Working Peak Reverse Voltage
$I_R$	Maximum Reverse Leakage Current @ $V_{RWM}$
$V_{BR}$	Breakdown Voltage @ $I_T$
$I_T$	Test Current




Note: 8/20μs pulse waveform.

## RATING AND CHARACTERISTIC CURVES (SD05)


**Figure 1: Peak Pulse Power vs. Pulse Time**



**Figure 2: Power Derating Curve**



**Figure 3: Pulse Waveform**



**Figure 4: Clamping Voltage vs.I<sub>pp</sub>**

