

Han EMC/B 6 surface mout. 1Lever 2xM32



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 806 0292
Specification	Han EMC/B 6 surface mout. 1Lever 2xM32
HARTING eCatalogue	https://b2b.harting.com/19628060292

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC/B
Type of hood/housing	Surface mounted housing
Type	Low construction

Version

Size	6 B
Version	Side entry
Cable entry	2x M32
Locking type	Single locking lever
Han-Easy Lock®	Yes
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated

Material properties

Colour (hood/housing)	Unpainted
Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	283 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140361591
ETIM	EC000437

Commercial data

eCl@ss

27440202 Shell for industrial connectors