

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB PCB connectors, degree of protection: IP20, number of positions: 9, 5 Gbps, material: Metal, connection method: Solder connection, USB 3.0

## Your advantages

- Optimized for wave soldering
- Data transmission up to 5 Gbps
- Comfortable tray packing

## Commercial data

Item number	1332638
Packing unit	140 pc
Minimum order quantity	140 pc
Sales key	AB14
Product key	ABNDAB
GTIN	4063151630300
Weight per piece (including packing)	2.36 g
Weight per piece (excluding packing)	2.36 g
Customs tariff number	85366930
Country of origin	CN

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	USB-A
Sensor type	USB 3.0
Number of positions	9
Connection profile	USB-A
Type of packaging	Tray
Number of slots	1
Type	Socket
Shielded	yes

### Data management status

Article revision	01
------------------	----

### Insulation characteristics

Overshoot category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/2)	30 V
Rated surge voltage (III/2)	1500 V
Rated current	1.8 A
Contact resistance	30 mΩ
Frequency range	20 Hz ... 500 Hz
Insulation resistance	1000 MΩ
Transmission medium	Copper
Transmission characteristics (category)	USB 3.2 Gen 1
Transmission speed	5 GBit/s
Power transmission	54 W

### Connection data

#### Connection technology

Connection method	Solder connection
-------------------	-------------------

### Dimensions

Width	14.45 mm
Height	7.4 mm
Length	14.8 mm
Orientation to	180.00 °

### Material specifications

Color of the housing part	blue
---------------------------	------

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	Brass
Contact surface material	Gold over nickel
Contact carrier material	PA 4T

## Cable/line

Test voltage Core/Core	500 V
Test voltage Core/Shield	500.00 V
Acceleration	3.1 m/s <sup>2</sup>
Halogen-free	yes

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 5000
Insertion force per signal contact	35.00 N
Extraction force per signal contact	< 10 N

## Environmental and real-life conditions

### Test specification

Specification	EIA 364-1000
Frequency	20-500 Hz
Sweep speed	1 octave/min
Acceleration	3.10 m/s <sup>2</sup>
Test duration	15.00 min.
Contact resistance R <sub>1</sub>	30.00 mΩ

### Test specification

Specification	60068-2-27
Acceleration	30.00 g
Number of shocks per direction	18.00

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

## Mounting

Mounting type	Wave soldering
---------------	----------------

### Processing notes

Process	Wave soldering
Classification temperature T <sub>c</sub>	260 °C

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors




1332638

<https://www.phoenixcontact.com/us/products/1332638>

## Drawings

Diagram



Classification wave soldering profile

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

## Classifications

### ECLASS

ECLASS-11.0	27440390
ECLASS-12.0	27440390
ECLASS-13.0	27460201

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)