



MI-200TM

Military COTS DC-DC Converters 50 to 100 W

Features

- ✧ Inputs:
28 Vdc per MIL-STD-704D/E
155 Vdc per MIL-STD-1399A
270 Vdc per MIL-STD-704D/E
- ✧ Single output: 2 – 48 Vdc
- ✧ Up to 23 W/in³
- ✧ MIL-STD-810 environments
- ✧ Up to 90% efficiency
- ✧ Remote sense
- ✧ Current limit
- ✧ OVP and thermal shut down
- ✧ Power boosters for higher power outputs
- ✧ ZVS/ZCS power architecture
- ✧ Low noise FM control
- ✧ Size: 4.6" x 2.4" x 0.5"
(116,8 x 61,0 x 12,7 mm)

Converter/Booster Specifications

(At $T_{BP} = 25^{\circ}\text{C}$, nominal line and 75% load, unless otherwise specified)

PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Input Characteristics					
Input voltage range	See input voltage chart				
No load power dissipation	1.35	2.0		Watts	
Output Characteristics					
Set point accuracy		0.5	1.0	% Vnom	
Load/line regulation		0.05	0.2	% Vnom	LL to HL, 10% to FL
		0.2	0.5	% Vnom	LL to HL, NL to 10%
Output temperature drift		0.01	0.02	%/°C	
Output noise - pp		1.0	1.5	% Vnom	} Whichever is greater 20 MHz BW
		100	150	mV	
Output voltage trimming ⁽¹⁾	50		110	% Vnom	
Remote sense compensation		0.5		Vdc	
OVP set point ⁽²⁾	115	125	135	% Vnom	Latching
Current limit	105		125	% Inom	Auto restart
Short circuit current ⁽³⁾	20		130	% Inom	
Control Pin Characteristics					
Gate in high threshold		6		Vdc	
Gate in low threshold	0.65			Vdc	
Gate in low current			6	mA	
Power sharing accuracy	0.95		1.05		
Isolation Characteristics					
Isolation (input to output)	3,000			Vrms	
Isolation (output to baseplate)	500			Vrms	
Isolation (input to baseplate)	1,500			Vrms	
Input/output capacitance		50	75	pF	
Environmental (MIL-STD-810)					
Altitude - method 500.2	70,000			feet	Procedure II
Humidity - method 507.2	86/240			%/hours	Procedure 1, cycle 1
Acceleration - method 513.3	9			g's	Procedure 2
Vibration - method 514.3	20			g's	Procedure 1, category 6
Shock - method 516.3	40			g's	Procedure 1
Reliability (MIL-HDBK-217F)					
25°C Ground Benign: G.B.		2,478,477		hours	
50°C Naval Sheltered: N.S.		584,920		hours	
65°C Airborne Inhabited Cargo: A.I.C.		483,303		hours	
Thermal Characteristics					
Efficiency		80-90		%	
Baseplate to sink		0.07		°C/W	With thermal pads
Thermal shut down	90	95	105	°C	Latching
Baseplate operating temperature			+85	°C	See product grade
Storage temperature			+100	°C	See product grade
Mechanical Specifications					
Weight		6.0 (170)		ounces (grams)	

⁽¹⁾ 10 V, 12 V, and 15 V outputs, standard trim range $\pm 10\%$. Consult factory for wider trim range.

⁽²⁾ No over temperature or voltage protection in booster modules.

⁽³⁾ Output voltages of 5 V or less incorporate foldback current limiting; outputs of 10 V and above provide constant current limiting.

Configuration Chart

MI-2



Semi-custom driver and booster modules available: *Consult factory.*

(1) 16 V operation at 75% load.

(2) These units rated at 75% load from 125-150 Vin:

MI-26Z-xV

MI-26Y-xV

MI-260-xW

28 Vdc input per MIL-STD 704D/E

155 Vdc input per DOD-STD-1399A

270 Vdc input per MIL-STD-704D/E

Input Voltage

Nominal	Range	Transient
2 = 28 V	18 - 50 V ⁽¹⁾	60 V
5 = 155 V	100 - 210 V	230 V
6 = 270 V	125 - 400 V ⁽²⁾	475 V
7 = 165 V	100 - 310 V	

Output Voltage

Z = 2 V	T = 6.5 V	N = 18.5 V
Y = 3.3 V	R = 7.5 V	3 = 24 V
O = 5 V	M = 10 V	L = 28 V
X = 5.2 V	1 = 12 V	J = 36 V
W = 5.5 V	P = 13.8 V	K = 40 V
V = 5.8 V	2 = 15 V	4 = 48 V

Product Grade Operating Temp.

I	=	-40°C to +85°C
M	=	-55°C to +85°C

Output Power/Current

	≥ 5 V	< 5 V
Y	50 W	10 A
X	75 W	15 A
W	100 W	20 A
V	—	30 A

For additional power, 100 W and 75 W booster modules available. Change MI-2xx-xx to MI-Bxx-xx.

Product Grade Specifications

PARAMETER	PRODUCT GRADE	
	I-Grade	M-Grade
Storage temperature	-55°C to +100°C	-65°C to +100°C
Operating temperature (baseplate)	-40°C to +85°C	-55°C to +85°C
Power cycling burn-in	12 hours, 25 cycles	96 hours, 200 cycles
Temperature cycled with power off	12 cycles	12 cycles
17°C per minute rate of change	-65°C to +100°C	-65°C to +100°C
Test data supplied at these temperatures*	-40°C, +80°C	-55°C, +80°C
Warranty	2 years	2 years
Environmental compliance	MIL-STD-810	MIL-STD-810
Derating	NAVMAT P-4855-1A	NAVMAT P-4855-1A

*Test data available for review or download from vicorpower.com

Mechanical Drawing

MI-200 Mechanical Drawing

