



Views from "X" rotated


6-Pole




7-Pole




9-Pole
(8+1)




12-Pole




16-Pole




17-Pole



19-Pole
(16+3)



Cable Diameter		Solder Contacts	Crimp Contacts	Without Contacts
6 Pole		KRS6G20-553	KRS6G20-403	KRS6G20-003
		1202310001	1202310002	1202310003
	Crimp range*		0,75-2,5mm ²	
7 Pole		KRS7G20-553	KRS7G20-403	KRS7G20-003
		1202310004	1202310005	1202310006
	Crimp range*		0,75-2,5mm ²	
9 Pole (8+1)		KRS9G20-553	KRS9G20-423	KRS9G20-003
		1202310007	1202310008	1202310009
	Crimp range*		0,34-1,0mm ² /0,75-2,5mm ²	
12 Pole		KRSCG20-553	KRSCG20-023	KRSCG20-003
		1202310010	1202310011	1202310012
	Crimp range*		0,34-1,0mm ²	
16 Pole		KRSHG20-553	KRSHG20-023	KRSHG20-003
		1202310013	1202310014	1202310015
	Crimp range*		0,34-1,0mm ²	
17 Pole		KRSJG20-553	KRSJG20-023	KRSJG20-003
		1202310016	1202310017	1202310018
	Crimp range*		0,34-1,0mm ²	
19 Pole (16+3)		KRSLG20-553	KRSLG20-223	KRSLG20-003
		1202310019	1202310020	1202310021
	Crimp range*		0,34-1,0mm ² /0,56-1,0mm ²	



Notes:

Tolerances (unless specified): DIN ISO 2768 m

*Crimp range only applies to "Crimp Contacts" version

DESCRIPTION EC NO: WEU2009-0135 DRWN: BBRAUCH 2008/11/14 CHK'D: ---- APPR: JKOLB 2009/03/02	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM		SCALE ---	DESIGN UNITS METRIC	 FIRST ANGLE PROJECTION	
		 = 0  = 0		mm	INCH	DRAWN BY BB	DATE 2008/11/14	M23 FRONT PM RECEPT. FEM FLANGE-MOUNT 4 X DIA 3.2MM			
			4 PLACES	±----	±----	CHECKED BY JKO	DATE 2008/12/09				
			3 PLACES	±----	±----	APPROVED BY DATE					
			2 PLACES	±0.05	±----	-----		 MOLEX INCORPORATED			
			1 PLACE	±0.1	±----						
			ANGULAR ± --- °			MATERIAL NO. see table		DOCUMENT NO. SD-120231-001		SHEET NO. 1 OF 1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							