

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Pin, straight, M12, coding: T, PCB mounting, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239189

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1418341
Packing unit	100 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQAGD
GTIN	4055626170664
Weight per piece (including packing)	7.645 g
Weight per piece (excluding packing)	7.37 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	4
Seal present	yes
Shielded	yes
Coding	T
Thread type	M12

Data management status

Article revision	10
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	\geq
Nominal voltage U_N	63 V
Nominal current I_N	12 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	T

Cable/line

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
	-40 °C ... 105 °C (without mechanical actuation)

Standards and regulations

M12	
Standard designation	M12 connector

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier




1418341

<https://www.phoenixcontact.com/us/products/1418341>

Drawings

Schematic diagram



Connector pin assignment of M12 plug, 4-pos., T-coded, view of pin side

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418341>

cUL Recognized				
Approval ID: E468743-20190917				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	63 V	12 A	16 - 16	-

UL Recognized				
Approval ID: E468743-20190917				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	63 V	12 A	16 - 16	-

cULus Recognized				
------------------	--	--	--	--

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	da688688-a16a-4823-b45a-470b4cded903

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com