

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier



1411964

<https://www.phoenixcontact.com/us/products/1411964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet, 8-position, Socket, straight, M12, coding: X, PCB mounting, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

## Commercial data

Item number	1411964
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQBGG
GTIN	4046356991612
Weight per piece (including packing)	4.786 g
Weight per piece (excluding packing)	4.456 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

### Data management status

Article revision	02
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$> 100 \text{ M}\Omega$
Nominal voltage $U_N$	50 V AC
	60 V DC
Nominal current $I_N$	0.5 A (Data)
Transmission characteristics (category)	CAT6 <sub>A</sub>

### Connection data

Connection method	SMD reflow
-------------------	------------

### Interfaces

Signal type/category	Ethernet
----------------------	----------

### Material specifications

Material	Die-cast zinc, nickel-plated (Shield crossover)
Flammability rating according to UL 94	V0
Contact material	CuZn

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier



1411964

<https://www.phoenixcontact.com/us/products/1411964>

Contact surface material	Au
Contact carrier material	PA

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

## Cable/line

Signal type/category	Ethernet
----------------------	----------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
	-55 °C ... 105 °C (without mechanical actuation)

## Standards and regulations

### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-109
Note	In line with

## Mounting

Mounting type	PCB mounting
---------------	--------------

## Packaging specifications

Type of packaging	Tray
Delivery state	with assembly pad

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier




1411964

<https://www.phoenixcontact.com/us/products/1411964>

## Drawings

Schematic diagram



Pin assignment M12 connector, 8-pos., view socket side

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier





1411964

<https://www.phoenixcontact.com/us/products/1411964>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411964>

 <b>cUL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	60 V	0.5 A	-	-

 <b>UL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	60 V	0.5 A	-	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier



1411964

<https://www.phoenixcontact.com/us/products/1411964>

## Classifications

### ECLASS

ECLASS-11.0	27440110
ECLASS-12.0	27440110
ECLASS-13.0	27440110

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12FSX-8P SMD SH T - Contact carrier



1411964  
<https://www.phoenixcontact.com/us/products/1411964>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)