

SAC-3P-Y/2XFS PE SCO - Y distributor



1523971

<https://www.phoenixcontact.com/us/products/1523971>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Y distributor, 4-position, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A and Socket straight M12 SPEEDCON, coding: A

Commercial data

Item number	1523971
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BF10
Product key	BF1GAB
Catalog page	Page 258 (C-2-2017)
GTIN	4046356127509
Weight per piece (including packing)	28.53 g
Weight per piece (excluding packing)	24 g
Customs tariff number	85366990
Country of origin	PL

SAC-3P-Y/2XFS PE SCO - Y distributor



1523971

<https://www.phoenixcontact.com/us/products/1523971>

Technical data

Notes

General	with center distance of 18 mm, suitable for molded connectors and unshielded connectors that can be assembled with QUICKON IDC terminal block connection technology and a connection range of 0.14 mm ² to 0.34 mm ²
---------	--

Product properties

Product type	Y-distributor
Number of positions	4
No. of cable outlets	2
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3


Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC 60 V DC
Nominal current I _N	4 A

Signaling

Status display	no
Status display present	No

Dimensions

Dimensional drawing	
Width	33 mm
Height	14.8 mm
Length	50.1 mm
Center distance	18 mm

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing

SAC-3P-Y/2XFS PE SCO - Y distributor



1523971

<https://www.phoenixcontact.com/us/products/1523971>

Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Locking type	SPEEDCON
Coding type	A

Connection 2

Type	Socket straight M12 SPEEDCON
Locking type	SPEEDCON
Coding type	A

Connection 3

Type	Socket straight M12 SPEEDCON
Locking type	SPEEDCON
Coding type	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SAC-3P-Y/2XFS PE SCO - Y distributor


1523971

<https://www.phoenixcontact.com/us/products/1523971>




Drawings

Dimensional drawing



Plug M12 x 1, Y distributor

Schematic diagram




Pin assignment M12 male connector, 5-pos., A-coded, male side

SAC-3P-Y/2XFS PE SCO - Y distributor

1523971


<https://www.phoenixcontact.com/us/products/1523971>

Schematic diagram



Layout of connector pin assignments

Circuit diagram




SAC-3P-Y/2XFS PE SCO - Y distributor

1523971

<https://www.phoenixcontact.com/us/products/1523971>



Schematic diagram



Pin assignment socket M 12, 3-pos. + PE

SAC-3P-Y/2XFS PE SCO - Y distributor




1523971

<https://www.phoenixcontact.com/us/products/1523971>

Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1523971>




EAC
Approval ID: RU C-DE.AI30.B.01102



EAC
Approval ID: RU C-DE.BL08.B.00511

	UL Listed Approval ID: E221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-

	cUL Listed Approval ID: E221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-

cULus Listed

SAC-3P-Y/2XFS PE SCO - Y distributor



1523971

<https://www.phoenixcontact.com/us/products/1523971>

Classifications

ECLASS

ECLASS-11.0	27440106
ECLASS-12.0	27440106
ECLASS-13.0	27440106

ETIM

ETIM 9.0	EC002925
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P-Y/2XFS PE SCO - Y distributor



1523971
<https://www.phoenixcontact.com/us/products/1523971>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	1.102 kg CO2e

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com