


Series 801 Mighty Mouse Double-Start ACME Thread PC Tail Receptacle with Threaded Standoff 801-075 Ordering Information



Series 801



Rear Panel Mount Jam-Nut Receptacle connectors offer military grade performance in a small, lightweight package. Features a double-start modified stub ACME mating thread for improved protection against cross-mating and thread damage. Aluminum or stainless steel, square flange receptacle for attachment to rigid PC boards. Square flange receptacle with integral standoffs for PC board washout come threaded with #2-56 stainless steel heli-coils. Gold-plated copper alloy PC tail contacts are factory installed and potted with epoxy. Contacts are non-removable.

How To Order						
Sample Part Number		801-075	-07	M	6-7	P A
Series	801-075 = Receptacle with Printed Circuit Board Contacts or Solder Cup Contacts					
Shell Style	-07 = Jam-Nut, Rear Panel Mount					
Material and Finish	M = Aluminum / Electroless Nickel RoHS Compliant MT = Aluminum / Nickel-PTFE RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate Z1 = Stainless Steel / Passivated RoHS Compliant					
Shell Size - Insert Arrangement	See Contact Arrangements page D-3					
Contact Type	P = Pin, PC Tail S = Socket, PC Tail					
Polarization (See Table I)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. E F = Pos. F G = Pos. G H = Pos. H J = Pos. J					

D

Table I: Keyway Positions		
Position	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

NOTES

1. Contacts are non removable, the connector is back potted
2. This receptacle connector mates with all quick coupling high density plug connectors with same polarization and opposite contact gender (801-01, 801-002, 801-007, and 801-008)

Material / finish:

- Shell, jam-nut: aluminum alloy or CRES
- Insulator: LCP / N.A.
- Interfacial seal, O-ring, peripheral seal: fluorosilicone / N.A.
- Contact: copper alloy / gold plate per ASTM B 488, Type II, Code C, Class 1.25 (.00005 minimum thickness), over a suitable underplate
- Potting compound: epoxy / N.A.


Dimensions in Inches (millimeters) are subject to change without notice.



Series 801 Mighty Mouse Double-Start ACME Thread PC Tail Receptacle with Threaded Standoff

801-075-07 Dimensions

Jam-nut PCB receptacle with threaded heli-coil standoff - shell style 07



D

Dimensions								
Shell Size	A Thread	B Thread	C Flat	Ø D	E SQ	F BSC	G Typ	H
5	.3125-.05P-1L-2A	.3750-28 UN-2A	.348 (8.84)	.720 (18.29)	.545 (13.84)	.363 (9.22)	.143 (3.63)	.772 (19.61)
6	.375-.05P-1L-2A	.4375-28 UNEF-2A	.408 (10.36)	.800 (20.32)	.595 (15.11)	.423 (10.74)	.203 (5.16)	.772 (19.61)
7	.4375-.05P-1L-2A	.5625-32 UN-2A	.534 (13.56)	.900 (22.86)	.723 (18.36)	.483 (12.27)	.263 (6.68)	.772 (19.61)
8	.5000-.05P-1L-2A	.5625-32 UN-2A	.534 (13.56)	.980 (24.89)	.723 (18.36)	.545 (13.84)	.325 (8.25)	.772 (19.61)
9	.5625-.05P-1L-2A	.6250-28 UN-2A	.594 (15.09)	1.080 (27.43)	.790 (20.07)	.607 (15.42)	.387 (9.83)	.772 (19.61)
10	.6250-.05P-1L-2A	.6875-28 UN-2A	.656 (16.66)	1.160 (29.46)	.855 (21.72)	.670 (17.02)	.450 (11.43)	.772 (19.61)
11	.6875-.05P-1L-2A	.7500-28 UN-2A	.716 (18.19)	1.220 (30.99)	.925 (23.50)	.715 (18.16)	.495 (12.57)	.772 (19.61)
13	.8125-.1P-2L-2A	.8750-28 UN-2A	.843 (21.41)	1.370 (34.80)	1.044 (26.52)	.812 (20.62)	.592 (15.04)	.881 (22.38)
16	1.0000-.1P-2L-2A	1.0625-20 UN-2A	1.020 (25.91)	1.620 (41.15)	1.230 (31.24)	.981 (24.92)	.751 (19.08)	.881 (22.38)
17	1.0625-.1P-2L-2A	1.1250-28 UN-2A	1.094 (27.79)	1.720 (43.69)	1.290 (32.77)	1.060 (26.92)	.840 (21.34)	.881 (22.38)
19	1.1875-.1P-2L-2A	1.2500-28 UN-2A	1.225 (31.12)	1.920 (48.77)	1.415 (35.94)	1.191 (30.25)	.971 (24.66)	.881 (22.38)
21	1.3125-.1p-2L-2a	1.3750-28 UN-2A	1.345 (34.16)	2.100 (53.34)	1.577 (40.06)	1.322 (33.58)	1.102 (27.99)	.881 (22.38)

Jam-Nut Panel Cutout		
Shell Size	A Flat ± .002 (.05)	Ø B +.005 (-.13) -.000 (-.00)
5	.356 (9.04)	.380 (9.65)
6	.416 (10.57)	.443 (11.25)
7	.542 (13.77)	.567 (14.40)
8	.542 (13.77)	.567 (14.40)
9	.602 (15.29)	.630 (16.00)
10	.664 (16.87)	.693 (17.60)
11	.726 (18.44)	.755 (19.18)
13	.851 (21.62)	.880 (22.35)
16	1.028 (26.11)	1.067 (27.10)
17	1.102 (27.99)	1.130 (28.70)
19	1.233 (31.32)	1.255 (31.88)
21	1.352 (34.34)	1.380 (35.05)

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[801-075-07M8-2PA](#) [801-075-07M21-130SA](#) [801-075-07M9-19SA](#) [801-075-07M9-19SB](#) [801-075-07M6-7PA](#) [801-075-07M7-10SA](#) [801-075-07M13-37SA](#) [801-075-07M9-19SC](#) [801-075-07M6-23PA](#) [801-075-07M8-13PA](#) [801-075-07MT9-19PA](#) [801-075-07AB10-26SA](#) [801-075-07M11-31SA](#) [801-075-07M13-37PA](#) [801-075-07M13-37PB](#) [801-075-07M8-13SB](#) [801-075-07M8-13SC](#) [801-075-07MT10-26SA](#) [801-075-07NF10-26SA](#) [801-075-07NF10-26SB](#) [801-075-07NF13-37SA](#) [801-075-07NF13-37SB](#) [801-075-07NF16-55SA](#) [801-075-07NF6-7SA](#) [801-075-07NF7-10SA](#) [801-075-07NF9-19SA](#) [801-075-07MT10-26PA-501H](#) [801-075-07MT13-37SA-501H](#) [801-075-07MT17-85PA-501H](#) [801-075-07MT17-85SA-501H](#) [801-075-07MT16-55PA-501H](#) [801-075-07MT8-13SA-501H](#) [801-075-07M10-26PA](#) [801-075-07M13-37SA-501](#) [801-075-07AB10-26SA-109C](#) [801-075-07AB10-26SB](#) [801-075-07AB10-26SB-109C](#) [801-075-07AB17-85SA-109C](#) [801-075-07AB19-100SA-109C](#) [801-075-07AB19-100SB](#) [801-075-07AB19-100SB-109C](#) [801-075-07AB19-100SC](#) [801-075-07AB19-100SD](#) [801-075-07AB19-100SD-109C](#) [801-075-07AB6-4SA](#) [801-075-07AB7-10SA](#) [801-075-07AB7-10SB](#) [801-075-07AB7-10SC](#) [801-075-07AB7-10SD](#) [801-075-07AB7-10SE](#) [801-075-07AB7-10SF](#) [801-075-07AB8-13SA](#) [801-075-07AB9-19SA](#) [801-075-07AB9-19SA-109C](#) [801-075-07M10-202SA](#) [801-075-07M10-26SA](#) [801-075-07M10-26SA-501](#) [801-075-07M10-26SB](#) [801-075-07M11-31SA-109C](#) [801-075-07M13-37PA-518](#) [801-075-07M13-37PB-518](#) [801-075-07M13-37SA-109C](#) [801-075-07M16-206PA](#) [801-075-07M17-7SA-501](#) [801-075-07M17-85PA](#) [801-075-07M19-100SA-501](#) [801-075-07M21-130PA](#) [801-075-07M21-130SA-109C](#) [801-075-07M21-130SB-109C](#) [801-075-07M5-3PA](#) [801-075-07M5-3PB](#) [801-075-07M5-3PC](#) [801-075-07M5-3SA](#) [801-075-07M6-4PA](#) [801-075-07M6-6SA](#) [801-075-07M6-7SA](#) [801-075-07M7-10PA](#) [801-075-07M7-25PA](#) [801-075-07M8-28PA](#) [801-075-07M9-19PA](#) [801-075-07M9-19PA-92B](#) [801-075-07M9-19PB](#) [801-075-07M9-19PC](#) [801-075-07M9-19PD](#) [801-075-07M9-210PC](#) [801-075-07M9-4PA](#) [801-075-07MT10-26PA](#) [801-075-07MT10-26PB](#) [801-075-07MT10-26PC](#) [801-075-07MT10-26PD](#) [801-075-07MT10-26SA-518](#) [801-075-07MT10-5PA-501H](#) [801-075-07MT11-31SA](#) [801-075-07MT13-37PA](#) [801-075-07MT13-37PA-501H](#) [801-075-07MT13-37PB](#) [801-075-07MT13-37PC](#) [801-075-07MT13-37SA](#) [801-075-07MT16-205PA](#) [801-075-07MT16-205PB](#)