







PANEL CUT OUT




SHELL SIZE	Ø A ±0.15	B ±0.20 (without marking)	C ±0.20	C ±0.37 specif. 30	D	Ø E	F ± 0.3	Thread	Tightening torque (Nut)
08	11.90	24.00	19.05 ±0.37	19.05	13.75 ± 0.20	14.60 ± 0.20	3.1	9/16 24 UNEF CLASS 2A	2 Nm
10	14.90	26.90	22.15	22.20	16.40 0/+0.2	17.30 0/+0.25	3.1	11/16 24 UNEF CLASS 2A	3 Nm
12	18.95	31.75	27.15	26.97	20.85 0/+0.3	22.10 0/+0.3	3.1	7/8 20 UNEF CLASS 2A	4 Nm
14	22.15	34.90	30.20	30.15	24.00 0/+0.3	25.40 0/+0.3	3 ± 0.1	1"20 UNEF CLASS 2A	5 Nm

DRILLING PATTERN

SHELL 8



SHELL 10/12/14



MATERIAL :

- Shell: Polyamid UL94 V-0
- Insert: Polychloropren (CR)
- Seal gasket : Sealing IP68/69K : Silicone
- O'ring: nitril
- Nut: Aluminium alloy black anodized
- Contact: Brass + gold plated

PERFORMANCE CHARACTERISTICS :

- Operating temperature: -40°C up to 105°C
- Insulation resistance: 5000 MΩ min
- Test potential: 2000 Vrms for #16 layout and 1500 Vrms for #20 layout
- Corrosion salt spray: 500 hours
- Durability: 250 matings and unmatings

- Sealing in mated and unmated conditions:


- IP68 : 1 bar during 1 week : immersion under 10 of water (IEC 60529)
- IP69K : exposure to high pressure water of cleaning equipment (DIN 40050)

NOTE :


- Insert arrangements : refer to C144-UTS1-A

TAILLE	Perçage 1		Perçage 2	
	A	B	C	D
T10	3.98	9.85	5.31	9.20
T12	4.92	12.17	6.56	11.37
T14	5.29	13.10	7.06	12.23

MALE CONNECTOR



FEMALE CONNECTOR



Shell size	I (male connector)	J (female connector)
8	3.8/6 for layout 8-2/8-3/8-4 4.7/7.25 for layout 8-3A/8-98/8-33	3.75/5.8 for layout 8-2/8-3/8-4 4.8/6.9 for layout 8-3A/8-98/8-33
10	4.9/7	4.9/7
12	4.8/7 3.85/5.9 for layout 12-14	5.2/7 3.85/5.9 for layout 12-14
14	4.8/7	5.3/7

UTS7 14 D 19 P . XX

Jam nut receptacle UTS

Shell size

D= Dipsolder contacts

Insert arrangement
(See table)

P = Male contact

S = Female contact

Orientations

Normal (no digit), W,X,Y,Z = different orientations

Specification

CUSTOMER DRAWING

f	05/12/13	DRILLING PATTERN: Modification of view and cotation	
ISS	DATE	Latest modification - by:	MOD N°
Designed by:	SORIN V.	Date: 23/10/08	CUSTOMER DRAWING
TITLE	JAM NUT RECEPTACLE WITH DIPSOLDER CONTACTS		
	UTS HI SEAL		
Scale	3/1	General linear Tolerances: ± 0.2	NPRDS / PROJECT UTS
SOURIAU		WWW.SOURIAU.COM	
FORMAT		SOURIAU DRG N°	
A2		C061-UTS1-A	
		SHEET	
		1/1	
		NOT EXPORT CONTROLLED	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[UTS710D6P](#) [UTS712D10P](#) [UTS714D19P](#) [UTS714D18S](#) [UTS710D6S](#) [UTS710D7P](#) [UTS710D7S](#) [UTS712D10S](#)
[UTS714D19S](#) [UTS712D14P](#) [UTS712D14S](#) [UTS712D2P](#) [UTS712D2S](#) [UTS712D3P](#) [UTS712D3S](#) [UTS712D8P](#)
[UTS712D8S](#) [UTS714D12P](#) [UTS714D12S](#) [UTS714D15P](#) [UTS714D15S](#) [UTS714D18P](#) [UTS714D5P](#) [UTS714D5S](#)
[UTS710D98S](#) [UTS710D98P](#) [UTS714D19PW](#) [UTS714D12PW](#) [UTS712D10SX](#) [UTS714D19SW](#) [UTS710D6PW](#)
[UTS712D8SW](#) [UTS714D12PX](#) [UTS714D5PW](#) [UTS710D98PW](#) [UTS710D98PX](#) [UTS710D98PY](#) [UTS710D98PZ](#)
[UTS712D8PW](#) [UTS710D6SW](#)