


MIL-DTL-38999 Series III Type

233-103 Bulkhead feed-thrus

HERMETIC CONNECTORS

233-103-H7 JAM-NUT MOUNT AND 233-103-DH7 DUAL O-RING JAM-NUT RECEPTACLE



Dimensions								
SHELL SIZE	A THREAD 0.1 P-0.3L- TS-2	H7 Jam-Nut		DH7 Dual O-Ring Jam-Nut		D DIA	E DIM	F THREAD METRIC X 1.0-6G
		B DIA	C	B DIA	C			
9	.6250	1.189 (30.20)	1.063 (27.00)	1.500 (38.10)	1.375 (34.92)	.703 (17.86) .693 (17.60)	.661 (16.79) .655 (16.64)	M17
11	.7500	1.375 (34.92)	1.252 (31.80)	1.625 (41.28)	1.500 (38.10)	.835 (21.21) .825 (20.96)	.771 (19.58) .761 (19.33)	M20
13	.8750	1.500 (38.10)	1.374 (34.90)	1.752 (44.50)	1.626 (41.30)	1.020 (25.91) 1.010 (25.65)	.955 (24.26) .945 (24.00)	M25
15	1.0000	1.626 (41.30)	1.500 (38.10)	1.937 (49.20)	1.811 (46.00)	1.145 (29.08) 1.135 (28.83)	1.085 (27.56) 1.075 (27.30)	M28
17	1.1875	1.752 (44.50)	1.626 (41.30)	2.063 (52.40)	1.937 (49.20)	1.270 (32.26) 1.260 (32.00)	1.210 (30.73) 1.200 (30.48)	M32
19	1.2500	1.937 (49.20)	1.811 (46.00)	2.189 (55.60)	2.063 (52.40)	1.395 (35.43) 1.385 (35.18)	1.335 (33.91) 1.325 (33.65)	M35
21	1.3750	2.063 (52.40)	1.937 (49.20)	2.311 (58.70)	2.189 (55.60)	1.520 (38.61) 1.510 (38.35)	1.460 (37.08) 1.450 (36.83)	M38
23	1.5000	2.189 (55.60)	2.063 (52.40)	2.500 (63.50)	2.300 (58.42)	1.645 (41.78) 1.635 (41.53)	1.585 (40.26) 1.575 (40.00)	M41
25	1.6250	2.311 (58.70)	2.189 (55.60)	2.625 (66.68)	2.400 (60.96)	1.770 (44.96) 1.760 (44.70)	1.710 (43.43) 1.700 (43.18)	M44

Jam-Nut Mount (H7) Panel Thickness			
DASH NO.	G DIM, OAL MAX	H DIM, MAX	J DIM, PANEL
-01	1.670 (42.42)	.890 (22.61)	.125 (3.18) .062 (1.57)
-02	1.780 (45.21)	1.090 (27.69)	.250 (6.35) .062 (1.57)
-03	2.030 (51.56)	1.340 (34.04)	.500 (12.70) .062 (1.57)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[233-103-H7Z111-02SN-03](#) [233-103-H7Z117-08SN-02](#) [233-103-H7ZL13-04SN-02](#) [233-103-H7ZL17-08SN-02](#) [233-103-H7Z121-16SB-02](#) [233-103-H7Z111-35SB-01](#) [233-103-H7Z111-99SN-03](#) [233-103-H7Z113-98SN-01](#) [233-103-H7Z123-35SN-02](#) [233-103-H7Z125-19SN-01](#) [233-103-H7ZL17-08SN-03](#) [233-103-H7ZL25-35PA-01](#) [233-103-H7ZL25-61PN-01](#) [233-103-H7ZL11-04PPN-03](#) [233-103-H7ZL15-35SSN-03](#) [233-103-H7ZL19-35SSA-03](#) [233-103-H7ZL19-35SSB-03](#) [233-103-H7ZL17-35PA-03](#) [233-103-H7Z121-41SN-02](#) [233-103-DH7Z117-35PN-03-585A](#) [233-103-DH7Z119-35PN-03-585A](#) [233-103-DH7ZL17-35PB-01](#) [233-103-DH7ZL25-19PU-03](#) [233-103-DH7ZL25-19SU-03](#) [233-103-DH7ZL25-61PU-03](#)