


Input Screw Terminal Block

XW2C


Consolidate Inputs for Omron
High-density I/O Modules

- Power supply common terminals for input devices
- Operation indicators make it possible to monitor the ON and OFF conditions of input signals with ease
- DIN track and screw mounting are available
- Dedicated cables to Omron PLC I/O modules available, order separately





Ordering Information

■ INPUT SCREW TERMINAL BLOCK

| Appearance | Number of input points | Input mode | Part number |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------|----------------|
|  | 16 | NPN input (negative common) | XW2C-20G5-IN16 |

■ CONNECTING CABLES

| Appearance | Applicable terminal block | Cable length | Part number |
|-------------------------------------------------------------------------------------|---------------------------|--------------------------------------|-------------|
|  | XW2C-20G5-IN16 | 0.5 m (1.64 ft) | XW2Z-050A |
| Single cable for 32-point I/O modules | | 1 m (3.28 ft) | XW2Z-100A |
| | | 1.5 m (4.92 ft) | XW2Z-150A |
| | | 2 m (6.56 ft) | XW2Z-200A |
| | | 3 m (9.84 ft) | XW2Z-300A |
| | | 5 m (16.40 ft) | XW2Z-500A |
|  | XW2C-20G5-IN16 | 1 m (3.28 ft) and 0.75 m (2.46 ft) | XW2Z-100D |
| Bifurcated cable for 32- and 64-point I/O modules | | 1.5 m (4.92 ft) and 1.25 m (4.10 ft) | XW2Z-150D |
| | | 2 m (6.56 ft) and 1.75 m (5.74 ft) | XW2Z-200D |
| | | 3 m (9.84 ft) and 2.75 m (9.02 ft) | XW2Z-300D |
| | | 5 m (16.40 ft) and 4.75 m (15.58 ft) | XW2Z-500D |

Specifications

■ INPUT SCREW TERMINAL BLOCK

| | |
|----------------------------|----------------------------------------|
| Rated current | 1 A/common |
| Rated voltage | 12 to 24 VDC |
| Number of inputs | 16 |
| Input indicator | Orange LED |
| Power supply voltage range | 12 to 24 VDC \pm 5% |
| LED current | 10 mA/point at 24 VDC |
| Insulation resistance | 50 M Ω min. at 500 VDC |
| Dielectric strength | 500 VAC for 1 minute |
| Enclosure rating | IP10 (IEC529) |
| Electrical protection | Class 0 |
| Ambient temperature | Operating: 0°C to 55°C (32°F to 131°F) |

■ CONNECTORS

Ratings/Characteristics

| Item | Rating |
|-----------------------|-----------------------------------------------------------------------|
| Rated current | 1 A at 20°C (68°F) |
| Rated voltage | 125 VAC |
| Contact resistance | 20 m Ω max. with 100 mA at 20 mV max. (See Note 1) |
| Insulation resistance | 100 M Ω min. at 500 VDC |
| Dielectric strength | 500 VAC for 1 minute with a current leakage of 1 mA max. (See Note 2) |
| Enclosure rating | IP00 |
| Electrical protection | Class 0 |
| Ambient temperature | Operating: -25°C to 80°C (-13°F to 176°F) |

Note: 1. The resistance indicated is the contact resistance of the connector.

2. The voltage indicated is the dielectric strength of the connector.



Materials/Finish

| Item | Parts | | Materials/Processing |
|----------------|-------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connector | XG4M-2030 XG4M-4030 XG4M-6030 | Housing | Black PBT resin with glass (UL94V-0) |
| | | Cover | |
| | | Contact | Contact-carrying portion: Phosphor bronze and nickel plated with 0.15- μ m-thick gold Press-fit portion: Phosphor bronze and nickel plated with 2.0- μ m-thick tin |
| | XG4T-2004 XG4T-4004 XG4T-6004 | Strain relief | Black PBT resin with glass (UL94V-0) |
| | | Housing | Black PBT resin (UL94V-0) |
| | | Contact | Contact-carrying portion: Gold-plated phosphor bronze Press-fit portion: Tin-plated phosphor bronze |
| | | Screw | Nickel-plated steel |
| Cable | UL2464 interface cable | | Equivalent to AWG28 |
| Crimp terminal | Fork-type crimp terminal | | Equivalent to 1.25YAS3.5 |



Dimensions

Unit: mm (inch)

XW2C-20G5-IN16



■ TERMINAL ARRANGEMENT



Precautions

■ WIRING

Do not wire the Terminal Block while power is supplied, or the terminals may be short-circuited with the cable and the unit may malfunction.

Do not connect or disconnect the connector while power is supplied to the Terminal Block, otherwise it may malfunction.

■ TERMINAL WIRE CONNECTIONS

The wires can be connected to the M3.5 screw terminal via the following crimp terminals:

2-3.5 type (round type)

2Y-3.5 type (fork type)

■ MOUNTING

More than one XW2C Input Control Terminal Block can be densely mounted to a DIN track. To do this, move the mounting stays from both sides of the XW2C to the bottom of the XW2C.

Secure both ends of the XW2C with end plates.

Terminal Screw Tightening Torque

When connecting crimp terminals or wires to the terminal block, be sure to tighten each crimp terminal or wire to 0.59 N • m (6 kgf • cm).

NOTE: DIMENSIONS SHOWN ARE IN MILLIMETERS. To convert millimeters to inches divide by 25.4.

OMRON®**OMRON ELECTRONICS, INC.**One East Commerce Drive
Schaumburg, IL 60173**1-800-55-OMRON****OMRON CANADA, INC.**885 Milner Avenue
Scarborough, Ontario M1B 5V8
416-286-6465