


## Receptacle for rear panel mounting

### General information

|                   |                       |
|-------------------|-----------------------|
| Part number       | GK1YBR-P14WCDO-000L   |
| Termination       | Solder                |
| Size              | 1                     |
| Locking principle | Break-Away, Push-Pull |
| Coding            | B (red)               |
| Cable Diameter    | 3.2 – 6.5 mm          |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.



The pin layout corresponds to the view on the termination area

### Contact insert description

|                      |         |
|----------------------|---------|
| Number of contacts   | 14      |
| Contact type         | Sockets |
| Contact diameter     | 0.5 mm  |
| Insulator material   | PEEK    |
| Wire cross section   | AWG 26  |
| Termination          | Solder  |
| Termination diameter | 0.65 mm |

Reverse gender on request

### Technical information

|                                |           |  |
|--------------------------------|-----------|--|
| Nominal current single contact | 5 A       | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Nominal current insert         | 2,5 A     | VDE 0298-4:2003                            |
| Test voltage                   | 0.6 kV AC | EIA-364-20F:2019-02                        |

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

## Mechanical and environmental data

|                       |                 |
|-----------------------|-----------------|
| Degree of protection* | IP6K8 / IP6K9K  |
| Operating temperature | -51 °C – 125 °C |
| Mating cycles         | 5000            |

\*mated condition

## Material and surface treatments

|         |                                |
|---------|--------------------------------|
| Housing | Cu-alloy with ruthenium finish |
| Contact | Cu-alloy with gold finish      |

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved [E110586].

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.