



GBU6005 THRU GBU610

SINGLE PHASE 6.0 AMP BRIDGE RECTIFIERS



FEATURES

- * Ideal for printed circuit board
- * Low forward voltage
- * Low leakage current
- * Polarity: marked on body
- * Mounting position: Any


VOLTAGE RANGE

50 to 1000 Volts

CURRENT

6.0 Amperes

GBU



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	GBU6005	GBU601	GBU602	GBU604	GBU606	GBU608	GBU610	UNITS
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current	6.0							A
.375"(9.5mm) Lead Length at Tc=100°C	6.0							A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	150							A
Maximum Forward Voltage Drop per Bridge Element at 3.0A D.C.	1.0							V
Maximum DC Reverse Current Ta=25°C	5.0							μA
at Rated DC Blocking Voltage Ta=100°C	500							μA
Operating Temperature Range, Tj	-65 — +150							°C
Storage Temperature Range, Tstg	-65 — +150							°C

RATING AND CHARACTERISTIC CURVES (GBU6005 THRU GBU610)

FIG.1-TYPICAL FORWARD CURRENT
DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE FORWARD
SURGE CURRENT




FIG.3-TYPICAL FORWARD
CHARACTERISTICS




FIG.4-TYPICAL REVERSE
CHARACTERISTICS

