

1559958

https://www.phoenixcontact.com/us/products/1559958

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 17-position, Socket, straight, M12-SPEEDCON, coding: A, Rear mounting, Pg9, Solder pins, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240078

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- · All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- · SPEEDCON fast locking system reduces cabling times

Commercial data

Item number	1559958
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEHL
Catalog page	Page 246 (C-2-2013)
GTIN	4046356322669
Weight per piece (including packing)	14.885 g
Weight per piece (excluding packing)	14.8 g
Customs tariff number	85366990
Country of origin	DE



1559958

https://www.phoenixcontact.com/us/products/1559958

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

Mounting

Mounting type	Rear mounting Pg9 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	17
Shielded	no
Coding	A
Thread type	M12

Data management status

Article revision 08

Insulation characteristics

Overvoltage category	Ш
Degree of pollution	3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ



1559958

https://www.phoenixcontact.com/us/products/1559958

Nominal voltage U _N	30 V
Nominal current I _N	1.5 A

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Socket
Tightening torque	2 Nm 3 Nm (Installation-side)

Mechanical properties

Mechanical data

Medianical data	
Insertion/withdrawal cycles	> 100

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Cable/line

Ambient temperature (operation)	-40 °C 85 °C (cable, fixed installation)
	-25 °C 85 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)
	-25 °C 85 °C (Cable, flexible installation)
	-40 °C 85 °C (cable, fixed installation)

Standards and regulations

M12


Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101



1559958

https://www.phoenixcontact.com/us/products/1559958

Drawings



Pin assignment M12, 17-pos., socket side view



1559958

https://www.phoenixcontact.com/us/products/1559958

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1559958

c 932 us	cULus Recognized Approval ID: E221474-20140616				
		Nominal voltage U_N	Nominal current I _N	Cross section AWG	Cross section mm ²
		30 V	1.5 A	-	-

7/	UL Recognized Approval ID: E118976-20100522				
		Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
		30 V	1.5 A	26 - 26	-



1559958

https://www.phoenixcontact.com/us/products/1559958

Classifications

UNSPSC 21.0

ECLASS

252.65		
27440102		
27440116		
27440116		
ETIM		
EC002635		

39121400



1559958

https://www.phoenixcontact.com/us/products/1559958

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c8480303-87b9-41a0-9f3b-a1be8c35c67a

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com